


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—		H	REV PER ECO 14-014240	10-1-14	CT	CD



- THIS PART CONFORMS TO REQUIREMENTS FOR DANIELS CRIMP TOOL NO. FT8, WITH DANIELS POSITIONER PART NO. TP731, STRIP LENGTH .375, #16 AWG SETTING 8, #18 AWG SETTING 6.
- MATES WITH 212013-1 IN AMPLIMITE CONNECTOR ASSEMBLIES ONLY.
- FINISH: PLATED GOLD .000050 [0.00127] MIN THK PER ATSM-B-488 OVER NICKEL .000050 [0.00127] MIN THK PER AMS-QQ-N-290.
- FINISH: PLATED GOLD .000030 [0.00076] MIN THK PER ATSM-B-488 OVER NICKEL .000050 [0.00127] MIN THK PER AMS-QQ-N-290.
- WIRE BARREL WILL ACCEPT #16-#18 AWG WIRE.
- PART NUMBER IS RESTRICTED.

6

PRELIMINARY NOT RELEASED FOR PRODUCTION

4	212014-2
3	212014-1
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C.THOMAS 11/10/00	TE TE Connectivity			
DIMENSIONS: INCHES [mm]		CHK D.MILLER 11/10/00				
		APVD D.MILLER 11/10/00	NAME ASSEMBLY, SOCKET CONTACT POWER VIII, #16 & #18 AWG			
		PRODUCT SPEC 108-10045				
MATERIAL SEE CALLOUTS		APPLICATION SPEC 114-10014	SIZE A2	CAGE CODE 00779	DRAWING NO C=212014	RESTRICTED TO -
		FINISH SEE TABLE	WEIGHT -			
		CUSTOMER DRAWING				