



OPTION D




I.D. SLOT CODE TO WIRE GAUGE CHART	
I.D. SLOT CODE	WIRE GAUGE
A	24 AWG.

PLATING CODE (STRIPE ON CARRIER STRIP)	
PLATING	COLOR
15 GOLD	YELLOW


- NOTES:
1. MATERIAL:
HOUSING: POLYESTER(PBT), GLASS FILLED, UL94 V-0;
COLOR: BLACK
TERMINAL: PHOSPHOR BRONZE
 2. FINISH:
15 GOLD: 0.38 MICROMETERS/15 MICROINCHES MINIMUM GOLD IN
1.91 MICROMETERS/75 MICROINCHES MINIMUM TIN
OVER NICKEL UNDERPLATE OVERALL
 3. TO BE USED WITH 24 AWG STRANDED WIRE WITH (1.35)/.053
DIAMETER MAXIMUM INSULATION
 4. SEE TABLE FOR AVAILABLE CIRCUIT SIZES
 5. STANDARD PACKAGING PER PK-70873-0001. OPTIONAL PACKAGING
MAY BE AVAILABLE, REQUEST DRAWING PK-70400
 6. PARTS STACKABLE END TO END ON (2.54)/.100 CENTERS
 7. PRODUCT SPECIFICATION: PS-70400
 8. SEE DRAWING SDA-70400-**** (SHEET 3) FOR OPTIONAL
HOUSING DETAILS
 9. 4 CIRCUIT SHOWN. 3-25 CIRCUITS HAVE 2 RIBS
 10. TO MATE WITH MOLEX PART NUMBERS: 70004-**** & 70013-****
 11. 2 CIRCUIT ASSEMBLIES SUPPLIED AS GROUPED PAIRS



SECTION C-C



PRE-LOADED ASSEMBLY



CKT. SIZE	A	B	EDP. NO.
2	(2.54) 1.00	(5.05) 1.99	I4-56-3024
3	(5.08) 2.00	(7.59) 2.99	I4-56-3034
4	(7.62) 3.00	(10.13) 3.99	I4-56-3044
5	(10.16) 4.00	(12.67) 4.99	I4-56-3054
6	(12.70) 5.00	(15.21) 5.99	I4-56-3064
7	(15.24) 6.00	(17.75) 6.99	I4-56-3074
8	(17.78) 7.00	(20.29) 7.99	I4-56-3084
9	(20.32) 8.00	(22.83) 8.99	I4-56-3094
10	(22.86) 9.00	(25.37) 9.99	I4-56-3104
11	(25.54) 1.000	(27.91) 1.099	I4-56-3114
12	(27.94) 1.100	(30.45) 1.199	I4-56-3124
13	(30.48) 1.200	(32.99) 1.299	I4-56-3134
14	(33.02) 1.300	(35.53) 1.399	I4-56-3144
15	(35.56) 1.400	(38.07) 1.499	I4-56-3154
16	(38.01) 1.500	(40.61) 1.599	I4-56-3164
17	(40.64) 1.600	(43.15) 1.699	I4-56-3174
18	(43.18) 1.700	(45.69) 1.799	I4-56-3184
19	(45.72) 1.800	(48.23) 1.899	I4-56-3194
20	(48.26) 1.900	(50.77) 1.999	I4-56-3204
21	(50.80) 2.000	(53.31) 2.099	I4-56-3214
22	(53.34) 2.100	(55.85) 2.199	I4-56-3224
23	(55.88) 2.200	(58.39) 2.299	I4-56-3234
24	(58.42) 2.300	(60.93) 2.399	I4-56-3244
25	(60.96) 2.400	(63.47) 2.499	I4-56-3254

REMOVE ENG NO. EC NO: UCP2011-110 G DWYANNS/BARRA 2010/10/19 CHKDORGAN 2010/10/19 APPR: SKILLER 2010/11/24	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM/IN		SCALE	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION		
			 =0  =0  =0	4 PLACES	± ---	± ---	DRAWN BY	DATE	ASSEMBLY, SL CONNECTOR SINGLE ROW 2.54/100 GRID			
				3 PLACES	± ---	± .010	CHECKED BY	DATE				
				2 PLACES	± 0.25	± .014	WAZ	1984/10/09				
				1 PLACE	± 0.35	± ---	APPROVED BY	DATE				
			ANGULAR ±1/2°			SMILLER	2010/11/24	 MOLEX INCORPORATED				
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
						SEE TABLE		SDA-70400-0596-0619		1 OF 1		
						SIZE C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				