

AT-CUT CRYSTAL UNIT (Metal-can Type)

RoHS compliant

HC-49/U-S





FEATURES

- Available in Tape and reel form.
- Suitable for various applications such as communication devices, AV devices and measuring instruments.

Taping dimension : 2000pcs/Ammo pack [mm]

DIMENSION [mm]



STANDARD SPECIFICATIONS

Item	Model	HC-49/U-S	Conditions
Nominal Frequency	f_0	3.5MHz~30.0MHz (Fundamental)	Need to contact us for the available frequency
		30.0MHz~50.0MHz (3rd Overtone)	
Frequency Tolerance	$\Delta f/f_0$	$\pm 30\text{ppm}$	at 25°C
Frequency Tolerance over Operating Temperature Range	$\Delta f/f_0$	below 6.0MHz: $\pm 50\text{ppm}$	-10°C~+60°C
		above 6.0MHz: $\pm 30\text{ppm}$	
Operating Temperature Range	T_{OPR}	-20°C~+70°C	
Storage Temperature Range	T_{STR}	-40°C~+85°C	
Motional (series) resistance	R_1	Refer to the following table	at 25°C
Load capacitance	C_L	Fundamental: 10.0pF~∞ 3rd Overtone: 5.0pF~∞	Need to specify your requirement
Shunt capacitance	C_0	7.0pF Max.	
Level of drive	D_L	100 μW	
Insulation Resistance	I_R	500M Ω Min.	DC100V $\pm$ 15V
Aging (first year)	$\Delta f/f_0$	$\pm 5\text{ppm}$ Max.	25°C $\pm$ 3°C

MOTIONAL (SERIES) RESISTANCE (R_1)

Frequency Range	$3.5\text{MHz} \leq f_0 < 4.0\text{MHz}$	$4.0\text{MHz} \leq f_0 < 6.0\text{MHz}$	$6.0\text{MHz} \leq f_0 < 10\text{MHz}$	$10\text{MHz} \leq f_0 < 14\text{MHz}$	$14\text{MHz} \leq f_0 < 30\text{MHz}$	$30\text{MHz} \leq f_0 < 36\text{MHz}$	$36\text{MHz} \leq f_0 \leq 50\text{MHz}$
Mode	Fundamental	Fundamental	Fundamental	Fundamental	Fundamental	3rd Overtone	3rd Overtone
R_1	200 Ω Max.	150 Ω Max.	100 Ω Max.	80 Ω Max.	50 Ω Max.	140 Ω Max.	100 Ω Max.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Citizen:

[HC49US-40.000MABJ-UB](#) [HC49US-16.384MABJ-UB](#) [HC49US-13.500MABJ-UB](#) [HC49US-9.8304MABJ-UB](#)
[HC49US-32.768MABJ-UB](#) [HC49US-16.9344MABJ-UB](#) [HC49US-10.000MABJ-UB](#) [HC49US-20.000MABJ-UB](#)
[HC49US-16.000MABJ-UB](#) [HC49US-24.000MABJ-UB](#) [HC49US-11.0592MABJ-UB](#) [HC49US-29.4912MABJ-UB](#)
[HC49US-9.216MABJ-UB](#) [HC49US-15.000MABJ-UB](#) [HC49US-12.000MABJ-UB](#) [HC49US-19.6608MABJ-UB](#) [HC49US-](#)
[4.9152MABJ-UB](#) [HC49US-11.2896MABJ-UB](#) [HC49US-6.000MABJ-UB](#) [HC49US-12.288MABJ-UB](#) [HC49US-](#)
[17.734475MABJ-UB](#) [HC49US-6.176MABJ-UB](#) [HC49US-4.000MABJ-UB](#) [HC49US-28.224MABJ-UB](#) [HC49US-](#)
[8.192MABJ-UB](#) [HC49US-4.194304MABJ-UB](#) [HC49US-50.000MABJ-UB](#) [HC49US-48.000MABJ-UB](#) [HC49US-](#)
[27.000MABJ-UB](#) [HC49US-18.000MABJ-UB](#) [HC49US-15.360MABJ-UB](#) [HC49US-5.000MABJ-UB](#) [HC49US-](#)
[32.000MABJ-UB](#) [HC49US-33.8688MABJ-UB](#) [HC49US-49.152MABJ-UB](#) [HC49US-4.096MABJ-UB](#) [HC49US-](#)
[18.432MABJ-UB](#) [HC49US-8.000MABJ-UB](#) [HC49US-3.579545MABJ-UB](#) [HC49US-24.576MABJ-UB](#) [HC49US-](#)
[14.7456MABJ-UB](#) [HC49US-14.31818MABJ-UB](#) [HC49US-21.47727MABJ-UB](#) [HC49US-6.144MABJ-UB](#) [HC49US-](#)
[25.000MABJ-UB](#) [HC49US-10.240MABJ-UB](#) [HC49US-7.680MABJ-UB](#) [HC49US-7.3728MABJ-UB](#) [HC49US-](#)
[22.1184MABJ-UB](#) [HC49US-6.144MBBP-UB](#) [HC49US-10.000MABKUB](#) [HC49US-24.000MABKUB](#) [HC49US-](#)
[24.576MABJUB](#) [HC49US-4.000MBBIUB](#) [HC49US-6.000MABO-UB](#) [HC49US-3.6864MABJ-UB](#) [HC49US-13.560MBBI-](#)
[UT](#) [HC49US-13.560MBBIUB](#) [HC49US-4.000MBBJ-UB](#)