



Part Number: 91999-3530

Image not available

Status: Active - Custom
Series: 91999
Category: PCB Headers
Overview: RAST 5 Connector System

Series image - Reference only

Part Detail

General

Status	Active - Custom
Category	PCB Headers
Series	91999
Application	Power, Wire-to-Board
Comments	<p>"This Molex product is manufactured from material that has the following ratings, tested by independent agencies:</p> <p>a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.</p> <p>b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12, and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety, section 30 Resistance to heat and fire.</p> <p>The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s).</p> <p>If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options."</p>
Overview	RAST 5 Connector System
Product Name	RAST 5

Physical

Breakaway	No
Circuits (Loaded)	7
Circuits (maximum)	7
Color - Resin	Natural
Durability (mating cycles max)	10
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Compliant	Yes
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	No
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Resin	Nylon
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.90mm
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.40mm
Packaging Type	Bag
Pitch - Mating Interface	5.00mm
Pitch - Termination Interface	5.00mm
Plating min - Mating	5.080µm
Polarized to PCB	Yes
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-20C TO +120C
Termination Interface: Style	Through Hole

Electrical

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	16A
Voltage - Maximum	250V AC

Agency Certification

CSA	LR19980
-----	---------

Material Info

UPC	883906919436
-----	--------------

Reference - Drawing Numbers

Packaging Specification	PK-90858-001
Product Specification	PS-99020-0037

Sales Drawing

SD-91999-001, SD-93319-001

Application Tooling

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application**Tooling**

[Check our list of old tooling that used to be available for this part](#)