


P22P 170mAh

Prismatic size (HR22)


Dimensions

(mm)




Width (mm)	26.50
Height 1 (mm)	46.00
Height 2 (mm)	48.50
Approximate weight (g)	32

Fast Charge (charge control required)




Low Rate Discharge



Specifications

Norminal Voltage	8.4V	
Discharge Capacity*	Typical	175mAh
	Rated(Min.)	170mAh
Internal reststance at 1000Hz at charged state	max. 2000mΩ	
Recommended discharge current	17 ~ 510mA	
Charge	Standard	0.1CmA*16hrs
	Rapid	0.5CmA-dV***
Ambient Temperature	Charge	Standard 0°C~45°C
		Rapid 10°C~45°C
	Discharge	-20°C~50°C
	Storage	-20°C~35°C

High Rate Discharge



* After charging at 0.1CmA for 16hours, discharge at 0.2CmA to 1.0V at 20°C

** For reference only.

*** Please consult Panasonic for details of -dV.

Battery performance and cycle life are strongly by how they are used.
In order to maximize battery safety, please consult Panasonic when determining charge/discharge specification, warning label contents and unit design.