


DESCRIPTION: .370" STAMPED FEMALE R/A D-SUB CONNECTOR




SERIES _____
NUMBER OF CONTACTS _____
GENDER _____
1 = MALE
2 = FEMALE (NO GROUND INDENTS)
PC MOUNT _____
3 = NICKEL SHELL _____
HARDWARE OPTIONS: _____
16 = .120 MATING HOLE WITH INSIDE GROUND STRAP
17 = 4-40 INSERT WITH INSIDE GROUND STRAP
18 = 4-40 STANDOFF WITH INSIDE GROUND STRAP
53 = 4-40 INSERT WITH FORK BOARD LOCKS
56 = 4-40 STANDOFF WITH FORK BOARD LOCKS
PLATING: _____
1 = GOLD FLASH

MATERIALS:
INSULATOR: NYLON 9T, UL94V-0 - 260°C PROCESS TEMP
CHEMICAL RESISTANCE, COLOR BLACK
SHELL: STEEL, NICKEL TIN PLATED
CONTACT: MALE: BRASS; FEMALE: PHOSPHOR BRONZE
GOLD FLASH - MATING AREA
TIN PLATING ON TAIL ENDS

RoHS COMPLIANT

ELECTRICAL:
CURRENT RATING: 5 AMPERES
DIELECTRIC WITHSTANDING VOLTAGE: 1000VAC rms AT SEA LEVEL
INSULATION RESISTANCE: 5000 MEGOHMS MIN.
CONTACT RESISTANCE: 10 MILLIOHMS MAX.
WORKING TEMPERATURE: -55° TO +125° C



(9, 15, 25, 37 POSITIONS)

NUMBER OF CONTACTS	"A" Inch (mm)	"B" Inch (mm)	"C" Inch (mm)	"D" Inch (mm)
9	1.214 (30.84)	.984 (24.99)	.432 (10.97)	.109 (2.76)
15	1.545 (39.24)	1.312 (33.32)	.756 (19.20)	.109 (2.76)
25	2.088 (53.04)	1.852 (47.04)	1.304 (33.12)	.109 (2.76)
37	2.730 (69.34)	2.500 (63.50)	1.956 (49.68)	.109 (2.76)

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
PAM JENKINS

CHECKED:

SCALE:

DWG NO.

DATE:
9-15-05

DATE:

SHEET
1 OF
1

REV
3

NorComp

192-YYY-213RYY1