

QT-Brightek Side View LED Series

0602 Side View LED

Part No.: QBLP617 Series

Product: QBL617_Series	Date: February 06, 2014	Page 1 of 13
	Version# 1.4	

Table of Contents:

Introduction	3
Electrical / Optical Characteristic (T=25 °C)	4
Absolute Maximum Rating	4
CIE Chromaticity Table	7
Characteristic Curves.....	8
Solder Profile & Footprint.....	10
Packing	11
Labeling	12
Ordering Information	12
Revision History	13
Disclaimer	13

Introduction

Feature:

- Water clear lens
- Package in tape and reel
- Side View Ultra bright 0602 LED package
- InGaN technology for IG/IB/IW
- AlInGaP technology for R/AG/Y/O
- 140° Viewing Angle

Description:

These ultra bright side view 0602 LEDs have a height profile of 0.6mm. With higher packing density and smaller footprint, these LEDs are ideal for smaller equipment and miniature application.

Application:



- Status indication
- Back lighting application
- General Use

Certification & Compliance:

- TS16949
- ISO9001
- RoHS Compliant



Dimension:



Units: mm / tolerance = +/-0.1mm

Electrical / Optical Characteristic (T=25 °C)

Product	Color	I _F (mA)	V _F (V)		λ _D (nm)			I _V (mcd)	
			Typ.	Max.	Min.	Typ.	Max.	Min.	Typ.
QBLP617-IB	Blue	20	3.1	3.7	465	470	475	50	63
QBLP617-IG	True Green	20	3.1	3.7	520	525	530	200	380
QBLP617-R	Red	20	2.0	2.5	615	620	630	63	100
QBLP617-AG	Yellow Green	20	2.0	2.5	565	570	576	25	35
QBLP617-Y	Yellow	20	2.0	2.5	585	590	595	80	150
QBLP617-O	Orange	20	2.0	2.5	600	605	610	80	165
QBLP617-IW	White	20	3.1	3.7	-	X = 0.28 Y = 0.29	-	160	250

Absolute Maximum Rating

Material	P _d (mW)	I _F (mA)	I _{FP} (mA)*	V _R (V)	T _{OP} (°C)	T _{ST} (°C)	T _{SOL} (°C)**
InGaN	111	30	125	5	-40 to +80	-40 to +85	260
AlInGaP	75	30	125	5	-40 to +80	-40 to +85	260

*Duty 1/8 @ 1kHz

**IR Reflow for no more than 10 sec @ 260 °C

Forward Voltage V_F for AlInGaP @ $I_F=20\text{mA}$

Bin	Min.	Max.	Unit
□	1.7	2.5	V

Forward Voltage V_F for InGaN @ $I_F=20\text{mA}$

Bin	Min.	Max.	Unit
f	2.8	3.1	V
g	3.1	3.4	
h	3.4	3.7	

Luminous Intensity I_V @ $I_F=20\text{mA}$

Bin	Min.	Max.	Unit
D	25	32	mcd
E	32	40	
F	40	50	
G	50	63	
H	63	80	
I	80	100	
J	100	125	
K	125	160	
L	160	200	
M	200	250	
N	250	320	
O	320	400	
P	400	500	
Q	500	630	

Dominant Wavelength λ_D for Blue @ $I_F=20\text{mA}$

Bin	Min.	Max.	Unit
G	465	467.5	nm
H	467.5	470	
I	470	472.5	
J	472.5	475	

Dominant Wavelength λ_D for Green @ $I_F=20\text{mA}$

Bin	Min.	Max.	Unit
U	520	522.5	nm
V	522.5	525	
W	525	527.5	
X	527.5	530	

Dominant Wavelength λ_D for Red @ $I_F=20\text{mA}$

Bin	Min.	Max.	Unit
s	615	620	nm
t	620	625	
u	625	630	

Dominant Wavelength λ_D for Yellow Green @ $I_F=20\text{mA}$

Bin	Min.	Max.	Unit
h	565	568	nm
i	568	572	
j	572	576	


Dominant Wavelength λ_D for Yellow @ $I_F=20\text{mA}$

Bin	Min.	Max.	Unit
m	585	590	nm
n	590	595	

Dominant Wavelength λ_D for Orange @ $I_F=20\text{mA}$

Bin	Min.	Max.	Unit
p	600	605	nm
q	605	610	







CIE Chromaticity Table









D		E		F		G	
0.25	0.24	0.27	0.25	0.29	0.26	0.31	0.27
0.25	0.31	0.27	0.32	0.29	0.33	0.31	0.34
0.27	0.31	0.29	0.32	0.31	0.33	0.33	0.34
0.27	0.24	0.29	0.25	0.31	0.26	0.33	0.27
0.25	0.24	0.27	0.25	0.29	0.26	0.31	0.27

Characteristic Curves

InGaN (IB/IG/IW)




AllnGaP (R/AG/Y/O)




Solder Profile & Footprint

- Recommended tin solder specifications: melting temperature in the range of 178~192 °C
- The recommended reflow soldering profile is as follows (temperatures indicated are as measured on the surface of the LED resin):



Recommended Pad Layout




Units: mm

Tolerance: $\pm 0.1\text{mm}$


Packing

Reel Dimension:




Unit: mm

Tape Dimension:




Unit: mm

Arrangement of Tape:



Packaging Specifications:



Labeling

	QT-Brighttek	
		
Part No: _____		
Customer P/N: _____		
Item: _____		
Q'ty: _____		
Vf: _____		
Iv: _____		
Wl: _____		
Date: _____		
Made in China		

Ordering Information

Part #	Orderable Part #	Spec Range	Quantity per reel
QBLP617-IB	QBLP617-IB	Iv=63mcd typ. @ 20mA / Color=465nm ~ 475nm	4,000 units
QBLP617-IG	QBLP617-IG	Iv=380mcd typ. @ 20mA / Color=520nm ~ 530nm	4,000 units
QBLP617-R	QBLP617-R	Iv=100mcd typ. @ 20mA / Color=615nm ~ 630nm	4,000 units
QBLP617-AG	QBLP617-AG	Iv=35mcd typ. @ 20mA / Color=565nm ~ 576nm	4,000 units
QBLP617-Y	QBLP617-Y	Iv=150 mcd typ. @ 20mA / Color=585nm ~ 595nm	4,000 units
QBLP617-O	QBLP617-O	Iv=165mcd typ. @ 20mA / Color=600nm ~ 610nm	4,000 units
QBLP617-IW	QBLP617-IW	Iv=250mcd typ. @ 20mA / CCT Coordinate: (X= 0.28, Y = 0.29) typ.	4,000 units

Revision History

Description:	Revision #	Revision Date
New Release of QBLP617 _series	V1.0	01/11/2012
Add Blue color Spec	V1.1	01/12/2012
Add Orange and White, update to new format	V1.2	06/18/2012
Update White luminous intensity	V1.3	09/13/2013
Update Blue wavelength and luminous intensity	V1.4	02/06/2014

Disclaimer

QT-BRIGHTTEK reserves the right to make changes without further notice to any products herein to improve reliability, function or design. QT-BRIGHTTEK does not assume any liability arising out of the application or use of any product or circuit described herein; neither does it convey any license under its patent rights, nor the rights of others.

Life Support Policy

QT-BRIGHTTEK's products are not authorized for use as critical components in life support devices or systems without the express written approval of QT-BRIGHTTEK. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.