




N-Channel 40-V (D-S), 175°C MOSFET

PRODUCT SUMMARY

$V_{(BR)DSS}$ (V)	$r_{DS(on)}$ (Ω)	I_D (A)
40	0.010 @ $V_{GS} = 10$ V	70
	0.014 @ $V_{GS} = 4.5$ V	58

175°C Rated
Maximum Junction Temperature

TO-220AB




G D S

Top View

SUP70N04-10

DRAIN connected to TAB


TO-263



G D S

Top View

SUB70N04-10



N-Channel MOSFET

ABSOLUTE MAXIMUM RATINGS ($T_C = 25^\circ\text{C}$ UNLESS OTHERWISE NOTED)

Parameter		Symbol	Limit	Unit
Drain-Source Voltage		V_{DS}	40	V
Gate-Source Voltage		V_{GS}	± 20	
Continuous Drain Current ($T_J = 175^\circ\text{C}$)	$T_C = 25^\circ\text{C}$	I_D	70	A
	$T_C = 100^\circ\text{C}$		47	
Pulsed Drain Current		I_{DM}	140	
Avalanche Current		I_{AR}	60	
Repetitive Avalanche Energy ^a		E_{AR}	180	mJ
	$L = 0.1$ mH			
Power Dissipation		P_D	107 ^b	W
	$T_C = 25^\circ\text{C}$			
Operating Junction and Storage Temperature Range		T_J, T_{stg}	-55 to 175	$^\circ\text{C}$

THERMAL RESISTANCE RATINGS

Parameter		Symbol	Typical	Maximum	Unit
Junction-to-Ambient	PCB Mount (TO-263) ^c	R_{thJA}	35	40	$^\circ\text{C/W}$
	Free Air (TO-220)		45	50	
Junction-to-Case		R_{thJC}	1.2	1.4	







Notes:






- Duty cycle $\leq 1\%$.
- See SOA curve for voltage derating.
- Surface mounted on 1" FR4 board.

SPECIFICATIONS (T _J = 25 ° C UNLESS OTHERWISE NOTED)						
Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Static						
Drain-Source Breakdown Voltage	V _{(BR)DSS}	V _{GS} = 0 V, I _D = 250 μA	40			V
Gate Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _{DS} = 250 μA	1		3	
Gate-Body Leakage	I _{GSS}	V _{DS} = 0 V, V _{GS} = ± 20 V			± 100	nA
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} = 40 V, V _{GS} = 0 V			1	μA
		V _{DS} = 40 V, V _{GS} = 0 V, T _J = 125 ° C			50	
		V _{DS} = 40 V, V _{GS} = 0 V, T _J = 175 ° C			150	
On-State Drain Current ^a	I _{D(on)}	V _{DS} = 5 V, V _{GS} = 10 V	70			A
Drain-Source On-State Resistance ^a	r _{DS(on)}	V _{GS} = 10 V, I _D = 30 A		0.008	0.010	Ω
		V _{GS} = 10 V, I _D = 30 A, T _J = 125 ° C		0.014	0.017	
		V _{GS} = 10 V, I _D = 30 A, T _J = 175 ° C		0.0175	0.022	
		V _{GS} = 4.5 V, I _D = 20 A		0.011	0.014	
		V _{GS} = 4.5 V, I _D = 20 A, T _J = 125 ° C		0.019	0.024	
		V _{GS} = 4.5 V, I _D = 20 A, T _J = 175 ° C		0.024	0.031	
Forward Transconductance ^a	g _{fs}	V _{DS} = 15 V, I _D = 30 A	20	57		S
Dynamic ^b						
Input Capacitance	C _{iss}	V _{GS} = 0 V, V _{DS} = 25 V, f = 1 MHz		2700		pF
Output Capacitance	C _{oss}			600		
Reverse Transfer Capacitance	C _{rss}			160		
Total Gate Charge ^c	Q _g	V _{DS} = 15 V, V _{GS} = 10 V, I _D = 70 A		50	100	nC
Gate-Source Charge ^c	Q _{gs}			10		
Gate-Drain Charge ^c	Q _{gd}			9		
Turn-On Delay Time ^c	t _{d(on)}	V _{DD} = 15 V, R _L = 0.2 Ω I _D ≈ 70 A, V _{GEN} = 10 V, R _G = 2.5 Ω		14	30	ns
Rise Time ^c	t _r			12	30	
Turn-Off Delay Time ^c	t _{d(off)}			58	100	
Fall Time ^c	t _f			30	60	
Source-Drain Diode Ratings and Characteristics (T _C = 25 ° C) ^b						
Continuous Current	I _S				70	A
Pulsed Current	I _{SM}				140	
Forward Voltage ^a	V _{SD}	I _F = 70 A, V _{GS} = 0 V		1.0	1.5	V
Reverse Recovery Time	t _{rr}	I _F = 70 A, di/dt = 100 A/μs		50	100	ns

Notes:

- a. Pulse test; pulse width $\leq 300\text{ }\mu\text{s}$, duty cycle $\leq 2\%$.
b. Guaranteed by design, not subject to production testing.
c. Independent of operating temperature.

**TYPICAL CHARACTERISTICS (25°C UNLESS NOTED)**

TYPICAL CHARACTERISTICS (25°C UNLESS NOTED)**THERMAL RATINGS**



Notice

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

[SUB70N04-10-E3](#) [SUP70N04-10-E3](#) [SUP70N04-10](#) [SUB70N04-10](#)