



13			12		11		10		9		8		7		6		5		4		3		2		1			
PACKAGING SEE NOTE 4 SHT 1			4-6 CKT		BULK		TAPE-N-REEL W/ VAC CAPS		N/A		BULK		TAPE-N-REEL W/ VAC CAPS		N/A		BULK		TAPE-N-REEL W/ VAC CAPS		N/A				BULK		BULK	
			8-100 CKT		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES W/ VAC CAPS				TUBES		TUBES	
			DIM. M±0.25 MM				6.10 (.240)				6.10 (.240)				6.10 (.240)				8.13 (.320)				8.13 (.320)					
			PLATING				150 TIN				15 GOLD				30 GOLD				15 GOLD				30 GOLD					
			DIM. H				2.54 (.100)				2.54 (.100)				2.54 (.100)				4.57 (.180)				4.57 (.180)					
CKTS	DIM. A		DIM. B		EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	EDP NUMBER	CKTS	
	MM	IN	MM	IN																								
04	5.08	.200	2.54	.100	015-91-2040	015-91-6040	N/A	015-91-0040	015-91-6042	N/A	015-91-3040	015-91-6043	N/A		015-91-0048	015-91-5049	04											
06	7.62	.300	5.08	.200	015-91-2060	015-91-6060	N/A	015-91-0060	015-91-6062	N/A	015-91-3060	015-91-6063	N/A		015-91-0068	015-91-5069	06											
08	10.16	.400	7.62	.300	015-91-2080	015-91-6080	015-91-3087	015-91-0080	015-91-6082	015-91-3086	015-91-3080	015-91-6083	015-91-3088		015-91-0088	015-91-5089	08											
10	12.70	.500	10.16	.400	015-91-2100	015-91-6100	015-91-3107	015-91-0100	015-91-6102	015-91-3106	015-91-3100	015-91-6103	015-91-3108		015-91-0108	015-91-5109	10											
12	15.24	.600	12.70	.500	015-91-2120	015-91-6120	015-91-3127	015-91-0120	015-91-6122	015-91-3126	015-91-3120	015-91-6123	015-91-3128		015-91-0128	015-91-5129	12											
14	17.78	.700	15.24	.600	015-91-2140	015-91-6140	015-91-3147	015-91-0140	015-91-6142	015-91-3146	015-91-3140	015-91-6143	015-91-3148		015-91-0148	015-91-5149	14											
16	20.32	.800	17.78	.700	015-91-2160	015-91-6160	015-91-3167	015-91-0160	015-91-6162	015-91-3166	015-91-3160	015-91-6163	015-91-3168		015-91-0168	015-91-5169	16											
18	22.86	.900	20.32	.800	015-91-2180		015-91-3187	015-91-0180		015-91-3186	015-91-3180		015-91-3188		015-91-0188	015-91-5189	18											
20	25.40	1.000	22.86	.900	015-91-2200	015-91-6200	015-91-3207	015-91-0200	015-91-6202	015-91-3206	015-91-3200	015-91-6203	015-91-3208		015-91-0208	015-91-5209	20											
22	27.94	1.100	25.40	1.000	015-91-2220		015-91-3227	015-91-0220		015-91-3226	015-91-3220		015-91-3228		015-91-0228	015-91-5229	22											
24	30.48	1.200	27.94	1.100	015-91-2240		015-91-3247	015-91-0240		015-91-3246	015-91-3240		015-91-3248		015-91-0248	015-91-5249	24											
26	33.02	1.300	30.48	1.200	015-91-2260	015-91-6260	015-91-3267	015-91-0260	015-91-6262	015-91-3266	015-91-3260		015-91-3268		015-91-0268	015-91-5269	26											
28	35.56	1.400	33.02	1.300	015-91-2280		015-91-3287	015-91-0280		015-91-3286	015-91-3280		015-91-3288		015-91-0288	015-91-5289	28											
30	38.10	1.500	35.56	1.400	015-91-2300		015-91-3307	015-91-0300		015-91-3306	015-91-3300		015-91-3308		015-91-0308	015-91-5309	30											
32	40.64	1.600	38.10	1.500	015-91-2320		015-91-3327	015-91-0320		015-91-3326	015-91-3320		015-91-3328		015-91-0328	015-91-5329	32											
34	43.18	1.700	40.64	1.600	015-91-2340		015-91-3347	015-91-0340		015-91-3346	015-91-3340		015-91-3348		015-91-0348	015-91-5349	34											
36	45.72	1.800	43.18	1.700	015-91-2360		015-91-3367	015-91-0360		015-91-3366	015-91-3360		015-91-3368		015-91-0368	015-91-5369	36											
38	48.26	1.900	45.72	1.800	015-91-2380		015-91-3387	015-91-0380		015-91-3386	015-91-3380		015-91-3388		015-91-0388	015-91-5389	38											
40	50.80	2.000	48.26	1.900	015-91-2400	015-91-6400	015-91-3407	015-91-0400	015-91-6402	015-91-3406	015-91-3400	015-91-6403	015-91-3408		015-91-0408	015-91-5409	40											
42	53.34	2.100	50.80	2.000	015-91-2420		015-91-3427	015-91-0420		015-91-3426	015-91-3420		015-91-3428		015-91-0428	015-91-5429	42											
44	55.88	2.200	53.34	2.100	015-91-2440		015-91-3447	015-91-0440		015-91-3446	015-91-3440		015-91-3448		015-91-0448	015-91-5449	44											
46	58.42	2.300	55.88	2.200	015-91-2460		015-91-3467	015-91-0460		015-91-3466	015-91-3460		015-91-3468		015-91-0468	015-91-5469	46											
48	60.96	2.400	58.42	2.300	015-91-2480		015-91-3487	015-91-0480		015-91-3486	015-91-3480		015-91-3488		015-91-0488	015-91-5489	48											
50	63.50	2.500	60.96	2.400	015-91-2500	015-91-6500	015-91-3507	015-91-0500	015-91-6502	015-91-3506	015-91-3500	015-91-6503	015-91-3508		015-91-0508	015-91-5509	50											
52	66.04	2.600	63.50	2.500	015-91-2520		015-91-3527	015-91-0520		015-91-3526	015-91-3520		015-91-3528		015-91-0528	015-91-5529	52											
54	68.58	2.700	66.04	2.600	015-91-2540		015-91-3547	015-91-0540		015-91-3546	015-91-3540		015-91-3548		015-91-0548	015-91-5549	54											
56	71.12	2.800	68.58	2.700	015-91-2560		015-91-3567	015-91-0560		015-91-3566	015-91-3560		015-91-3568		015-91-0568	015-91-5569	56											
58	73.66	2.900	71.12	2.800	015-91-2580		015-91-3587	015-91-0580		015-91-3586	015-91-3580		015-91-3588		015-91-0588	015-91-5589	58											
60	76.20	3.000	73.66	2.900	015-91-2600		015-91-3607	015-91-0600		015-91-3606	015-91-3600		015-91-3608		015-91-0608	015-91-5609	60											
62	78.74	3.100	76.20	3.000	015-91-2620		015-91-3627	015-91-0620		015-91-3626	015-91-3620		015-91-3628		015-91-0628	015-91-5629	62											
64	81.28	3.200	78.74	3.100	015-91-2640		015-91-3647	015-91-0640		015-91-3646	015-91-3640		015-91-3648		015-91-0648	015-91-5649	64											
66	83.82	3.300	81.28	3.200	015-91-2660		015-91-3667	015-91-0660		015-91-3666	015-91-3660		015-91-3668		015-91-0668	015-91-5669	66											
68	86.36	3.400	83.82	3.300	015-91-2680		015-91-3687	015-91-0680		015-91-3686	015-91-3680		015-91-3688		015-91-0688	015-91-5689	68											
70	88.90	3.500	86.36	3.400	015-91-2700		015-91-3707	015-91-0700		015-91-3706	015-91-3700		015-91-3708		015-91-0708	015-91-5709	70											
72	91.44	3.600	88.90	3.500	015-91-2720		015-91-3727	015-91-0720		015-91-3726	015-91-3720		015-91-3728		015-91-0728	015-91-5729	72											
74	93.98	3.700	91.44	3.600	015-91-2740		015-91-3747	015-91-0740		015-91-3746	015-91-3740		015-91-3748		015-91-0748	015-91-5749	74											
76	96.52	3.800	93.98	3.700	015-91-2760		015-91-3767	015-91-0760		015-91-3766	015-91-3760		015-91-3768		015-91-0768	015-91-5769	76											
78	99.06	3.900	96.52	3.800	015-91-2780		015-91-3787	015-91-0780		015-91-3786	015-91-3780		015-91-3788		015-91-0788	015-91-5789	78											
80	101.60	4.000	99.06	3.900	015-91-2800		015-91-3807	015-91-0800		015-91-3806	015-91-3800		015-91-3808		015-91-0808	015-91-5809	80											
82	104.14	4.100	101.60	4.000	71308-0082		71308-0482	71308-0182		71308-0582	71308-0282		71308-0682		71308-1182	71308-1282	82											
84	106.68	4.200	104.14	4.100	71308-0084		71308-0484	71308-0184		71308-0584	71308-0284		71308-0684		71308-1184	71308-1284	84											
86	109.22	4.300	106.68	4.200	71308-0086		71308-0486	71308-0186		71308-0586	71308-0286		71308-0686		71308-1186	71308-1286	86											
88	111.76	4.400	109.22	4.300	71308-0088		71308-0488	71308-0188		71308-0588	71308-0288		71308-0688		71308-1188	71308-1288	88											
90	114.30	4.500	111.76	4.400	71308-0090		713																					

13		12		11				10		8		7		6		5		4		3		2		1	
J		IN TAPE AND REEL WITH SHALLOW POCKET TAPE												BULK / IN TUBES										J	
		PACKAGING SEE NOTE 4. SHT 1		4-8 CKT		TAPE-N-REEL W/ VAC CAPS		TAPE-N-REEL W/ VAC CAPS										BULK		BULK					
				10-100 CKT		TAPE-N-REEL W/ VAC CAPS		TAPE-N-REEL W/ VAC CAPS										TUBES		TUBES					
		DIM. M±0.25 MM				6.10 (.240)		6.10 (.240)										8.13 (.320)		13.59 (.535)					
		PLATING				30 GOLD		15 GOLD										150 TIN		150 TIN					
		DIM. H				2.54 (.100)		2.54 (.100)										4.57 (.180)		4.57 (.180)					
I		CKTS		DIM. A		DIM. B		EDP NUMBER		EDP NUMBER								EDP NUMBER		EDP NUMBER		CKTS			
				MM	IN	MM	IN																		
		04	5.08	.200	2.54	.100																	04		
		06	7.62	.300	5.08	.200			015-91-6068														06		
		08	10.16	.400	7.62	.300			015-91-6088														08		
		10	12.70	.500	10.16	.400			015-91-6108								713088010		71308-8210				10		
		12	15.24	.600	12.70	.500																	12		
H		14	17.78	.700	15.24	.600	015-91-6148																14		
		16	20.32	.800	17.78	.700											713088016						16		
		18	22.86	.900	20.32	.800																	18		
		20	25.40	1.000	22.86	.900																	20		
		22	27.94	1.100	25.40	1.000																	22		
		24	30.48	1.200	27.94	1.100																	24		
		26	33.02	1.300	30.48	1.200																	26		
G		28	35.56	1.400	33.02	1.300																	28		
		30	38.10	1.500	35.56	1.400																	30		
		32	40.64	1.600	38.10	1.500																	32		
		34	43.18	1.700	40.64	1.600																	34		
		36	45.72	1.800	43.18	1.700																	36		
		38	48.26	1.900	45.72	1.800																	38		
		40	50.80	2.000	48.26	1.900																	40		
F		42	53.34	2.100	50.80	2.000																	42		
		44	55.88	2.200	53.34	2.100																	44		
		46	58.42	2.300	55.88	2.200																	46		
		48	60.96	2.400	58.42	2.300																	48		
		50	63.50	2.500	60.96	2.400																	50		
		52	66.04	2.600	63.50	2.500																	52		
		54	68.58	2.700	66.04	2.600																	54		
		56	71.12	2.800	68.58	2.700																	56		
E		58	73.66	2.900	71.12	2.800																	58		
		60	76.20	3.000	73.66	2.900																	60		
		62	78.74	3.100	76.20	3.000																	62		
		64	81.28	3.200	78.74	3.100																	64		
		66	83.82	3.300	81.28	3.200																	66		
		68	86.36	3.400	83.82	3.300																	68		
		70	88.90	3.500	86.36	3.400																	70		
D		72	91.44	3.600	88.90	3.500																	72		
		74	93.98	3.700	91.44	3.600																	74		
		76	96.52	3.800	93.98	3.700																	76		
		78	99.06	3.900	96.52	3.800																	78		
		80	101.60	4.000	99.06	3.900																	80		
		82	104.14	4.100	101.60	4.000																	82		
		84	106.68	4.200	104.14	4.100																	84		
C		86	109.22	4.300	106.68	4.200																	86		
		88	111.76	4.400	109.22	4.300																	88		
		90	114.30	4.500	111.76	4.400																	90		
		92	116.84	4.600	114.30	4.500																	92		
		94	119.38	4.700	116.84	4.600																	94		
		96	121.92	4.800	119.38	4.700																	96		
		98	124.46	4.900	121.92	4.800																	98		
		100	127.00	5.000	124.46	4.900																	100		
B		NO PEG VERSION										SEE SHEET 1 EC NO: UCP2014-0809 DRAWN:KIPPER 2013/08/20 CHKD:JBELL 2013/08/20 APPR:FSMITH 2013/09/03		QUALITY SYMBOLS ▽=0 ▽=0 ▽=0		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM/IN		SCALE		DESIGN UNITS INCH		THIRD ANGLE PROJECTION	
																mm		INCH		DRAWN BY DATE KMS 1999/10/15		TITLE SALES ASSY INSULATOR DUAL ROW SMT W/BREAK-OFF .025SQ PIN GULLWING .100			
A		(ALSO SEE SHEET 2)										K5		REV		ANGULAR ±1/2° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE C		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		DOCUMENT NO. SD-71308-001		SHEET NO. 3 OF 6	
1b_frame_C_P_AM.T Rev. G 2012/01/11		12		11		10		9		8		7		6		5		4		3		2		1	

13			12		11		10		9		8		7		6		5		4		3		2		1					
			PACKAGING SEE NOTE 4 SHT 1				4-8 CKT		BULK		TAPE-N-REEL W/ VAC CAPS		BULK		TAPE-N-REEL W/ VAC CAPS		BULK		TAPE-N-REEL W/ VAC CAPS		BULK		BULK		BULK					
							10-100 CKT		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES		TAPE-N-REEL W/ VAC CAPS		TUBES		TUBES		TUBES					
							DIM. M±0.25 MM				6.10 (.240)				6.10 (.240)				6.10 (.240)				8.13 (.320)		8.13 (.320)				8.13 (.320)	
							PLATING				150 TIN				15 GOLD				30 GOLD				150 TIN		15 GOLD				30 GOLD	
							DIM. H				2.54 (.100)				2.54 (.100)				2.54 (.100)				4.57 (.180)		4.57 (.180)				4.57 (.180)	
CKTS	DIM. A		DIM. B		DIM. C		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		CKTS			
	MM	IN	MM	IN	MM	IN																								
04	5.08	.200	2.54	.100	----	----	015-91-1041	015-91-6044	015-91-1042	015-91-6045	015-91-1043	015-91-6046	015-91-1044	015-91-0047	015-91-1040										04					
06	7.62	.300	5.08	.200	2.54	.100	015-91-1061	015-91-6064	015-91-1062	015-91-6065	015-91-1063	015-91-6066	015-91-1064	015-91-0067	015-91-1060										06					
08	10.16	.400	7.62	.300	5.08	.200	015-91-1081	015-91-6084	015-91-1082	015-91-6085	015-91-1083	015-91-6086	015-91-1084	015-91-0087	015-91-1080										08					
10	12.70	.500	10.16	.400	7.62	.300	015-91-1101	015-91-6104	015-91-1102	015-91-6105	015-91-1103	015-91-6106	015-91-1104	015-91-0107	015-91-1100										10					
12	15.24	.600	12.70	.500	10.16	.400	015-91-1121		015-91-1122		015-91-1123		015-91-1124	015-91-0127	015-91-1120										12					
14	17.78	.700	15.24	.600	12.70	.500	015-91-1141	015-91-6144	015-91-1142	015-91-6145	015-91-1143	015-91-6146	015-91-1144	015-91-0147	015-91-1140										14					
16	20.32	.800	17.78	.700	15.24	.600	015-91-1161	015-91-6164	015-91-1162	015-91-6165	015-91-1163	015-91-6166	015-91-1164	015-91-0167	015-91-1160										16					
18	22.86	.900	20.32	.800	17.78	.700	015-91-1181		015-91-1182		015-91-1183		015-91-1184	015-91-0187	015-91-1180										18					
20	25.40	1.000	22.86	.900	20.32	.800	015-91-1201		015-91-1202		015-91-1203		015-91-1204	015-91-0207	015-91-1200										20					
22	27.94	1.100	25.40	1.000	22.86	.900	015-91-1221		015-91-1222		015-91-1223		015-91-1224	015-91-0227	015-91-1220										22					
24	30.48	1.200	27.94	1.100	25.40	1.000	015-91-1241	71308-6901	015-91-1242		015-91-1243		015-91-1244	015-91-0247	015-91-1240										24					
26	33.02	1.300	30.48	1.200	27.94	1.100	015-91-1261		015-91-1262		015-91-1263		015-91-1264	015-91-0267	015-91-1260										26					
28	35.56	1.400	33.02	1.300	30.48	1.200	015-91-1281		015-91-1282		015-91-1283		015-91-1284	015-91-0287	015-91-1280										28					
30	38.10	1.500	35.56	1.400	33.02	1.300	015-91-1301		015-91-1302		015-91-1303		015-91-1304	015-91-0307	015-91-1300										30					
32	40.64	1.600	38.10	1.500	35.56	1.400	015-91-1321		015-91-1322		015-91-1323		015-91-1324	015-91-0327	015-91-1320										32					
34	43.18	1.700	40.64	1.600	38.10	1.500	015-91-1341		015-91-1342		015-91-1343		015-91-1344	015-91-0347	015-91-1340										34					
36	45.72	1.800	43.18	1.700	40.64	1.600	015-91-1361		015-91-1362		015-91-1363		015-91-1364	015-91-0367	015-91-1360										36					
38	48.26	1.900	45.72	1.800	43.18	1.700	015-91-1381		015-91-1382		015-91-1383		015-91-1384	015-91-0387	015-91-1380										38					
40	50.80	2.000	48.26	1.900	45.72	1.800	015-91-1401		015-91-1402		015-91-1403		015-91-1404	015-91-0407	015-91-1400										40					
42	53.34	2.100	50.80	2.000	48.26	1.900	015-91-1421		015-91-1422		015-91-1423		015-91-1424	015-91-0427	015-91-1420										42					
44	55.88	2.200	53.34	2.100	50.80	2.000	015-91-1441		015-91-1442		015-91-1443		015-91-1444	015-91-0447	015-91-1440										44					
46	58.42	2.300	55.88	2.200	53.34	2.100	015-91-1461		015-91-1462		015-91-1463		015-91-1464	015-91-0467	015-91-1460										46					
48	60.96	2.400	58.42	2.300	55.88	2.200	015-91-1481		015-91-1482		015-91-1483		015-91-1484	015-91-0487	015-91-1480										48					
50	63.50	2.500	60.96	2.400	58.42	2.300	015-91-1501	015-91-6504	015-91-1502	015-91-6505	015-91-1503	015-91-6506	015-91-1504	015-91-0507	015-91-1500										50					
52	66.04	2.600	63.50	2.500	60.96	2.400	015-91-1521		015-91-1522		015-91-1523	71308-5203	015-91-1524	015-91-0527	015-91-1520										52					
54	68.58	2.700	66.04	2.600	63.50	2.500	015-91-1541		015-91-1542		015-91-1543		015-91-1544	015-91-0547	015-91-1540										54					
56	71.12	2.800	68.58	2.700	66.04	2.600	015-91-1561		015-91-1562		015-91-1563		015-91-1564	015-91-0567	015-91-1560										56					
58	73.66	2.900	71.12	2.800	68.58	2.700	015-91-1581		015-91-1582		015-91-1583		015-91-1584	015-91-0587	015-91-1580										58					
60	76.20	3.000	73.66	2.900	71.12	2.800	015-91-1601		015-91-1602		015-91-1603		015-91-1604	015-91-0607	015-91-1600										60					
62	78.74	3.100	76.20	3.000	73.66	2.900	015-91-1621		015-91-1622		015-91-1623		015-91-1624	015-91-0627	015-91-1620										62					
64	81.28	3.200	78.74	3.100	76.20	3.000	015-91-1641		015-91-1642		015-91-1643		015-91-1644	015-91-0647	015-91-1640										64					
66	83.82	3.300	81.28	3.200	78.74	3.100	015-91-1661		015-91-1662		015-91-1663		015-91-1664	015-91-0667	015-91-1660										66					
68	86.36	3.400	83.82	3.300	81.28	3.200	015-91-1681		015-91-1682		015-91-1683		015-91-1684	015-91-0687	015-91-1680										68					
70	88.90	3.500	86.36	3.400	83.82	3.300	015-91-1701		015-91-1702		015-91-1703		015-91-1704	015-91-0707	015-91-1700										70					
72	91.44	3.600	88.90	3.500	86.36	3.400	015-91-1721		015-91-1722		015-91-1723		015-91-1724	015-91-0727	015-91-1720										72					
74	93.98	3.700	91.44	3.600	88.90	3.500	015-91-1741		015-91-1742		015-91-1743		015-91-1744	015-91-0747	015-91-1740										74					
76	96.52	3.800	93.98	3.700	91.44	3.600	015-91-1761		015-91-1762		015-91-1763		015-91-1764	015-91-0767	015-91-1760										76					
78	99.06	3.900	96.52	3.800	93.98	3.700	015-91-1781		015-91-1782		015-91-1783		015-91-1784	015-91-0787	015-91-1780										78					
80	101.60	4.000	99.06	3.900	96.52	3.800	015-91-1801		015-91-1802		015-91-1803		015-91-1804	015-91-0807	015-91-1800										80					
82	104.14	4.100	101.60	4.000	99.06	3.900	71308-4082		71308-4182		71308-4282		71308-5082	71308-5182	71308-5282										82					
84	106.68	4.200	104.14	4.100	101.60	4.000	71308-4084		71308-4184		71308-4284		71308-5084	71308-5184	71308-5284										84					
86	109.22	4.300	106.68	4.200	104.14	4.100	71308-4086		71308-4186		71308-4286		71308-5086	71308-5186	71308-5286										86					
88	111.76	4.400	109.22	4.300	106.68	4.200	71308-4088		71308-4188		71308-4288		71308-5088	71308-5188	71308-5288										88					
90	114.30	4.500	111.76	4.400	109.22	4.300	71308-4090		71308-4190		71308-4290		71308-5090	71308-5190	71308-5290										90					
92	116.84	4.600	114.30	4.500	111.76	4.400	71308-4092		71308-4192		71308-4292		71308-5092	71308-5192	71308-5292										92					
94	119.38	4.700	116.84	4.600	114.30	4.500	71308-4094		71308-4194		71308-4294		71308-5094	71308-5194	71308-5294															

		13		12		11		10		9		8		7		6		5		4		3		2		1																	
J		PEG OPTION																										J															
		NO PEG VERSION														NO PEG VERSION				LONG PEG VERSION (.130")				SHORT PEG VERSION (.055")																			
		PACKAGING SEE NOTE 4, SHT 1		4-6 CKT		BULK		TAPE-N-REEL W/VAC CAPS		N/A				4-8 CKT		TAPE-N-REEL W/VAC CAPS		BULK		BULK		BULK		TAPE-N-REEL W/VAC CAPS		BULK				BULK		TAPE-N-REEL W/ VAC CAPS											
				8-100 CKT		TUBES		TAPE-N-REEL W/VAC CAPS		TUBES W/ VAC CAPS				10-100 CKT		TAPE-N-REEL W/VAC CAPS		TUBES		TUBES		TUBES		TAPE-N-REEL W/VAC CAPS		TUBES				BULK		TAPE-N-REEL W/ VAC CAPS											
		DIM. M±0.25 MM										6.10 (.240)														8.13(.320)				13.59(.535)				6.10(.240)				8.13(.320)				6.10 (.240)	
I		PLATING										59 TIN														59 TIN				59 TIN				59 TIN				59 TIN					
		DIM. H										2.54(.100)														4.57(.180)				4.57(.180)				2.54(.100)				2.54(.100)					
KCTS		DIM. A		DIM. B		DIM. C		EDP NUMBER		EDP NUMBER		EDP NUMBER				EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		EDP NUMBER		KCTS											
		MM	IN	MM	IN	MM	IN																																				
H		04	5.08	.200	2.54	.100	---	---	71308-5404	71308-5504	N/A											71308-6404	71308-6504	71308-6604			71308-6706	71308-6806			04												
		06	7.62	.300	5.08	.200	2.54	.100	71308-5406	71308-5506	N/A											71308-6406	71308-6506	71308-6606	71308-6706	71308-6806			06														
		08	10.16	.400	7.62	.300	5.08	.200	71308-5408	71308-5508	71308-5608											71308-6408	71308-6508	71308-6608	71308-6708	71308-6808			08														
		10	12.70	.500	10.16	.400	7.62	.300	71308-5410	71308-5510	71308-5610			71308-5810	71308-5910					71308-6410	71308-6510	71308-6610	71308-6710	71308-6810			10																
		12	15.24	.600	12.70	.500	10.16	.400	71308-5412	71308-5512	71308-5612									71308-6412			71308-6612					12															
		14	17.78	.700	15.24	.600	12.70	.500	71308-5414	71308-5514	71308-5614									71308-6414	71308-6514	71308-6614					14																
		16	20.32	.800	17.78	.700	15.24	.600	71308-5416	71308-5516	71308-5616			71308-5816					71308-6416	71308-6516	71308-6616					16																	
		18	22.86	.900	20.32	.800	17.78	.700	71308-5418			71308-5618							71308-6418			71308-6618					18																
		20	25.40	1.000	22.86	.900	20.32	.800	71308-5420	71308-5520	71308-5620									71308-6420			71308-6620					20															
		22	27.94	1.100	25.40	1.000	22.86	.900	71308-5422			71308-5622							71308-6422			71308-6622					22																
G		24	30.48	1.200	27.94	1.100	25.40	1.000	71308-5424			71308-5624	71308-5724		71308-5824			71308-6424			71308-6624					24																	
		26	33.02	1.300	30.48	1.200	27.94	1.100	71308-5426			71308-5626							71308-6426			71308-6626	71308-6726			26																	
		28	35.56	1.400	33.02	1.300	30.48	1.200	71308-5428			71308-5628							71308-6428			71308-6628					28																
		30	38.10	1.500	35.56	1.400	33.02	1.300	71308-5430			71308-5630							71308-6430			71308-6630					30																
		32	40.64	1.600	38.10	1.500	35.56	1.400	71308-5432			71308-5632							71308-6432			71308-6632					32																
		34	43.18	1.700	40.64	1.600	38.10	1.500	71308-5434			71308-5634							71308-6434			71308-6634					34																
		36	45.72	1.800	43.18	1.700	40.64	1.600	71308-5436			71308-5636							71308-6436			71308-6636					36																
		38	48.26	1.900	45.72	1.800	43.18	1.700	71308-5438			71308-5638							71308-6438			71308-6638					38																
		40	50.80	2.000	48.26	1.900	45.72	1.800	71308-5440	71308-5540	71308-5640									71308-6440			71308-6640					40															
		42	53.34	2.100	50.80	2.000	48.26	1.900	71308-5442			71308-5642							71308-6442			71308-6642					42																
F		44	55.88	2.200	53.34	2.100	50.80	2.000	71308-5444			71308-5644							71308-6444			71308-6644					44																
		46	58.42	2.300	55.88	2.200	53.34	2.100	71308-5446			71308-5646							71308-6446			71308-6646					46																
		48	60.96	2.400	58.42	2.300	55.88	2.200	71308-5448			71308-5648							71308-6448			71308-6648					48																
		50	63.50	2.500	60.96	2.400	58.42	2.300	71308-5450	71308-5550	71308-5650							71308-6450	71308-6550	71308-6650					50																		
		52	66.04	2.600	63.50	2.500	60.96	2.400	71308-5452			71308-5652							71308-6452			71308-6652					52																
		54	68.58	2.700	66.04	2.600	63.50	2.500	71308-5454			71308-5654							71308-6454			71308-6654					54																
		56	71.12	2.800	68.58	2.700	66.04	2.600	71308-5456			71308-5656							71308-6456			71308-6656					56																
		58	73.66	2.900	71.12	2.800	68.58	2.700	71308-5458			71308-5658							71308-6458			71308-6658					58																
		60	76.20	3.000	73.66	2.900	71.12	2.800	71308-5460			71308-5660							71308-6460			71308-6660					60																
		62	78.74	3.100	76.20	3.000	73.66	2.900	71308-5462			71308-5662							71308-6462			71308-6662					62																
D		64	81.28	3.200	78.74	3.100	76.20	3.000	71308-5464			71308-5664							71308-6464			71308-6664					64																
		66	83.82	3.300	81.28	3.200	78.74	3.100	71308-5466			71308-5666							71308-6466			71308-6666					66																
		68	86.36	3.400	83.82	3.300	81.28	3.200	71308-5468			71308-5668							71308-6468			71308-6668					68																
		70	88.90	3.500	86.36	3.400	83.82	3.300	71308-5470			71308-5670							71308-6470			71308-6670					70																
		72	91.44	3.600	88.90	3.500	86.36	3.400	71308-5472			71308-5672							71308-6472			71308-6672					72																
		74	93.98	3.700	91.44	3.600	88.90	3.500	71308-5474			71308-5674							71308-6474			71308-6674					74																
		76	96.52	3.800	93.98	3.700	91.44	3.600	71308-5476			71308-5676							71308-6476			71308-6676					76																
		78	99.06	3.900	96.52	3.800	93.98	3.700	71308-5478			71308-5678							71308-6478			71308-6678					78																
		80	101.60	4.000	99.06	3.900	96.52	3.800	71308-5480			71308-5680							71308-6480			71308-6680					80																
		82	104.14	4.100	101.60	4.000	99.06	3.900	71308-5482			71308-5682							71308-6482			71308-6682					82																
C		84	106.68	4.200	104.14	4.100	101.60	4.000	71308-5484			71308-5684							71308-6484			71308-6684					84																
		86	109.22	4.300	106.68	4.200	104.14	4.100	71308-5486			71308-5686							71308-6486			71308-6686					86																
		88	111.76	4.400	109.22	4.300	106.68	4.200	71308-5488			71308-5688							71308-6488			71308-6688					88																
		90	114.30	4.500	111.76	4.400	109.22	4.300	71308-5490			71308-5690							71308-6490			71308-6690					90																
		92	116.84	4.600	114.30	4.500	111.76	4.400	71308-5492			71308-5692							71308-6492			71308-6692					92																
		94	119.38	4.700	116.84	4.600	114.30	4.500	71308-5494			71308-5694							71308-6494			71308-6694					94																
		96	121.92	4.800	119.38	4.700	116.84	4.600	71308-5496			71308-5696							71308-6496			71308-6696					96																
		98	124.46	4.900	121.92	4.800	119.38	4.700	71308-5498			71308-5698							71308-6498			71308-6698					98																
		100	127.00	5.000	124.46	4.900	121.92	4.800	71308-5500			71308-5700							71308-6500			71308-6700					100																
		B		59 TIN PLATE ASSEMBLIES										SEE SHEET 1 EC NO: UCP2014-0809 DRWN:MKIPPER 2013/08/20 CHKD:JBELL 2013/08/20 APPR:FSMITH 2013/09/03		QUALITY SYMBOLS ▽=0 ▽=0 ▽=0		GENERAL TOLERANCES (UNLESS SPECIFIED)				DIMENSION STYLE MM/IN				SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION													
mm																		INCH		DRAWN BY		DATE		TITLE																			
4 PLACES ± ---																		± ---		KMS		1999/10/15		SALES ASSY INSULATOR																			
3 PLACES ± ---																		± .005		CHECKED BY		DATE		DUAL ROW SMT W/BREAK-OFF																			
2 PLACES ± 0.13																		± .010		KMS		1999/10/15		.025SQ PIN GULLWING .100																			
A		REV		K5		DESCRIPTION		ANGULAR ±1/2°		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO. SEE TABLE		DOCUMENT NO. SD-71308-001		SHEET NO. 6 OF 6		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																									
		12		11		10		9		8		7		6		5		4		3		2		1																			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

15-91-1508