

Release-type torque drivers

Micro-Tech® tool set

▷ ISO 6789.

- Case-set includes bits and adjusting key.
- Supplied with inspection report.



	Capacity	Screwdriver	Adjusting key	Contents			Dimensions mm	ΔΔ g
	N.m			Bits⊖	Bits⊕	Bits○		
A.300MTJ1	4-20	A.300MT	82.4	1,8 - 2,5 mm	0,9 - 1,3 - 1,5 - 2 mm	PZ 0 - 1 - 2 mm	185X109X40	300
A.301MTJ1	15-75	A.301MT	82.4	4 - 4,5 - 5,5 mm	1,5 - 2,5 - 3 mm	PZ 0 - 1 mm	185x109x40	370

Driver bit set $\square$ 1/4"

▷ Exceeds ISO 6789 requirements.

- Class II type D (A.400 maintenance).
- One-way drivers, clockwise operation.
- Hexagon socket drive for $\square$ 1/4".
- Drive $\square$ 1/4" on the handle for ratchet handle A.300PA.
- Supplied with inspection report, adjusting key and individual identification number.
- Case BP.102 and tray PL.436.



	Screwdriver	Bit holder	Handle	Contents Adjusting key	Contents		
					Bits⊖	Bits○	Bits⊕
A.402J2	A.402	EF.1P4	A.300PA	A.402-20	4,5 - 6,5 - 8 mm	3 - 4 - 5 mm	PZ 1 - 2 - 3 mm
A.404J2	A.404	EF.1PA	A.300PA	A.404-20	4,5 - 6,5 - 8 mm	3 - 4 - 5 mm	PZ 1 - 2 - 3 mm

Socket set $\square$ 1/4"

▷ Exceeds ISO 6789 requirements.

- Class II type D (A.400 maintenance).
- One-way drivers, clockwise operation.
- Hexagon socket drive for $\square$ 1/4".
- ECR $\square$ 1/4" - $\square$ 1/4" adaptor for sockets and accessories.
- Drive $\square$ 1/4" on the handle for ratchet handle A.300PA.
- Supplied with inspection report, adjusting key and individual identification number.
- Supplied with adaptor ECR, extensions R.210 and R.215.
- Case BP.115 and tray PL.434.



	Screwdriver	Contents Handle	Adjusting key	Socket
A.402J1	A.402	A.300PA	A402-20	R.3,2-4-5-5,5-6-7-8-9-10 mm
A.404J1	A.404	A.300PA	A404-20	R.3,2-4-5-5,5-6-7-8-9-10 mm