


CUSTOMER INFORMATION SHEET



MAX. PIN LENGTH = 7.0

$L = (2.54 \times \text{No. OF PITCHES}) + 2.48 \text{ MAX}$
E.G. 12 + 12 WAYS = 30.42 MAX
15 + 15 WAYS = 38.04 MAX

MOULDING:
MATERIAL = GLASS-FILLED
POLYESTER UL94V-0

SOCKETS:
MATERIAL = PHOSPHOR BRONZE
FINISH =
06 - 90/10 TIN/LEAD
22 - GOLD OVER NICKEL ON CONTACT FACE,
90/10 TIN/LEAD ON P.C. TAILS
27 - 0.8µ GOLD OVER NICKEL ON CONTACT FACE,
90/10 TIN/LEAD ON P.C. TAILS

ORDER CODE M20-989XXXX

No. OF WAYS PER ROW
02 TO 36
(I.E. 2+2 TO 36+36)

FINISH:
06 = TIN/LEAD
22 = SELECTIVE GOLD/TIN-LEAD
27 = 0.8µ SELECTIVE GOLD/TIN-LEAD

17	17.11.95	3104
5	26.09.95	3049
4	13.07.93	2334
3	17.03.93	2223
2	02.10.90	----
1	01.08.89	----
ISS.	DATE	C/N
APPROVED:		
CHECKED:		
DRAWN:	V. BOURNE	
CUSTOMER REF.		
ASSEMBLY DRG:		



HARWIN INC U.S.A. TEL: (812) 285 0055 FAX: (812) 285 0056	HARWIN PLC U.K. TEL: (01705) 370451 FAX: (01705) 324010	HARWIN PTE SINGAPORE TEL: 7794909 FAX: 7793868
--	--	---

TOLERANCES X. = ±1mm X.X = ±0.25mm X.XX = ±0.10mm X.XXX = ±0.01mm ANGLES = ±1° UNLESS STATED	MATERIAL: SEE ABOVE FINISH: SEE ABOVE S/AREA: mm²	TITLE: P.C. SOCKET ASSEMBLY (DOUBLE ROW - HORIZONTAL) DRAWING NUMBER: M20-988XXXX	SHT 2 OF 2
--	--	---	---------------------