

# EMI Suppression Filters (EMIFIL®) for AC Power Lines



**muRata**

*Innovator  
in Electronics*

Murata  
Manufacturing Co., Ltd.

Cat.No.C09E-9

# CONTENTS

EMIFIL® in this catalog is the trademark of Murata Manufacturing Co., Ltd.

|                                                                       |    |
|-----------------------------------------------------------------------|----|
| <b>Part Numbering</b>                                                 | 2  |
| <b>Outline of EMI Suppression Filter (EMIFIL®) for AC Power Lines</b> | 3  |
| <b>1 Common Mode Choke Coil</b>                                       | 5  |
| FKOB Series                                                           | 5  |
| PLA10 Series Standard Winding Type                                    | 6  |
| PLA10 Series Sectional Winding Type                                   | 6  |
| PLA10 Series (Safety Standard Recognized) Standard Winding Type       | 8  |
| PLA10 Series (Safety Standard Recognized) Sectional Winding Type      | 8  |
| PLH10 Series                                                          | 10 |
| PLH10 Series (Safety Standard Recognized)                             | 11 |
| <b>2 Hybrid Choke Coil</b>                                            | 12 |
| PLY10 Series Standard Winding Type                                    | 12 |
| PLY10 Series Sectional Winding Type                                   | 13 |
| PLY17 Series A Type                                                   | 14 |
| PLY17 Series B Type                                                   | 14 |
| ● Noise Suppression Effect of PLY10 Series                            | 16 |
| <b>⚠Caution /Notice</b>                                               | 17 |
| <b>Packaging</b>                                                      | 18 |

## ● Part Numbering

### AC Line Filters

(Part Number)

|    |   |    |   |   |     |     |   |   |   |
|----|---|----|---|---|-----|-----|---|---|---|
| PL | A | 10 | A | S | 152 | 2R0 | R | 2 | B |
| ①  | ② | ③  | ④ | ⑤ | ⑥   | ⑦   | ⑧ | ⑨ | ⑩ |

#### ① Product ID

| Product ID |                         |
|------------|-------------------------|
| PL         | Common Mode Choke Coils |

#### ② Type

| Code | Type                       |
|------|----------------------------|
| A    | AC Standard Type           |
| H    | AC High-frequency Type     |
| Y    | AC Hybrid Choke Coils Type |

#### ③ Applications

| Code | Applications |
|------|--------------|
| 10   | for AC Line  |
| 17   |              |

#### ④ Structure

| Code | Structure            |
|------|----------------------|
| A    | Core Vertical Type   |
| B    | Core Horizontal Type |

#### ⑤ Features

| Code | Features          |
|------|-------------------|
| S    | Safety Recognized |
| N    | General Use       |

#### ⑩ Packaging

| Code | Packaging        | Series     |
|------|------------------|------------|
| B    | Bulk             | All series |
| M    | Magazine Package |            |

- Please contact us for **FKOB** series.

#### ⑥ Inductance

Expressed by three figures. The unit is micro-henry ( $\mu\text{H}$ ). The first and second figures are significant digits, and the third figure expresses the number of zeros which follow the two figures. If there is a decimal point, it is expressed by the capital letter "R". In this case, all figures are significant digits. If inductance is less than  $0.1 \mu\text{H}$ , the inductance code is expressed by a combination of two figures and capital letter "N", and the unit of inductance is nano-henry (nH). The capital letter "N" indicates the unit of "nH", and also expresses a decimal point. In this case, all figures are significant digits.

#### ⑦ Rated Current

Expressed by three figures. The unit is in amperes (A). A decimal point is expressed by the capital letter "R". In this case, all figures are significant digits.

#### ⑧ Winding Mode

| Code | Winding Mode                                  |
|------|-----------------------------------------------|
| A    | Parallel Winding Type                         |
| B    | Parallel Winding Type (High Performance Type) |
| D    | Sectional Winding Type                        |
| R    | Standard Type                                 |
| P    | Single Layer Winding Type                     |

#### ⑨ Lead Dimensions

| Code | Lead Dimensions |
|------|-----------------|
| 2    | 3.5mm           |

## Outline of EMI Suppression Filter (EMIFIL®) for AC Power Lines




EMI (Electro Magnetic Interference) suppression filter for AC power lines eliminate noise entering equipment from commercial power lines or noise generated from electronic equipment.

Common mode chokes, line bypass capacitors, across the line capacitors are generally used as AC EMI suppression filter device. In suppressing common mode noise, common mode chokes are most important devices. Because the characteristics of common mode chokes influences

performance of total filter block MURATA provides two types of common mode chokes. (Standard type, High frequency type)

Hybrid choke coil is high performance EMI suppression device which can suppress both common mode noise and differential mode noise at the same time. It is effective in AC power supplies with active device for higher harmonic countermeasure, which tend to emit relatively higher differential mode noise.


### ■ Classification of EMI Suppression Filter for AC Power Lines

| Product Name                                                                                                 | Appearance                                                                                                                                                                                                             | Effective Frequency Range (Hz) |      |    |     |      |    | Application                                                                                                                                                                                                      |
|--------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------|------|----|-----|------|----|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|                                                                                                              |                                                                                                                                                                                                                        | 10k                            | 100k | 1M | 10M | 100M | 1G |                                                                                                                                                                                                                  |
| Common Mode Choke Coil<br> | Standard Type<br><br><b>PLA10</b><br><br><b>FKOB</b> |                                |      |    |     |      |    | Suppression of general common mode noise                                                                                                                                                                         |
|                                                                                                              | High Frequency Type<br><br><b>PLH10</b>                                                                                             |                                |      |    |     |      |    | Suppression of common mode noise contains high frequency noise above 10MHz                                                                                                                                       |
| Hybrid Choke Coil<br>     | <br><b>PLY10</b>                                                                                                                    |                                |      |    |     |      |    | Suppression of conduction noise in AC power line with active device for higher harmonic countermeasure.<br>Suppression of AC power line noise which contains both common mode noise and differential mode noise. |
| Hybrid Choke Coil<br>     | <br><b>PLY17</b>                                                                                                                    |                                |      |    |     |      |    | For AC power supply, AC adaptor.<br>Set for low profile equipment.                                                                                                                                               |

## Outline of EMI Suppression Filter (EMIFIL<sup>®</sup>) for AC Power Lines

### Common Mode Choke Coil Standard Winding and Sectional Winding

#### Standard Winding



High-frequency noise can pass through the Filter easily because both edges of coils are close as shown above


#### Standard Winding

Large inductance is available  
→ Highly Efficient in Low Frequency


#### Sectional Winding

Excellent performance in high frequency  
Stray capacity between windings is low



#### Sectional Winding



High-frequency noise can hardly pass through the Filter because both edges of coil are not close as shown above



### Noise Measures for Switching Power Supply



# EMI Suppression Filters (EMIFIL®) for AC Power Lines

**muRata**



1

## Common Mode Choke Coil

### FKOB Series

The FKOB series is compact size AC common mode choke coil which uses troidal type ferrite core.


Its broad band frequency characteristic enables simple filter composition in relative low noise equipments.




| Part Number | Common Mode Inductance<br>(min.)<br>(μH) | Rated Current<br>(A) | Rated Voltage<br>(V) | Insulation Resistance<br>(min.)<br>(M ohm) |
|-------------|------------------------------------------|----------------------|----------------------|--------------------------------------------|
| FKOB160MH02 | 250                                      | 2.5                  | 250                  | 100                                        |
| FKOB160MH06 | 250                                      | 2.5                  | 250                  | 100                                        |
| FKOB160MH13 | 600                                      | 2.5                  | 250                  | 100                                        |
| FKOB160MH25 | 600                                      | 2.5                  | 250                  | 100                                        |
| FKOB160MH14 | 800                                      | 2.5                  | 250                  | 100                                        |
| FKOB160MH23 | 800                                      | 2.5                  | 250                  | 100                                        |
| FKOB160MH16 | 1000                                     | 1.5                  | 250                  | 100                                        |
| FKOB160MH26 | 1000                                     | 1.5                  | 250                  | 100                                        |
| FKOB160MH15 | 1500                                     | 1.5                  | 250                  | 100                                        |
| FKOB160MH24 | 1500                                     | 1.5                  | 250                  | 100                                        |

Operating Temperature Range (Ambient Temperature Range + Winding Temperature Rise): -20°C to 95°C Winding Temperature Rise (at Rated Current) (max.): 35K

### Equivalent Circuit Diagram



### Insertion Loss-Frequency Characteristics




## PLA10 Series Standard Winding Type

The PLA10 series is a compact size AC common mode choke coil. It can obtain a high inductance value in spite of its compact size.

### ■ Features


1. Compact and light weight
2. Low profile in vertical core layout
3. Both a standard winding type and a sectional winding type for higher frequency noise are available.



| Part Number     | Common Mode Inductance<br>(min.)<br>(mH) | Rated Current<br>(A) | Rated Voltage<br>(V) | Insulation Resistance<br>(min.)<br>(M ohm) |
|-----------------|------------------------------------------|----------------------|----------------------|--------------------------------------------|
| PLA10AN1522R0R2 | 1.5                                      | 2.0                  | 300                  | 100                                        |
| PLA10AN1821R7R2 | 1.8                                      | 1.7                  | 300                  | 100                                        |
| PLA10AN2221R5R2 | 2.2                                      | 1.5                  | 300                  | 100                                        |
| PLA10AN3021R3R2 | 3.0                                      | 1.3                  | 300                  | 100                                        |
| PLA10AN3521R2R2 | 3.5                                      | 1.2                  | 300                  | 100                                        |
| PLA10AN5521R0R2 | 5.5                                      | 1.0                  | 300                  | 100                                        |
| PLA10AN7420R8R2 | 7.4                                      | 0.8                  | 300                  | 100                                        |
| PLA10AN1030R7R2 | 10.0                                     | 0.7                  | 300                  | 100                                        |
| PLA10AN1230R6R2 | 12.0                                     | 0.6                  | 300                  | 100                                        |
| PLA10AN2030R5R2 | 20.0                                     | 0.5                  | 300                  | 100                                        |
| PLA10AN3030R4R2 | 30.0                                     | 0.4                  | 300                  | 100                                        |
| PLA10AN4330R3R2 | 43.0                                     | 0.3                  | 300                  | 100                                        |

Operating Temperature Range (Ambient Temperature Range + Winding Temperature Rise): -25°C to 120°C Winding Temperature Rise (at Rated Current) (max.): 60K


## PLA10 Series Sectional Winding Type





| Part Number     | Common Mode Inductance<br>(min.)<br>(mH) | Rated Current<br>(A) | Rated Voltage<br>(V) | Insulation Resistance<br>(min.)<br>(M ohm) |
|-----------------|------------------------------------------|----------------------|----------------------|--------------------------------------------|
| PLA10AN9012R0D2 | 0.9                                      | 2.0                  | 300                  | 100                                        |
| PLA10AN1321R7D2 | 1.3                                      | 1.7                  | 300                  | 100                                        |
| PLA10AN1821R5D2 | 1.8                                      | 1.5                  | 300                  | 100                                        |
| PLA10AN2021R3D2 | 2.0                                      | 1.3                  | 300                  | 100                                        |
| PLA10AN3621R0D2 | 3.6                                      | 1.0                  | 300                  | 100                                        |
| PLA10AN7720R7D2 | 7.7                                      | 0.7                  | 300                  | 100                                        |
| PLA10AN1330R5D2 | 13.0                                     | 0.5                  | 300                  | 100                                        |
| PLA10AN2230R4D2 | 22.0                                     | 0.4                  | 300                  | 100                                        |
| PLA10AN3630R3D2 | 36.0                                     | 0.3                  | 300                  | 100                                        |

Operating Temperature Range (Ambient Temperature Range + Winding Temperature Rise): -25°C to 120°C Winding Temperature Rise (at Rated Current) (max.): 60K

## ■ Equivalent Circuit Diagram



## ■ Insertion Loss-Frequency Characteristics



Switching power supply, electric ballast  
(AC-AC converter)




Operating Temperature Range : -25°C to 60°C      Winding Temperature Rise (at Rated Current) (max.): 60K



## Sectional Winding Type

Operating Temperature Range : -25°C to 60°C      Winding Temperature Rise (at Rated Current) (max.): 60K

## ■ Equivalent Circuit Diagram



## ■ Insertion Loss-Frequency Characteristics




## PLH10 Series

The PLH10 series is a common mode choke coil for high frequency use. The same dimensions as the PLA10 series enables flexible design.

### ■ Features


1. High performance in high frequency range
2. Low profile in vertical core layout
3. Compact and light weight




| Part Number     | Common Mode Inductance<br>(min.)<br>(μH) | Rated Current<br>(A) | Rated Voltage<br>(V) | Insulation Resistance<br>(min.)<br>(M ohm) |
|-----------------|------------------------------------------|----------------------|----------------------|--------------------------------------------|
| PLH10AN7003R6P2 | 70                                       | 3.6                  | 300                  | 100                                        |
| PLH10AN1112R6P2 | 110                                      | 2.6                  | 300                  | 100                                        |
| PLH10AN1612R1P2 | 160                                      | 2.1                  | 300                  | 100                                        |
| PLH10AN2211R5P2 | 220                                      | 1.5                  | 300                  | 100                                        |
| PLH10AN2911R2P2 | 290                                      | 1.2                  | 300                  | 100                                        |
| PLH10AN3711R0P2 | 370                                      | 1.0                  | 300                  | 100                                        |

Operating Temperature Range (Ambient Temperature Range + Winding Temperature Rise): -25°C to 120°C Winding Temperature Rise (at Rated Current) (max.): 60K

### ■ Equivalent Circuit Diagram



### ■ Insertion Loss-Frequency Characteristics




## PLH10 Series (Safety Standard Recognized)

### ■ Features

1. High performance in high frequency range
2. Low profile in vertical core layout
3. Compact and light weight
4. Safety standards: EN60065

### ■ Applications

Suppressing radiation noise in switching power supply and inverter (AC-AC converter)




| Part Number     | Common Mode Inductance<br>(min.)<br>(μH) | Rated Current<br>(A) | Rated Voltage<br>(V) | Insulation Resistance<br>(min.)<br>(M ohm) |
|-----------------|------------------------------------------|----------------------|----------------------|--------------------------------------------|
| PLH10AS7003R6P2 | 70                                       | 3.6                  | 250                  | 100                                        |
| PLH10AS1112R6P2 | 110                                      | 2.6                  | 250                  | 100                                        |
| PLH10AS1612R1P2 | 160                                      | 2.1                  | 250                  | 100                                        |
| PLH10AS2211R5P2 | 220                                      | 1.5                  | 250                  | 100                                        |
| PLH10AS2911R2P2 | 290                                      | 1.2                  | 250                  | 100                                        |
| PLH10AS3711R0P2 | 370                                      | 1.0                  | 250                  | 100                                        |


Operating Temperature Range : -25°C to 60°C

Winding Temperature Rise (at Rated Current) (max.): 60K

### ■ Equivalent Circuit Diagram



### ■ Insertion Loss-Frequency Characteristics



# EMI Suppression Filters (EMIFIL<sup>®</sup>) for AC Power Lines

**muRata**

## Hybrid Choke Coil

2

### PLY10 Series Standard Winding Type


The PLY10 is a compact and high performance hybrid choke coil which can handle differential mode noise caused by the harmonics currents regulation circuit as well as common mode noise. It can handle noise problems much more compactly than a combination of a conventional common mode choke coil and a differential mode choke coil.

#### ■ Features

1. PLY10 has both functions of a common mode choke coil and a differential mode choke coil in its compact body.
2. Low profile in vertical core layout
3. PLY10 has the same pin layout as a general type common mode choke coil which enables it to replace conventional components.
4. Both a standard winding type and a sectional winding type for higher frequency noise are available.

#### ■ EMI Problem for harmonics currents regulation

There are some methods meet harmonics currents regulations (IEC1000-3, EN60555-2) such as an active filter type and one converter type. However, they cause new EMI problems of differential mode noise because they use active components. For that reason, additional filter components to meet differential mode noise must be applied.




| Part Number     | Common Mode Inductance<br>(min.)<br>(mH) | Normal Mode Inductance<br>(min.)<br>(μH) | Rated Current<br>(A) | Rated Voltage<br>(Vac) |
|-----------------|------------------------------------------|------------------------------------------|----------------------|------------------------|
| PLY10AN9012R0R2 | 0.9                                      | 65                                       | 2.0                  | 300                    |
| PLY10AN1121R8R2 | 1.1                                      | 90                                       | 1.8                  | 300                    |
| PLY10AN1521R6R2 | 1.5                                      | 110                                      | 1.6                  | 300                    |
| PLY10AN2121R4R2 | 2.1                                      | 150                                      | 1.4                  | 300                    |
| PLY10AN2821R2R2 | 2.8                                      | 190                                      | 1.2                  | 300                    |
| PLY10AN4321R0R2 | 4.3                                      | 300                                      | 1.0                  | 300                    |
| PLY10AN6220R8R2 | 6.2                                      | 400                                      | 0.8                  | 300                    |
| PLY10AN8720R7R2 | 8.7                                      | 530                                      | 0.7                  | 300                    |
| PLY10AN9920R6R2 | 9.9                                      | 690                                      | 0.6                  | 300                    |
| PLY10AN1430R5R2 | 14.0                                     | 1000                                     | 0.5                  | 300                    |

Operating Temperature (Ambient Temperature Range+Winding Temperature Rise): -25°C to 120°C

Winding Temperature Rise (at Rated Current) (max.): 60K

## PLY10 Series Sectional Winding Type




| Part Number     | Common Mode Inductance<br>(min.)<br>(mH) | Normal Mode Inductance<br>(min.)<br>(μH) | Rated Current<br>(A) | Rated Voltage<br>(Vac) |
|-----------------|------------------------------------------|------------------------------------------|----------------------|------------------------|
| PLY10AN7012R0D2 | 0.7                                      | 50                                       | 2.0                  | 300                    |
| PLY10AN1121R7D2 | 1.1                                      | 65                                       | 1.7                  | 300                    |
| PLY10AN1421R4D2 | 1.4                                      | 110                                      | 1.4                  | 300                    |
| PLY10AN2321R2D2 | 2.3                                      | 160                                      | 1.2                  | 300                    |
| PLY10AN3521R0D2 | 3.5                                      | 240                                      | 1.0                  | 300                    |
| PLY10AN4420R8D2 | 4.4                                      | 320                                      | 0.8                  | 300                    |
| PLY10AN8720R7D2 | 8.7                                      | 500                                      | 0.7                  | 300                    |
| PLY10AN9720R6D2 | 9.7                                      | 670                                      | 0.6                  | 300                    |
| PLY10AN1130R5D2 | 11.0                                     | 840                                      | 0.5                  | 300                    |



Operating Temperature (Ambient Temperature Range+Winding Temperature Rise): -25°C to 120°C

Winding Temperature Rise (at Rated Current) (max.): 60K

### Equivalent Circuit Diagram



### Common Mode Insertion Loss-Frequency Characteristics




Continued on the following page. ↗


Continued from the preceding page.

## Differential Mode Insertion Loss-Frequency Characteristics

Standard Winding Type



Sectional Winding Type




## PLY17 Series A Type

### Features

- Integration of choke coil function to suppress differential mode/Low and High Frequency common mode noise.
- Low Profile (H=<13mm)

### Applications

- For AC power supply, AC adapter
- Low profile equipment such as lighting equipment, FPD, Digital Amplifier



| Part Number     | Common Mode Inductance<br>(min.)<br>(mH) | Normal Mode Inductance<br>(min.)<br>(μH) | Rated Current<br>(A) | Rated Voltage<br>(Vac) |
|-----------------|------------------------------------------|------------------------------------------|----------------------|------------------------|
| PLY17BN4912R4A2 | 0.49                                     | 18                                       | 2.4                  | 300                    |
| PLY17BN9612R0A2 | 0.96                                     | 36                                       | 2.0                  | 300                    |
| PLY17BN1023R0A2 | 1.0                                      | 36                                       | 3.0                  | 300                    |
| PLY17BN1121R8A2 | 1.1                                      | 44                                       | 1.8                  | 300                    |
| PLY17BN1721R5A2 | 1.7                                      | 67                                       | 1.5                  | 300                    |
| PLY17BN2921R2A2 | 2.9                                      | 110                                      | 1.2                  | 300                    |
| PLY17BN3721R0A2 | 3.7                                      | 140                                      | 1.0                  | 300                    |
| PLY17BN5620R8A2 | 5.6                                      | 210                                      | 0.8                  | 300                    |
| PLY17BN7820R7A2 | 7.8                                      | 290                                      | 0.7                  | 300                    |
| PLY17BN9320R6A2 | 9.3                                      | 350                                      | 0.6                  | 300                    |

Operating Temperature (Ambient Temperature Range+Winding Temperature Rise): -25°C to 120°C

Winding Temperature Rise (at Rated Current) (max.): 60K


## PLY17 Series B Type

| Part Number     | Common Mode Inductance<br>(min.)<br>(mH) | Normal Mode Inductance<br>(min.)<br>(μH) | Rated Current<br>(A) | Rated Voltage<br>(Vac) |
|-----------------|------------------------------------------|------------------------------------------|----------------------|------------------------|
| PLY17BN4912R4B2 | 0.49                                     | 24                                       | 2.4                  | 300                    |
| PLY17BN9612R0B2 | 0.96                                     | 47                                       | 2.0                  | 300                    |
| PLY17BN1023R0B2 | 1.0                                      | 47                                       | 3.0                  | 300                    |
| PLY17BN1121R8B2 | 1.1                                      | 58                                       | 1.8                  | 300                    |
| PLY17BN1721R5B2 | 1.7                                      | 88                                       | 1.5                  | 300                    |
| PLY17BN2921R2B2 | 2.9                                      | 140                                      | 1.2                  | 300                    |
| PLY17BN3721R0B2 | 3.7                                      | 180                                      | 1.0                  | 300                    |
| PLY17BN5620R8B2 | 5.6                                      | 280                                      | 0.8                  | 300                    |
| PLY17BN7820R7B2 | 7.8                                      | 390                                      | 0.7                  | 300                    |
| PLY17BN9320R6B2 | 9.3                                      | 460                                      | 0.6                  | 300                    |


Operating Temperature (Ambient Temperature Range+Winding Temperature Rise): -25°C to 120°C

Winding Temperature Rise (at Rated Current) (max.): 60K



## ■ Equivalent Circuit Diagram



## ■ Common Mode Insertion Loss-Frequency Characteristics




## ■ Differential Mode Insertion Loss-Frequency Characteristics



## Noise Suppression Effect of PLY10 Series

The data shows noise suppression effects comparison PLY10 with existing common mode choke coil. (In AC adaptor of note PC)


2




### • Noise Level

The filter circuit with hybrid choke coil has suppressed conducted noise as well as conventional filter in spite of its compact composition.

Common mode choke coil and differential mode choke coil are used.



Hybrid choke coil PLY10



## ⚠Caution /Notice

### ■ ⚠Caution (Rating)

#### 1. Rated Current

Operating current should not exceed the rated value. Even if operating current is under the rated value, adequate ventilation is required to avoid excessive heat generated within the product (choke coil) and from surrounding heat sources. If exceeding these conditions, excessive heat may cause fumes or permanent damage to the product. Please ensure that product (choke coil) is evaluated and confirmed against the specification when it is mounted in your final assembled product.  
-> Winding temperature should be less than 120 degree C.

\*As for FKOB series winding temperature should be less than 95 degree C.

Maximum allowable temperature at the surface of coil (ambient temperature + winding temperature rise) is in accordance with each safety standard applicable to final assembled product. When the temperature at winding exceeds maximum allowable temperature of safety standard, the rated current should be derated.

#### 2. Inrush Current

Inrush current should not exceed 10 times rated current within 1/4 cycle of 50/60Hz commercial power line. Inrush current should be limited to a minimum of 10 seconds after last inrush.

If these conditions are exceeded, excessive heat may cause fumes or permanent damage to the component, or at worst cause ignition.


### ■ Notice (Storage and Operating Condition)

#### 1. Soldering Conditions

##### (1) Flux, Solder

- Rosin-based flux should be used. Do not use strong acidic flux with halide content exceeding 0.2wt% (chlorine conversion value)
- Use 63/37 solder (Sn/Pb = 63/37) or 60/40 solder (Sn/Pb = 60/40). In case of lead-free solder, use Sn-3.0Ag-0.5Cu solder

##### (2) Flow soldering profile



| Standard profile             |                |                       |                | Limit profile   |                |               |
|------------------------------|----------------|-----------------------|----------------|-----------------|----------------|---------------|
| Sn/Pb = 60/40, Sn/Pb = 63/37 |                | Sn-3.0Ag-0.5Cu solder |                |                 |                |               |
| Soldering temp.              | Soldering time | Soldering temp.       | Soldering time | Soldering temp. | Soldering time | Cycle of flow |
| 240-260°C                    | 5s max.        | 250±2°C               | 4-6s           | 265±3°C         | 5s             | 2 times       |

For additional mounting methods, please contact Murata.

### ■ Notice (Soldering and Mounting)

#### Magnetic Flux Leakage

Choke coils generate small amounts of magnetic flux leakage that may adversely affect equipment operation according to component arrangement. Testing should be completed on final assembly to ensure equipment performance is not affected.

#### 2. Cleaning

Avoid cleaning product due to non-waterproof construction.

#### 3. Storage and Handling Requirements

##### (1) Storage period

Product should be used within 12 months after receiving. Solderability should be checked if this period is exceeded.

##### (2) Storage conditions

Storage Temperature: -10 to 40 °C

Relative humidity: 30 to 70%

Avoid sudden changes in temperature and humidity. Don't keep products in corrosive gases such as sulfur, chlorine gas or acid, or it may cause oxidation of lead terminals resulting in poor solderability or corrosion of component windings.

##### (3) Handling conditions

Care should be taken when transporting or handling product to avoid excessive vibration or mechanical shock.

### ■ Notice (Rating)

#### Coil Humming Noise

Magnetic flux generated between coil and core or between the choke coil windings creates repulsive power between the coil windings. This repulsive power causes the coil winding to vibrate and create a humming noise. The amount of hum produced by the coil is proportionate to the amount of harmonic distortion generated by the operating current. This does not influence the electrical performance of the coils, but it should be considered and tested in actual circuit application.

## Packaging

### ■ Minimum Quantity

| Part Number  | Minimum Quantity (pcs.) |      |
|--------------|-------------------------|------|
|              | Magazine Package        | Box  |
| <b>FKOB</b>  | -                       | 100  |
| <b>PLA10</b> | 1800                    | 1260 |
| <b>PLH10</b> | 1800                    | 1260 |
| <b>PLY10</b> | 1800                    | 1200 |
| <b>PLY17</b> | 1920                    | 1080 |

 **Note:**

1. Export Control  
〈For customers outside Japan〉  
Murata products should not be used or sold for use in the development, production, stockpiling or utilization of any conventional weapons or mass-destructive weapons (nuclear weapons, chemical or biological weapons, or missiles), or any other weapons.  
〈For customers in Japan〉  
For products which are controlled items subject to the "Foreign Exchange and Foreign Trade Law" of Japan, the export license specified by the law is required for export.
2. Please contact our sales representatives or product engineers before using the products in this catalog for the applications listed below, which require especially high reliability for the prevention of defects which might directly damage to a third party's life, body or property, or when one of our products is intended for use in applications other than those specified in this catalog.
  - ① Aircraft equipment                      ② Aerospace equipment
  - ③ Undersea equipment                  ④ Power plant equipment
  - ⑤ Medical equipment                    ⑥ Transportation equipment (vehicles, trains, ships, etc.)
  - ⑦ Traffic signal equipment              ⑧ Disaster prevention / crime prevention equipment
  - ⑨ Data-processing equipment          ⑩ Application of similar complexity and/or reliability requirements to the applications listed in the above
3. Product specifications in this catalog are as of January 2005. They are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. If there are any questions, please contact our sales representatives or product engineers.
4. Please read rating and  **CAUTION** (for storage, operating, rating, soldering, mounting and handling) in this catalog to prevent smoking and/or burning, etc.
5. This catalog has only typical specifications because there is no space for detailed specifications. Therefore, please approve our product specifications or transact the approval sheet for product specifications before ordering.
6. Please note that unless otherwise specified, we shall assume no responsibility whatsoever for any conflict or dispute that may occur in connection with the effect of our and/or a third party's intellectual property rights and other related rights in consideration of your use of our products and/or information described or contained in our catalogs. In this connection, no representation shall be made to the effect that any third parties are authorized to use the rights mentioned above under licenses without our consent.
7. No ozone depleting substances (ODS) under the Montreal Protocol are used in our manufacturing process.