

TWIST LEVER FOR POSITION SWITCH 3SE52 METAL
LEVER 21MM LONG PLASTIC ROLLER 19MM**General technical details:**

product designation	actuator for part-turn actuator			
Explosion protection category for dust	none			
Mechanical operating cycles as operating time				
• typical			15,000,000	
Resistance against vibration	0.35 mm / 5g			
Resistance against shock	30g / 11 ms			
Ambient temperature	°C	°C	-25 ... +85	
• during operating			-40 ... +90	
• during storage				
Design of the operating mechanism	metal lever, 21 mm long, straight, plastic roller 19 mm			
mounting position	any			
Item designation			E	
• according to DIN 40719 extendable after IEC 204-2 / according to IEC 750			T	
• according to DIN EN 61346-2				

Certificates/approvals:



CCC



CSA



GOST



UL




VDE



EG-Konf.

Test Certificates

other

Special Test
CertificateConfirmationVibration Test
Certificates**Further information:****Information- and Downloadcenter (Catalogs, Brochures,...)**<http://www.siemens.com/industrial-controls/catalogs>**Industry Mall (Online ordering system)**<http://www.siemens.com/industrial-controls/mall>**CAx-Online-Generator**<http://www.siemens.com/cax>**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**<http://support.automation.siemens.com/WW/view/en/3SE5000-0AA21/all>**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3SE5000-0AA21

last change:

Jul 1, 2013