


Model 6294 Minipincer® Test Clip To Straight Sheathed Banana Plug



FEATURES:

- Attaches to component leads up to .090" (2.3 mm)
- Pincer test lead interfaces directly into the most popular multimeters configured with 4 mm sheathed safety jacks, including Amprobe, Fluke, H-P, Tektronix and Wavetek.
- For added safety, the pincer and banana plug body insulation material is fire retardant Nylon 6, UL94V-0 rated.
- Plug is molded directly to the cable in an integral one-piece design and the wire is double crimped for a long lasting connection.
- Multi-leaf banana spring material is nickel plated Beryllium Copper for extended insertion life & low contact resistance.
- High strand count silicone insulated wire offers excellent flexibility and high temperature resistance.

MATERIALS:

Pincer: Body: Nylon 6 – Fire Retardant – UL94 V-O Rated, Color per part number

Pincer Contact: Beryllium Copper, Gold Plated

Wire: 18 AWG, 65 x 36 Tinned Copper, Insulation – Silicone, .144" (3.66 mm) O.D., Color per P/N

Banana Plug: Body - Brass, Nickel Plated, Spring – Beryllium Copper, Nickel Plated

Insulation - Polypropylene, Fire Retardant UL94 V-2 Rated, Color per part number

RATINGS:

IEC 1010-2-031, Category II, P2 Compliant

Operating Voltage: 300 V RMS

Current: 5 Amperes

ORDERING INFORMATION: Model 6294-48-*

Standard Length: 48" (122 cm) *= Color Code, -0 Black and -2 Red

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[6294-48-0](#) [6294-48-2](#)