


Packaged on 13" recyclable reels. Tape width is 24mm. Supplied with polyamide patch for vacuum pick up. Reels conform to EIA-481.



[larger image](#)

Thread Size x Pitch	M3 x 0.5
Thread Code	M3
Length Code	2
L - Length ± 0.13 	2 mm  larger image
Min. Sheet Thickness	1.53 mm
A Max.	1.53 mm
C Max.	4.09 mm
E ± 0.13	5.56 mm
ØH - Hole Size in Sheet + 0.08	4.22 mm
ØD - Min. Solder Pad	6.2 mm
Parts per Reel	1500
Pitch	12 mm
For Use in Sheet Hardness ¹	Not Applicable
Thread Specification	Internal, ASME B1.13M, 6H
Fastener Material	Carbon Steel
Optional Finish	Electro-Plated Matte - Tin, ASTM B 545, Class A with Clear Preservative Coating, Annealed
CAD Supplier	PennEngineering® (PEM®)

¹ HRB - Hardness Rockwell "B" Scale. HB - Hardness Brinell.