




LOC		DIST		REVISIONS						
GP		00		P	LTR	DESCRIPTION		DATE	DWN	APVD
					H	REVISED PER ECO-11-016769		19AUG2011	CJV	SLB

D




- 1 HOUSING: PBT, UL94V-0, COLOR (SEE TABLE).
POSTS: PHOSPHOR BRONZE.
2 POSTS: 0.00076[.000030] MIN GOLD ON MATING AREA, 0.00254[.000100] MIN TIN ON SOLDER END, ALL OVER 0.00127[.000050] MIN NICKEL ON ENTIRE POST.
3 DATUMS S & T TO BE ESTABLISHED BY CUSTOMER.
4 NO KEYING SLOT ON THIS END FOR 6, 10, 12 & 14 POSITION ASSEMBLIES.
5 NO KEYING SLOT ON THIS END FOR 6 & 10 POSITION ASSEMBLIES.

C



B



RECOMMENDED PC BOARD LAYOUT
(VIEWED FROM CONNECTOR SIDE)

	BLUE	78.74 [3.100]	31	86.36 [3.400]	88.90 [3.500]	64	3-1761605-7
	BLUE	60.96 [2.400]	24	68.58 [2.700]	71.12 [2.800]	50	3-1761605-5
	BLUE	53.34 [2.100]	21	60.96 [2.400]	63.50 [2.500]	44	3-1761605-4
	BLUE	48.26 [1.900]	19	55.88 [2.200]	58.42 [2.300]	40	3-1761605-3
	BLUE	43.18 [1.700]	17	50.80 [2.000]	53.34 [2.100]	36	3-1761605-2
	BLUE	40.64 [1.600]	16	48.26 [1.900]	50.80 [2.000]	34	3-1761605-1
	BLUE	35.56 [1.400]	14	43.18 [1.700]	45.72 [1.800]	30	3-1761605-0
	BLUE	30.48 [1.200]	12	38.10 [1.500]	40.64 [1.600]	26	2-1761605-9
	BLUE	27.94 [1.100]	11	35.56 [1.400]	38.10 [1.500]	24	2-1761605-8
	BLUE	22.86 [.900]	9	30.48 [1.200]	33.02 [1.300]	20	2-1761605-7
	BLUE	17.78 [.700]	7	25.40 [1.000]	27.94 [1.100]	16	2-1761605-6
	BLUE	15.24 [.600]	6	22.86 [.900]	25.40 [1.000]	14	2-1761605-5
	BLUE	12.70 [.500]	5	20.32 [.800]	22.86 [.900]	12	2-1761605-4
	BLUE	10.16 [.400]	4	17.78 [.700]	20.32 [.800]	10	2-1761605-3
	BLUE	5.08 [.200]	2	12.70 [.500]	15.24 [.600]	6	2-1761605-1
	OBSOLETE	BLACK	73.66 [2.900]	81.28 [3.200]	83.82 [3.300]	60	1-1761605-6
	OBSOLETE	BLACK	60.96 [2.400]	68.58 [2.700]	71.12 [2.800]	50	1-1761605-5
	OBSOLETE	BLACK	53.34 [2.100]	60.96 [2.400]	63.50 [2.500]	44	1-1761605-4
	OBSOLETE	BLACK	48.26 [1.900]	55.88 [2.200]	58.42 [2.300]	40	1-1761605-3
	OBSOLETE	BLACK	40.64 [1.600]	48.26 [1.900]	50.80 [2.000]	34	1-1761605-1
	OBSOLETE	BLACK	35.56 [1.400]	43.18 [1.700]	45.72 [1.800]	30	1-1761605-0
	OBSOLETE	BLACK	30.48 [1.200]	38.10 [1.500]	40.64 [1.600]	26	1761605-9
	OBSOLETE	BLACK	22.86 [.900]	30.48 [1.200]	33.02 [1.300]	20	1761605-7
	OBSOLETE	BLACK	17.78 [.700]	25.40 [1.000]	27.94 [1.100]	16	1761605-6
	OBSOLETE	BLACK	15.24 [.600]	22.86 [.900]	25.40 [1.000]	14	1761605-5
	OBSOLETE	BLACK	10.16 [.400]	17.78 [.700]	20.32 [.800]	10	1761605-3
	HOUSING COLOR	D	C	B	A	NO OF POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. GERACE 11FEB05	 TE Connectivity				
DIMENSIONS: mm [INCHES]		CHK S. BOLASH 11FEB05					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M. WALMSLEY 11FEB05	NAME		HEADER ASSEMBLY, RIGHT ANGLE, LOW PROFILE, IDC —		
0. PLC ± — 1. PLC ± — 2. PLC ± — 3. PLC ± 0.13[.005] 4. PLC ± — ANGLES ± —		PRODUCT SPEC — APPLICATION SPEC	SIZE				
MATERIAL		WEIGHT —	CAGE CODE		DRAWING NO		RESTRICTED TO
FINISH		A1		00779		1761605	
		CUSTOMER DRAWING		SCALE		4:1	
				SHEET		1 of 1	
				REV		H	

COPYRIGHT 2005
TE CONNECTIVITY CORP
ALL RIGHTS RESERVED