

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—

D

D

C

C

B

B


A

A

9	1.650	33	1.830	68	10 8-104068-8
	2.450	49	2.630	100	8-104068-7
	1.950	39	2.130	80	10 8-104068-6
	1.750	35	1.930	72	10 8-104068-5
	1.050	21	1.230	44	10 8-104068-4
	.800	16	.980	34	8-104068-3
	.600	12	.780	26	10 8-104068-2
	.550	11	.730	24	10 8-104068-1
	.350	7	.530	16	10 8-104068-0
	.300	6	.480	14	10 7-104068-9
	.250	5	.430	12	10 7-104068-8
	.150	3	.330	8	7-104068-7
	1.450	29	1.630	60	10 7-104068-6
	1.200	24	1.380	50	10 7-104068-5
	.950	19	1.130	40	10 7-104068-4
	.700	14	.880	30	10 7-104068-3
	.200	4	.380	10	10 7-104068-2
	.450	9	.630	20	10 7-104068-1
7	1.650	33	1.830	68	6-104068-8
	2.450	49	2.630	100	6-104068-7
	1.950	39	2.130	80	6-104068-6
	1.750	35	1.930	72	6-104068-5
	1.050	21	1.230	44	6-104068-4
	.800	16	.980	34	6-104068-3
	.600	12	.780	26	6-104068-2
	.550	11	.730	24	6-104068-1
	.350	7	.530	16	6-104068-0
	.300	6	.480	14	5-104068-9
	.250	5	.430	12	5-104068-8
	.150	3	.330	8	11 5-104068-7
	1.450	29	1.630	60	5-104068-6
	1.200	24	1.380	50	5-104068-5
	.950	19	1.130	40	5-104068-4
	.700	14	.880	30	5-104068-3
	.200	4	.380	10	5-104068-2
	.450	9	.630	20	5-104068-1
FINISH	C	B	A	NO OF POS	PART NUMBER

8	1.650	33	1.830	68	10 3-104068-8
	2.450	49	2.630	100	10 3-104068-7
	1.950	39	2.130	80	10 3-104068-6
	1.750	35	1.930	72	10 3-104068-5
	1.050	21	1.230	44	10 3-104068-4
	.800	16	.980	34	10 3-104068-3
	.600	12	.780	26	10 3-104068-2
	.550	11	.730	24	10 3-104068-1
	.350	7	.530	16	10 3-104068-0
	.300	6	.480	14	10 2-104068-9
	.250	5	.430	12	10 2-104068-8
	.150	3	.330	8	10 2-104068-7
	1.450	29	1.630	60	10 2-104068-6
	1.200	24	1.380	50	10 2-104068-5
	.950	19	1.130	40	10 2-104068-4
	.700	14	.880	30	10 2-104068-3
	.200	4	.380	10	10 2-104068-2
	.450	9	.630	20	10 2-104068-1
1	1.650	33	1.830	68	1-104068-8
	2.450	49	2.630	100	1-104068-7
	1.950	39	2.130	80	1-104068-6
	1.750	35	1.930	72	1-104068-5
	1.050	21	1.230	44	1-104068-4
	.800	16	.980	34	1-104068-3
	.600	12	.780	26	1-104068-2
	.550	11	.730	24	1-104068-1
	.350	7	.530	16	1-104068-0
	.300	6	.480	14	104068-9
	.250	5	.430	12	104068-8
	.150	3	.330	8	11 104068-7
	1.450	29	1.630	60	104068-6
	1.200	24	1.380	50	104068-5
	.950	19	1.130	40	104068-4
	.700	14	.880	30	104068-3
	.200	4	.380	10	104068-2
	.450	9	.630	20	104068-1
FINISH	C	B	A	NO OF POS	PART NUMBER

104068

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. CLOUSER 10-3-88	TE Connectivity			
DIMENSIONS: INCHES		CHK T. ZOLA 10-3-88				
		APVD T. ZOLA 10-3-88	NAME HEADER ASSEMBLY, VERTICAL SHROUDED, DOUBLE ROW W/SIDE & END LATCHES, AMPMODU System 50			
		PRODUCT SPEC 108-1093				
MATERIAL		APPLICATION SPEC 114-25031	SIZE A2	CAGE CODE 00779	DRAWING NO C=104068	RESTRICTED TO -
		WEIGHT -	SCALE 4:1		SHEET 2 of 2	REV P
SEE TABLE			CUSTOMER DRAWING			