


AD8020 SERIES



Specifications(Nominal)


*:Noise is measured at the distance of one (1) meter from the axis of intake.

Frame size (mm)	Model No.	Bearing System Type	Rated Voltage (VDC)	Current (A)	Power (W)	Rated Speed (rpm)	Maximum AirFlow		Maximum Pressure		*Noise Level (dB/A)	Weight (g)
							(CMM)	(CFM)	(InAq)	(mmAq)		
80x80x20	AD0805MB-C73(N75)	◎ ●	5	0.17	0.85	2440	0.584	20.664	0.107	2.717	28.1	68.0
	AD0805HB-C73(N75)	◎ ●	5	0.24	1.20	3000	0.747	26.408	0.158	4.013	34.4	
	AD0812MB-C73(N75)	◎ ●	12	0.07	0.84	2440	0.584	20.664	0.107	2.717	28.1	
	AD0812HB-C73(N75)	◎ ●	12	0.13	1.56	3000	0.747	26.408	0.158	4.013	34.4	
	AD0812UB-C73(N75)	◎ ●	12	0.25	3.00	4200	1.057	37.375	0.300	7.620	43.3	
	AD0824MB-C73(NEUM)	◎ ●	24	0.05	1.20	2440	0.584	20.664	0.107	2.717	28.1	
	AD0824HB-C73(NEUM)	◎ ●	24	0.08	1.92	3000	0.747	26.408	0.158	4.013	34.4	

Bearing type: ◎=Ball ※=Sleeve ●=Hypro bearing

Specifications subject to change without notice.

The specification for bearing type is for reference only , for more bearing types information, please contact with your ADDA sales representative, thanks!!
 (網頁上呈現產品軸承資訊均以2Ball為主，若需其他產品資訊請聯絡您在ADDA的業務代表，謝謝！！)



*Motor protective circuit and third lead wire functions

0	1	2	3	4	6	7	8	9	A	B
	✓	✓	✓							

*Safety approvals

✓	✓	✓	✓	✓

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ADDA:](#)

[AD0824HB-C71-LF](#) [AD0812MB-C76-LF](#)