





Rotary DIP Switch A6R/A6RV

Low-Cost Rotary DIP Switches

- Series includes top-actuated, side-actuated, flat, and extended-shaft models.
- The rotor has an O-ring sealed construction that prevents the ingress of dirt and dust.
- Two different types of terminal arrangements are available for each model to allow flexibility of circuit design.
- RoHS Compliant.



Ordering Information

Output code	Number of positions	Terminal arrangement	Top-actuated flat	Top-actuated extended shaft	Side-actuated flat	Side-actuated extended shaft
						
BCD 1-2-4-8	10	4 × 1	A6R-101RF	A6R-101RS	A6RV-101RF	A6RV-101RS
		3 × 3	A6R-102RF	A6R-102RS	A6RV-102RF	A6RV-102RS
BCD Hexadecimal 1-2-4-8	16	4 × 1	A6R-161RF	A6R-161RS	A6RV-161RF	A6RV-161RS
		3 × 3	A6R-162RF	A6R-162RS	A6RV-162RF	A6RV-162RS

Note: Switches are delivered in units of 48 per tube. Order in multiples of 48.

Specifications

■ Ratings/Characteristics

Switching Capacity	25 mA at 24 VDC	
Min. Permissible Load	10 μ A at 3.5 VDC	
Contact resistance	200 m Ω max.	
Insulation resistance	100 M Ω min. (at 250 VDC)	
Dielectric strength	250 VAC for 1 minute between terminals	
Operating torque	200 g-cm max. (1.96 x 10 ⁻² N-m max.)	
Vibration resistance	Malfunction: 10 to 55 Hz, 1.5-mm double amplitude	
Shock resistance	Malfunction: 300 m/s ² (30G) min.	
Ambient operating temperature	-25 to 80°C at 60% RH max. (with no icing or condensation)	
Ambient operating humidity	35% to 95% (at 5 to 35°C)	
Electrical service life	5,000 steps min.	
Weight (See note 2)	Top-actuated:	Approx. 0.6 g
	Side-actuated:	Approx. 0.8 g

- Note:**
1. Data shown are of initial value.
 2. Add 0.13 g for the extended-shaft version of each model
 3. Switches cannot be water washed

■ Output Codes

10-position Models

Type	BCD 1-2-4-8			
	Terminal No. Position	1	2	4 8
0				
1		●		
2			●	
3		●	●	
4				●
5		●		●
6			●	●
7		●	●	●
8				●
9		●		●

Note: "●" indicates that the internal switch is ON.

16-position Models


Type	BCD/hexadecimal 1-2-4-8			
	Terminal No. Position	1	2	4 8
0				
1		●		
2			●	
3		●	●	
4				●
5		●		●
6			●	●
7		●	●	●
8				●
9		●		●
A			●	●
B		●	●	●
C				●
D		●		●
E			●	●
F		●	●	●

Dimensions

- Note:** 1. All units are in millimeters unless otherwise indicated.
2. Unless otherwise specified, a tolerance of ± 0.4 mm applies to all dimensions.


Top-actuated Flat Models with 4x1 Terminal Arrangement

A6R-101RF
A6R-161RF



4x1 Terminal Arrangement


A6R-101RS
A6R-161RS



Top-actuated Extended-shaft Models with


Top-actuated Flat Models with 3x3 Terminal Arrangement

A6R-102RF
A6R-162RF




Top-actuated Extended-shaft Models with 3x3 Terminal Arrangement

A6R-102RS
A6R-162RS




Mounting holes Top-actuated models

4x1 Terminal




3x3 Terminal




Internal connections Top-actuated models

4x1 Terminal




3x3 Terminal




Side-actuated Flat Models with 4x1 Terminal Arrangement

A6RV-101RF
A6RV-161RF




Side-actuated Extended-shaft Models with 4x1 Terminal Arrangement

A6RV-101RS
A6RV-161RS




Side-actuated Flat Models with 3x3 Terminal Arrangement

A6RV-102RF
A6RV-162RF




Side-actuated Extended-shaft Models with 3x3 Terminal Arrangement

A6RV-102RS
A6RV-162RS




Mounting holes Side-actuated models

4x1 Terminal




3x3 Terminal




Internal connections Side-actuated models

4x1 Terminal



3x3 Terminal



All sales are subject to Omron Electronic Components LLC standard terms and conditions of sale, which can be found at http://www.components.omron.com/components/web/webfiles.nsf/sales_terms.html

ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.

To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.

OMRON[®]

**OMRON ELECTRONIC
COMPONENTS LLC**

55 E. Commerce Drive, Suite B
Schaumburg, IL 60173

847-882-2288

OMRON ON-LINE

Global - <http://www.omron.com>

USA - <http://www.components.omron.com>

Cat. No. X303-E-1

11/10

Specifications subject to change without notice

Printed in USA

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Omron:

[A6R-101RS](#) [A6RV-162RF](#) [A6RV-102RF](#) [A6RV-101RS](#) [A6RV-101RF](#) [A6R-101RF](#) [A6RV-161RF](#) [A6R-162RS](#)
[A6R-162RF](#) [A6R-161RF](#) [A6R-161RS](#) [A6R-102RF](#) [A6R-102RS](#) [A6RV-161RS](#) [A6RV-162RS](#) [A6RV-102RS](#)