




DESCRIPTION: .085" RIBBON SOLDER CUP



	A	B	C	D	E
14	1.729	.992	.476	.602	1.417
24	43.92	25.20	12.10	15.30	35.99
36	2.154	1.417	.476	.602	1.842
50	54.71	36.00	12.10	15.30	46.79
36	2.665	1.925	.476	.602	2.352
50	67.69	48.90	12.10	15.30	59.74
50	3.259	2.538	.476	.602	2.947
50	82.78	64.47	12.10	15.30	74.85

111-XXX-203-001

SERIES _____

POSITIONS _____

014

024

036

050

GENDER _____

2 = FEMALE

TERMINATION _____

3 = SOLDER CUP

SHELL PLATING _____

3 = NICKEL

HARDWARE OPTIONS _____

00 = NO HARDWARE

PLATING OPTIONS _____

01 = GOLD FLASH

MATERIALS:

INSULATOR: GLASS-FILLED THERMOPLASTIC
UL RATED 94V-0

CONTACTS: COPPER ALLOY

ELECTRICALS:

CONTACT CURRENT RATING: 5 AMPS

DIELECTRIC WITHSTANDING VOLTAGE: AC 1200 R.M.S.

INSULATION RESISTANCE: 1000 mohms MINIMUM AT 500V DC

CONTACT RESISTANCE: 30 mOHMS MAXIMUM

OPERATING TEMPERATURE: -55°C TO +125°C



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
WAYNE ROBBINS

DATE:
8-23-98

CHECKED:
PAM JENKINS

DATE:
8-24-98

SCALE:

SHEET

OF

1 1

REV

5

DWG NO.

111-XXX-203-001

NorComp