




Technical drawing of a mechanical part showing dimensions and a surface texture symbol.

Dimensions:

- Top horizontal dimension: 1.65 ± 0.15 [$.065 \pm .006$]
- Bottom horizontal dimension: 0.85 ± 0.10 [$.033 \pm .004$]

Surface texture symbol: A triangle with the number 5 inside, indicating a surface texture requirement.

Feature identifier: (15)


[illegible]




Technical drawing of a carbide tool. The tool is shown in a side view with a central cutting edge. The top surface is labeled "CARBIDE" and "T007". A callout points to the top surface with the text "2 & 3 POSITIONS ONLY". The bottom surface is dimensioned with a diameter of $\varnothing 0.60$ and a length of $[.024]$ REF. A cross-section view is shown below the main view, indicating a diameter of $\varnothing 0.60$ and a length of $[.024]$ REF. A table at the bottom left contains the following information:

(13)	$\oplus$	0,25	Z	X	Y
------	----------	------	---	---	---

0.85±0.10
[.034±.004]TYP
(16)

SIDE





47.50 [1.870]	50.83 [2.001]	52.50 [2.067]	20	2-2132415-0
45.00 [1.772]	48.33 [1.903]	50.00 [1.968]	19	1-2132415-9
42.50 [1.673]	45.83 [1.804]	47.50 [1.870]	18	1-2132415-8
40.00 [1.575]	43.33 [1.706]	45.00 [1.772]	17	1-2132415-7
37.50 [1.476]	40.83 [1.607]	42.50 [1.673]	16	1-2132415-6
35.00 [1.378]	38.33 [1.510]	40.00 [1.575]	15	1-2132415-5
32.50 [1.280]	35.83 [1.411]	37.50 [1.476]	14	1-2132415-4
30.00 [1.181]	33.33 [3.12]	35.00 [1.378]	13	1-2132415-3
27.50 [1.083]	30.83 [.214]	32.50 [1.280]	12	1-2132415-2
25.00 [.984]	28.33 [.115]	30.00 [1.181]	11	1-2132415-1
22.50 [.886]	25.83 [.167]	27.50 [1.083]	10	1-2132415-0
20.00 [.787]	23.33 [.919]	25.00 [.984]	9	2132415-9
17.50 [.689]	20.83 [.820]	22.50 [.886]	8	2132415-8
15.00 [.591]	18.33 [.722]	20.00 [.787]	7	2132415-7
12.50 [.492]	15.83 [.623]	17.50 [.689]	6	2132415-6
10.00 [.394]	13.33 [.525]	15.00 [.591]	5	2132415-5
7.50 [.295]	10.83 [.426]	12.50 [.492]	4	2132415-4
5.00 [.197]	8.33 [.328]	10.00 [.394]	3	2132415-3
2.50 [.098]	5.83 [.229]	7.50 [.295]	2	2132415-2
DIM C	DIM B	DIM A	POS	PART NO