





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		A	RELEASED	01MAR2001	EZ	DB
			B	REVISED EC 0G3B-0167-02	16JAN2003	SW	CR




1. MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0, COLOR BLUE
CLAMP: BRASS, TIN PLATED.
CLAMPING SCREW: M3, BRASS, NICKEL PLATED.
2. SUITABLE FOR 1.6-2.4mm PCB THICKNESS
3. END-TO-END STACKABLE W/INTERLOCK, WITHOUT LOSS OF CENTERLINE SPACING.
4. WIRE SIZE RANGE: 12-30 AWG
5. RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORY INC. FILE No. E60677
6. IMQ CERTIFICATE WITH SURVEILANCE IN CONFORMITY WITH IEC 998-1/998-2-1.
7. NOT CUMULATIVE TOLERANCE.



796688-3 AS SHOWN

120	24	2-796688-4
115	23	2-796688-3
110	22	2-796688-2
105	21	2-796688-1
100	20	2-796688-0
95	19	1-796688-9
90	18	1-796688-8
85	17	1-796688-7
80	16	1-796688-6
75	15	1-796688-5
70	14	1-796688-4
65	13	1-796688-3
60	12	1-796688-2
55	11	1-796688-1
50	10	1-796688-0
45	9	796688-9
40	8	796688-8
35	7	796688-7
30	6	796688-6
25	5	796688-5
20	4	796688-4
15	3	796688-3
10	2	796688-2
DIM. A		No. POS.
		PART NUMBER



THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.2

1 PLC ±0.2

2 PLC ±0.2

3 PLC ±0.2

4 PLC ±0.2

ANGLES ±2

FINISH

MATERIAL

DWN E. ZANOLINI 28FEB2001

CHK E. ZANOLINI 28FEB2001

APVD D. BLEVENOUR 28FEB2001

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

CUSTOMER DRAWING

BUCHANAN

Tyco Electronics

Harrisburg, PA 17105-3608

NAME

TERMINAL BLOCK, PCB MOUNT

ANGLED ENTRY WIRE, STACKING

W/INTERLOCK, 5mm PITCH

SIZE A2

CAGE CODE 00779

DRAWING NO. 796688

RESTRICTED TO -

SCALE 5:1

SHEET 1 OF 1

REV B