





LOC	DIST	REVISIONS 變更					
J	—	P	LTR	DESCRIPTION	DATE	DWN	AP/D
			K5	REVISED ECR-13-006271	12APR2013	TS	KB



プリント基板取付穴寸法図
(MOUNTING DIMENSIONS FOR P.C.BOARD)

1. 板厚, 1.6 ± 0.15
(P.C.B. THICKNESS, 1.6 ± 0.15)
2. 公差, ± 0.1
(TOLERANCE, ± 0.1)



注記：

△ 相手ハウジングと所定の機能を満たしてかん合できること。

△ フードの反りは0.2以内。

3 プリント基板の取付けは JIS B1115 M3 1種の
タッピンネジで締め付けた後ばんだ付けする。

4 適用製品規格：108-5093

△  面より2mmの範囲で測定のこと。

6 相手ハウジングとのかん合力は、29.4N以下
但し、リセプタクルコンタクトは含まない。

△ 金もっき位置番号：下図参照のこと（図略番号はありません）

NOTE :


① IN COUPLING WITH THE PLUG HOUSING MATING SATISFIES FUNCTION
WARPAGE 0.2 MAX.

③ SOLDERING AFTER MOUNTING P.C. BOARD BY 3mmDIA TAPPING SCREW,
SPECIFIED IN JIS B1115

④ PRODUCT SPEC NO. 108-5093


⑤ TO BE MEASURED WITHIN 2mm FROM -A-

⑥ IN COUPLING WITH THE PLUG HOUSING MATING FORCE 29.4N MAX.
WITHOUT RECEPTACLE CONTACT



	①～②	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD (0.38μm MIN.)	NATURAL	3-5171367-1
	①～②	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD (0.76μm MIN.)	NATURAL	2-5171367-1
	⑥ ⑨ ⑩ ⑭ ⑲ ⑳	TIN-LEAD	SELECTIVE GOLD (0.38μm MIN.)	NATURAL	4-171367-1
			PRE-TIN		
OBSOLETE	①～⑩, ⑪～⑳	TIN-LEAD	SELECTIVE GOLD (0.38μm MIN.)	GREEN	3-171367-4
	↑	TIN-LEAD	SELECTIVE GOLD (0.38μm MIN.)	NATURAL	3-171367-1
OBSOLETE	①～⑩, ⑪～⑳	TIN-LEAD	SELECTIVE GOLD (0.76μm MIN.)	GREEN	2-171367-4
	↑	TIN-LEAD	SELECTIVE GOLD (0.76μm MIN.)	NATURAL	2-171367-1
	③ ⑨ ⑬ ⑮	TIN-LEAD	SELECTIVE GOLD (0.38μm MIN.)	YELLOW	1-171367-7
	↑		PRE-TIN		
	↑			GRAY	1-171367-6
	↑			BLUE	1-171367-5
	↑			GREEN	1-171367-4
	↑			BROWN	1-171367-3
	↑			BLACK	1-171367-2
	③ ⑨ ⑬ ⑮	TIN-LEAD	SELECTIVE GOLD (0.38μm MIN.)	NATURAL	1-171367-1
			PRE-TIN		
	—//—		PRE-TIN	GRAY	171367-6
	—//—		PRE-TIN	BLUE	171367-5
	—//—		PRE-TIN	GREEN	171367-4
	—//—		PRE-TIN	BROWN	171367-3
	—//—		PRE-TIN	BLACK	171367-2
	—//—		PRE-TIN	NATURAL	171367-1
GOLD PL. POSITION No. 金めっき位置番番号	SOLDERING SIDE 半田付け部		CONTACT SIDE 接触部側	COLOR 色	PART NUMBER 製品番番
	CONTACT FINISH コンタクト仕上				

TOLERANCE UNLESS OTHERWISE SPECIFIED: 一般公差	
$0 < x \leq 10$	± 0.2
$10 < x \leq 30$	± 0.25
$30 < x \leq 100$	± 0.3
ANGLE ; 角度	$\pm 3''$

THIS DRAWING IS A CONTROLLED DOCUMENT.						DWG SHINOHARA	31AUG07			TE Connectivity	
DIMENSIONS: 単位:mm		TOLERANCES UNLESS OTHERWISE SPECIFIED		CHEK K.BETSUI	APPR K.BETSUI	31AUG07	NAME 名称	21P HORIZONTAL TYPE CAP HOUSING MULTI-INTERLOCK CONN. WIRE TO PCB			
9 PLC ± 2 PLC ± 2 PLC ± 2 PLC ± 2 PLC ±		全長± ± ± ± ±		PRODUCT SPEC 製品仕様		NOTE 4					
		取付適用規格		APPLICATION SPEC 取付適用規格							
MATERIAL 材質	HSG: 66 NYLON CONTACT: BRASS		FINISH 仕上		WEIGHT		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
						A1	00779	 171367	—		
CUSTOMER DRAWING							SCALE	2:1	SHEET	1 OF 1	REV K