










- 1 POSITION CENTER CONTACT
- 2 MATERIAL: PHOS - BRONZE,
PLATING: 0.3 - 0.5 μm MIN GOLD
OVER 4.0 - 6.0 μm MIN NICKEL.
- 3 MATERIAL: BRASS,
PLATING: 0.3 - 0.5 μm MIN GOLD
OVER 4.0 - 6.0 μm MIN NICKEL.
- 4 MISALIGNMENT BETWEEN CONNECTOR AXIS
AND TARGET PAD, 0.80 mm MAX.
- 5 MATERIAL: PTFE



THIS DRAWING IS A CONTROLLED DOCUMENT.

OWN
M. VAN SCO
CHK
M. PHILLIPS
APVD
M. PHILLIPS

21JAN2003
21JAN2003
21JAN2003

DIMENSIONS:

mm

9 PLC ±
1 PLC ±0.2
2 PLC ±0.05
3 PLC ±
4 PLC ±
ANGLES ±1°
FINISH

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

9 PLC ±
1 PLC ±0.2
2 PLC ±0.05
3 PLC ±
4 PLC ±
ANGLES ±1°
FINISH

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

NAME

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

CONNECTOR, COAXIAL,
BOARD TO BOARD
4.0 mm HEIGHT

A100779C=1658260

SCALE 40:1

SHEET 1 OF 2

REV E1

750

L/P

QTY

REELED CONNECTOR

COAX CONNECTOR

DESCRIPTION

1658260-2

1658260-1

PART
NUMBER

STE

TE Connectivity

