


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION , 19 .
© COPYRIGHT 19 BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	P	F	REVISIONS				
				ZONE	LTR	DESCRIPTION	DATE	APPD
BD	35				F	REDRAWN AND REV PER ECN BD4183	8-20-90	KB
					G	OBS -2 PER EC 0020-1305-95	16 MAY 96	RB



OBSOLETE	NO	207846-2
	YES	207846-1
	SEALS	PART NUMBER

- 1. WIRE INSULATION SEALING RANGE .070-.130 DIA.
- 2. THIN MEMBRANE PERMISSIBLE ON SMALL DIAMETER OF WIRE SEALS.
- 3. ROTATION OF CAVITY CIRCUIT KEY FROM PART TO PART IS PERMISSIBLE.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON: 2 PLC DEC ± - 3 PLC DEC ± - ANGLES ± - MATERIAL SEE CALLOUT FINISH -	DR 8-20-90 J GALLUCCI BG	AMP AMP INCORPORATED Harrisburg, Pa. 17105	
	CHK 1-4-91 J MCCLINTON		
	APPD 1-18-91 K BEAVER	NAME RECEPTACLE, 2 POSITION, STANDARD ECONOSEAL CONNECTOR	
	APPD 1-29-91 J FULPONI		
	PRODUCT SPEC -	SIZE B	FSCM NO 00779
	APPLICATION SPEC -	DRAWING NO 207846	
	WEIGHT -	SCALE 2:1	SHEET 1 OF 1