

## Patch panels - VS-PP-R-3XRJ45/5-LSA - 1653045

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Patch panel, RJ45, DIN rail mounting, IP20, 3 slots, IDC connection, CAT5e, option of shielding via jumpers



### Key commercial data

Packing unit	1 pc
GTIN	 4 017918 970000
Weight per Piece (excluding packing)	147.2 GRM
Custom tariff number	85366990
Country of origin	Germany

### Technical data

#### Mechanical characteristics

Number of positions	8
Number of slots	3
Insertion/withdrawal cycles	≥ 200
Connection method	LSA-PLUS
Conductor cross section	0.14 mm <sup>2</sup> ... 0.34 mm <sup>2</sup> (solid)
Connection cross section AWG	26 ... 22 (solid)
External cable diameter	5 mm ... 8.5 mm
Color	green

#### Ambient conditions

Ambient temperature (operation)	0 °C ... 70 °C
Degree of protection	IP20

#### Material data

## Patch panels - VS-PP-R-3XRJ45/5-LSA - 1653045

### Technical data

#### Material data

Inflammability class according to UL 94	V0
Housing material	PC
Contact carrier material	PBT
Contact material	Copper alloy
Contact surface material	Gold over nickel

#### Electrical characteristics

Number of positions	8
Transmission characteristics (category)	CAT5 (IEC 11801:2002), CAT5e (TIA 568B:2001)
Rated current	1 A

### Classifications

#### eCl@ss

eCl@ss 4.0	27140815
eCl@ss 4.1	27140815
eCl@ss 5.0	19030109
eCl@ss 5.1	19030109
eCl@ss 6.0	19170107
eCl@ss 7.0	19170112

#### ETIM

ETIM 2.0	EC000200
ETIM 3.0	EC001128
ETIM 4.0	EC001128
ETIM 5.0	EC001128


#### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

#### Drawings

## Patch panels - VS-PP-R-3XRJ45/5-LSA - 1653045

Dimensioned drawing



Patch panel with three RJ45 connections

---

Phoenix Contact 2014 © - all rights reserved  
<http://www.phoenixcontact.com>