







PRODUCT NO.	STAND OFF (MM)	SOLDER TAIL	LOWER OR UPPER DECK	HOLD DOWN	LOCATOR
10119103-040LF	2.0	R/A	LOWER	NONE	NONE




DETAIL B
SCALE 10.000



DETAIL A
SCALE 10.000



DIM"L"	4.25±0.1	3.5±0.1	5.0±0.1
PIN NO.	OTHERS	36, 37	1, 17, 34, 35, 51, 68

spec ref				dr	Su-Hua Miao	2012/05/22	projection 	MM 	size	A4	scale	1.000	
tolerance std ISO1101 ISO406	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Su-Hua Miao	2012/06/04			ecn no	-			
				chr	-	-			rel level			Released	
				appr	Rick Bian	2012/06/04	product family			PCMCIA	-		
surface ISO1302	linear	0.X	±0.3		title	68 POS EJECTOR HEADER ASSY FOR 5V APPLICATION			dwg no	10119103		rev	A
		0.XX	±0.13										
		0.XXX	±0.05										
		angular	0°	±2°	www.fci.com	cat. no.	-			Product - Customer Drw			sheet 1 of 3







PrintE File - REV C - 2009-06-09

PDS: Rev :A

STATUS:Released

Printed: Jun 04, 2012

PRODUCT NO.	STAND OFF (MM)	SOLDER TAIL	LOWER OR UPPER DECK	HOLD DOWN	LOCATOR
10119103-505LF	0	R/A	UPPER	NONE	YES



DIM "L"	4.25±0.1	3.5±0.1	5.0±0.1
PIN NO.	OTHERS	36,37	1,17,34,35,51,68

spec ref				dr	Su-Hua Miao	2012/05/22	projection 	MM 	size	A4	scale	1.000
tolerance std ISO1101 ISO406	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Su-Hua Miao	2012/06/04			ecn no	-		
				chr	-	-			rel level	Released		
				appr	Rick Bian	2012/06/04	product family		-			
surface ISO1302	linear	0.X	±0.3		title	68 POS EJECTOR HEADER ASSY FOR 5V APPLICATION			dwg no	10119103		rev A
		0.XX	±0.13									
		0.XXX	±0.05									
		angular	0°	±2°	www.fci.com	cat. no.	-	Product - Customer Drw			sheet 2 of 3	

Print File - REV C - 2009-06-09

PDS: Rev :A

STATUS:Released


Printed: Jun 04, 2012




Copyright FCI.



TOP MOUNT HEADER/MECH. PCB LAYOUT




BOTTOM MOUNT HEADER/MECH. PCB LAYOUT



10119103-XXXXLF

- LEAD FREE
- HOLD DOWN NONE: NO
H: YES
- SOLDER TAIL 0: R/A
5: R/A
- STAND OFF 0: 0MM
4: 2MM
- MOUNTING STYLE 0: TOP MOUNTING
5: BOTTOM MOUNTING

- NOTES
- MATERIAL
HOUSING: HIGH TEMPERATURE THERMOPLASTIC
UL94V-0 BLACK
PIN: COPPER ALLOY
HOLD DOWN: BRASS
 - FINISH
PIN
UNDER PLATING: 0.5um MIN. Ni
CONTACT AREA: 1.27um MIN. GOLD
SOLDER AREA: 2.5um MIN. PURE Sn
HOLD DOWN: 2.5um MIN. PURE Sn
 - THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008
 - PRODUCT SPEC: 110-263

spec ref				dr	Su-Hua Miao	2012/05/22	projection 	MM 	size	A4	scale	1.000	
tolerance std ISO1101 ISO406	TOLERANCES UNLESS OTHERWISE SPECIFIED			eng	Su-Hua Miao	2012/06/04			ecn no				-
				chr	-	-			rel level				Released
				appr		Rick Bian			2012/06/04	product family		-	
surface ISO1302	linear	0.X	±0.3		title 68 POS EJECTOR HEADER ASSY FOR 5V APPLICATION			dwg no	10119103			rev A	
		0.XX	±0.13										
		0.XXX	±0.05										
	angular	0°	±2°	www.fci.com	cat. no.		-	Product - Customer Drw			sheet 3 of 3		

PrintE File - REV C - 2009-06-09