


## Slide DIP Switch

## A6TN

**Knife-edge Structure with High Contact Pressure Mechanism Assures High reliability**

- Knife-edge structure enables washing without seal.
- Improved solder heat resistance (peak solder temperature: 265 °C).



RoHS Compliant



**NEW**

### ■ List of Models

Tube packaging type

Type and color of actuator		Flat actuator (white)	Raised actuator (white)
No. of poles	Quantity per tube		
1	100	A6TN-1101	A6TN-1104
2	60	A6TN-2101	A6TN-2104
3	45	A6TN-3101	A6TN-3104
4	35	A6TN-4101	A6TN-4104
5	30	A6TN-5101	A6TN-5104
6	25	A6TN-6101	A6TN-6104
7	20	A6TN-7101	A6TN-7104
8	20	A6TN-8101	A6TN-8104
9	15	A6TN-9101	A6TN-9104
10	15	A6TN-0101	A6TN-0104




**Note:** Order in multiples of the package quantity.

### ■ Ratings/Characteristics


<b>Rating</b>	25 mA at 24 VDC, 10 μA (minimum current) at 3.5 VDC
<b>Ambient operating temperature</b>	-30 to +85 °C at 60% max. (with no icing or condensation)
<b>Ambient operating humidity</b>	35% to 95% (at +5 to +35 °C)
<b>Insulation resistance</b>	100 MΩ min. (at 100 VDC)
<b>Contact resistance</b>	200 mΩ max. (initial value)
<b>Dielectric strength</b>	300 VAC for 1 min between terminals
<b>Vibration resistance</b>	Malfunction: 10 to 55 Hz, 1.5-mm double amplitude
<b>Shock resistance</b>	Malfunction: 490 m/s <sup>2</sup> min.
<b>Durability</b>	Electrical: 1,000 operations min.
<b>Operating force</b>	0.98 to 7.9 N {100 to 806 gf}
<b>Weight</b>	0.31 g (2 poles) 0.58 g (4 poles) 0.84 g (6 poles) 1.1 g (8 poles) 1.36 g (10 poles)

## ■ Dimensions (Unit: mm)




### Flat actuator A6TN-□101




1 pole type



### Raised actuator A6TN-□104



Raised actuator




Flat actuator

No. of poles	Models		A
	Flat actuator	Raised actuator	
1	A6TN-1101	A6TN-1104	4.48
2	A6TN-2101	A6TN-2104	7.0
3	A6TN-3101	A6TN-3104	9.6
4	A6TN-4101	A6TN-4104	12.1
5	A6TN-5101	A6TN-5104	14.6
6	A6TN-6101	A6TN-6104	17.2
7	A6TN-7101	A6TN-7104	19.7
8	A6TN-8101	A6TN-8104	22.3
9	A6TN-9101	A6TN-9104	24.8
10	A6TN-0101	A6TN-0104	27.3

**Note:** Unless otherwise specified, a tolerance of  $\pm 0.4$  mm applies to all dimensions.

## ■ Internal Connection

### Contact Form (Top View)



## ■ Precautions

Be sure to read the Safety precautions common to all DIP Switches for correct use.

- Application examples provided in this document are for reference only. In actual applications, confirm equipment functions and safety before using the product.
- Consult your OMRON representative before using the product under conditions which are not described in the manual or applying the product to nuclear control systems, railroad systems, aviation systems, vehicles, combustion systems, medical equipment, amusement machines, safety equipment, and other systems or equipment that may have a serious influence on lives and property if used improperly. Make sure that the ratings and performance characteristics of the product provide a margin of safety for the system or equipment, and be sure to provide the system or equipment with double safety mechanisms.

**Note:** Do not use this document to operate the Unit.

**OMRON Corporation**

ELECTRONIC AND MECHANICAL COMPONENTS COMPANY

Contact: [www.omron.com/ecb](http://www.omron.com/ecb)

Cat. No. A194-E1-03  
0812(0207)(O)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Omron:

[A6TN-2101](#) [A6TN-4101](#) [A6TN-6101](#) [A6TN-8101](#) [A6TN-2104](#) [A6TN-4104](#) [A6TN-6104](#) [A6TN-8104](#) [A6TN-0101](#)  
[A6TN-0104](#) [A6TN-1101](#) [A6TN-1104](#) [A6TN-3101](#) [A6TN-3104](#) [A6TN-5101](#) [A6TN-5104](#) [A6TN-7101](#) [A6TN-7104](#)  
[A6TN-9101](#) [A6TN-9104](#)