

Straight Brushstrip in Aluminium Carrier (90° flange)

Type 25 Straight brushstrip in 90° flanged carrier, is available in a range of standard sizes or manufactured to customer specification. The 90° angle is particularly useful for accomodating sliding components such as hangar door sections or the tops of roller shutter doors.



Standard range

Available in 3000mm lengths, this selection, as shown in the opposite table, can also be supplied cut to length and re-trimmed to customer specification. All sections are filled in Nylon 6, a hard wearing material, temperature resistant from -40°C to 100°C.



How to specify Type 25 products

Part number
(if standard):
Section Code:
Filling material:
Brush Height (BH):
Carrier Code:
Overall length (A):



Special Manufacture

BRUSHSTRIP DIMENSIONS AND TOLERANCES								FILLING MATERIALS					
BRUSH SECTION CODE	CARRIER CODE	CARRIER DIMENSIONS				OVERALL LENGTH	BRUSH TRIM	SYNTHETIC		STEEL WIRE		PHOS. BRONZE NICKEL SILVER BRASS	
		S	T	U	V			(Min)	(Max)	(Min)	(Max)	(Min)	(Max)
M1	EA082	3.70	4.00	13.10	1.00	Up to 100 ±0.50	Up to 38 (max) ±0.50	0.06	0.20	0.06		0.06	
M2	EA082	3.70	4.00	13.10	1.00			0.06	0.20	0.06		0.06	
A1	EA058	5.20	5.60	14.00	1.40			0.06	0.25	0.06	0.11	0.06	0.13
A2	EA058	5.20	5.60	14.00	1.40			0.06	0.25	0.06	0.11	0.06	0.13
A4	EA058	5.20	5.60	14.00	1.40	101 - 1000 ±1.00	Up to 130 ±1.00	0.06	0.20				
B1	EA054	6.50	6.70	17.50	1.60			0.06	0.35	0.06	0.13	0.06	0.19
B2	EA054	6.50	6.70	17.50	1.60			0.06	0.35	0.06	0.13	0.06	0.19
B4	EA054	6.50	6.70	17.50	1.60			0.06	0.25				
C1	EA061	8.10	8.40	22.00	1.80	101 - 1000 ±1.00	131 - 300 ±1.50	0.06	0.40	0.06	0.19	0.06	0.25
C2	EA061	8.10	8.40	22.00	1.80			0.06	0.40	0.06	0.19	0.06	0.25
D1	EA052	10.00	11.20	27.00	1.90			0.06	0.50	0.06	0.25	0.06	0.29
D2	EA052	10.00	11.20	27.00	1.90			0.06	0.50	0.06	0.25	0.06	0.29
E1	EA057	10.50	11.80	29.00	1.90	1001 - 3000 ±1.50	Over 300 ±2.00	0.06	0.60	0.06	0.29	0.06	0.34
E2	EA057	10.50	11.80	29.00	1.90			0.06	0.60	0.06	0.29	0.06	0.34
G1	EA035	13.50	14.50	35.00	2.00			0.06	0.90	0.06	0.34	0.06	0.46
G2	EA035	13.50	14.50	35.00	2.00			0.06	0.90	0.06	0.34	0.06	0.46
H1	EA079	17.90	18.10	67.90	3.00	1001 - 3000 ±1.50	Over 300 ±2.00	0.06	2.00	0.06	0.46	0.06	0.56
H2	EA079	17.90	18.10	67.90	3.00			0.06	2.00	0.06	0.46	0.06	0.56

Section codes

Nominal size: M-H

1: Electroplated mild steel (Galvanised)

2: Stainless steel (AISI 304)

4: Aluminium

Refer to page 6 for section dimensions.

Tolerances shown are standard.

Tighter tolerances can be achieved on request.

(Dimensions are in mm).

(Illustrations are approximately full size).