







PART NUMBER 10106262-5206002LF




spec ref	*			
tolerance std	TOLERANCES UNLESS OTHERWISE SPECIFIED			
ASME Y14.5				
surface	linear	0.X	±0.5	
		0.XX	±0.25	
		0.XXX	±0.10	
ASME Y14.5	angular	0°	±2°	

dr	Peng-Bing Fu	2012/03/01		projection		size	A3	scale	3:2
eng	Peng-Bing Fu	2012/11/13				ecn no	ELX-DG-013147-1		
chr	Shao-Qi Kuang	2012/11/13				rel level	Released		
appr	Pei-Ming Zheng	2012/11/13	product family			PwrBlade+			
			title			5HP + 2LP + 24S			rev
			RA SOLDER HEADER			dwg no			B
www.fci.com			cat. no.			Product - Customer Drw			sheet 1 of 3

PRODUCT NO.	ROWS	HIGH POWER						LP		SIGNAL						E2
		E1	P1	P2	P3	P4	P5	LP1	LP2	1	2	3	4	5	6	
10106262-5206002LF	D C B A		H1	H1	H1	H1	H1	LJ	LJ	U	U	U	U	U	U	
										T	T	T	T	G	G	
										S	S	S	S	S	S	
										R	R	L	R	E	E	

CODE	DESCRIPTION
E	MLBF SIGNAL CONTACT, ROW A (3.43)
G	MLBF SIGNAL CONTACT, ROW C (3.43)
HI	STD HIGH POWER CONTACT (3.43)
LJ	MFBL LOW POWER CONTACT (3.43)
R	STD SIGNAL CONTACT, ROW A (3.43)
RL	MFBL SIGNAL CONTACT, ROW A (3.43)
S	STD SIGNAL CONTACT, ROW B (3.43)
SL	MFBL SIGNAL CONTACT, ROW B (3.43)
T	STD SIGNAL CONTACT, ROW C (3.43)
TL	MFBL SIGNAL CONTACT, ROW C (3.43)
U	STD SIGNAL CONTACT, ROW D (3.43)
UL	MFBL SIGNAL CONTACT, ROW D (3.43)



dr	Peng-Bing Fu	2012/03/01	projection	MM	size	A3	scale	3:2
eng	Peng-Bing Fu	2012/11/13			ecn no	ELX-DG-013147-1		
chr	Shao-Qi Kuang	2012/11/13						
appr	Pei-Ming Zheng	2012/11/13	product family	PwrBlade+	rel level	Released		
www.fci.com			title			5HP + 2LP + 24S		rev
			RA SOLDER HEADER			dwg no		B
						10106262-5206002		
cat. no.			Product - Customer Drw			sheet 2 of 3		

A

B

C

D

A

B

C



D

NOTES:

- 1) "FCI", PART NUMBER AND DATE CODE TO BE MARKED ON THIS SURFACE.
THE P/N CAN BE OMITTED IF THERE IS NOT ENOUGH SPACE ON THIS SURFACE.
- 2) MATERIALS:
-HOUSING - GLASS FILLED WITH HIGH TEMP THERMOPLASTIC, UL94V-0.
-SIGNAL CONTACT - COPPER ALLOY.
-POWER CONTACT - HIGH CONDUCTIVITY COPPER ALLOY.
- 3) PLATING SPECIFICATION REFER TO FCI 10116351
- 4) DENOTES CONNECTOR KEEP OUT ZONE.
- 5) DATUM AND BASIC DIMENIONS WERE ESTABLISHED BY CUSTOMER.
- 6) ALL HOLE DIAMETERS ARE FINISHED HOLE SIZES.
- 7) 1.15 ± 0.025 MM DRILLED HOLE PLATED WITH 0.00762MM MIN Sn
OVER 0.0254-0.0762MM Cu PLATING TO ACHIEVE A 1.02 ± 0.07 MM HOLE.
- 8) PRODUCT SPECIFICATION REFER TO FCI GS-12-658.
APPLICATION SPECIFICATION REFER TO FCI GS-20-141.
PRODUCT PACKAGED IN TRAYS, REFER TO FCI GS-14-1502.
- 9) A  SYMBOL WILL BE NEXT TO ANY DIMENSION,VIEW,OR NOTE WHICH HAS BEEN
MODIFIED WITH THE CURRENT DRAWING REVISION.



Copyright FCI.

dr	Peng-Bing Fu	2012/03/01	projection 	MM 	size	scale
eng	Peng-Bing Fu	2012/11/13			A3	3:2
chr	Shao-Qi Kuang	2012/11/13			ecn no	ELX-DG-013147-1
appr	Pei-Ming Zheng	2012/11/13	product family	PwrBlade+	rel level	Released
		5HP + 2LP + 24S			dwg no	rev
www.fci.com		RA SOLDER HEADER			10106262-5206002	B
cat. no.			Product - Customer Drw			sheet 3 of 3