


## Miniature Basic Switch

## D3V

### Reliable Basic Switch with External Lever

- Available by 21 A, 16 A, 11 A, 6 A and 0.1 A models, all with self-cleaning contacts.
- Available with internally or externally fitted levers, and 2 fixing positions for external levers.

RoHS Compliant



## Ordering Information

### Model Number Legend

D3V-□□□□-□□□□-□□□  
1 2 3 4 5 6 7 8 9

#### 1. Ratings

21: 20 (4) A at 250 VAC  
16: 16 (3) A at 250 VAC  
11: 11 (3) A at 250 VAC  
6: 6 (2) A at 250 VAC  
01: 0.1 A at 125 VAC

#### 2. Contact Gap

None: 1 mm (F gap)  
G: 0.5 mm (G gap)

#### 3. Actuator

None: Pin plunger  
1: Short hinge lever  
2: Hinge lever  
3: Long hinge lever  
4: Simulated roller lever  
5: Short hinge roller lever  
6: Hinge roller lever

#### 4. Hinge Position

None: Internal/Far from plunger  
M: External/Far from plunger  
K: External/Near plunger

#### 5. Contact Form

1: SPDT  
2: SPST-NC  
3: SPST-NO

#### 6. Terminals

A: Solder terminals  
C2: Quick-connect terminals (#187)  
C: Quick-connect terminals (#250)

#### 7. Maximum Operating Force

5: 1.96 N {200 gf}  
4A: 1.23 N {125 gf}  
4: 0.98 N {100 gf}  
3: 0.49 N {50 gf}  
2: 0.25 N {25 gf}

**Note:** These values are for the pin plunger models.

#### 8. Mounting Hole Size

None: 3.1 mm  
K: 2.9 mm


#### 9. Special Code

None: Standard  
H: High temperature (125°C) (See note)  
E: Special rating: 21 (8) A

**Note:** Consult your OMRON sales representative for high temperature models.

## List of Models

- 21 A (OF: 1.23 N {125 gf})

| Actuator                                                                                                   | Hinge position | Maximum Operating Force (OF) | Contact form     |                  |                  |
|------------------------------------------------------------------------------------------------------------|----------------|------------------------------|------------------|------------------|------------------|
|                                                                                                            |                |                              | SPDT             | SPST-NC          | SPST-NO          |
| Pin plunger               | ---            | 1.23N {125gf}                | D3V-21G-1□4A-Δ   | D3V-21G-2□4A-Δ   | D3V-21G-3□4A-Δ   |
| Short hinge lever         | Internal       | 1.23N {125gf}                | D3V-21G1-1□4A-Δ  | D3V-21G1-2□4A-Δ  | D3V-21G1-3□4A-Δ  |
|                                                                                                            | M              |                              | D3V-21G1M-1□4A-Δ | D3V-21G1M-2□4A-Δ | D3V-21G1M-3□4A-Δ |
| Hinge lever               | Internal       | 0.78N {80gf}                 | D3V-21G2-1□4A-Δ  | D3V-21G2-2□4A-Δ  | D3V-21G2-3□4A-Δ  |
|                                                                                                            | M              |                              | D3V-21G2M-1□4A-Δ | D3V-21G2M-2□4A-Δ | D3V-21G2M-3□4A-Δ |
| Long hinge lever          | Internal       | 0.44N {45gf}                 | D3V-21G3-1□4A-Δ  | D3V-21G3-2□4A-Δ  | D3V-21G3-3□4A-Δ  |
|                                                                                                            | M              |                              | D3V-21G3M-1□4A-Δ | D3V-21G3M-2□4A-Δ | D3V-21G3M-3□4A-Δ |
| Simulated roller lever    | Internal       | 0.83N {85gf}                 | D3V-21G4-1□4A-Δ  | D3V-21G4-2□4A-Δ  | D3V-21G4-3□4A-Δ  |
|                                                                                                            | M              |                              | D3V-21G4M-1□4A-Δ | D3V-21G4M-2□4A-Δ | D3V-21G4M-3□4A-Δ |
| Short hinge roller lever  | Internal       | 1.42N {145gf}                | D3V-21G5-1□4A-Δ  | D3V-21G5-2□4A-Δ  | D3V-21G5-3□4A-Δ  |
|                                                                                                            | M              |                              | D3V-21G5M-1□4A-Δ | D3V-21G5M-2□4A-Δ | D3V-21G5M-3□4A-Δ |
| Hinge roller lever        | Internal       | 0.79N {80gf}                 | D3V-21G6-1□4A-Δ  | D3V-21G6-2□4A-Δ  | D3V-21G6-3□4A-Δ  |
|                                                                                                            | M              |                              | D3V-21G6M-1□4A-Δ | D3V-21G6M-2□4A-Δ | D3V-21G6M-3□4A-Δ |

**Note:** The □ in the model number is for the terminal code.  
 C: Quick-connect terminals (#250)  
 The Δ in the model number is for the mounting hole size.  
 None: 3.1 mm  
 K: 2.9 mm

- 16 A (OF: 1.96 N {200 gf})

| Actuator                                                                                                     | Hinge position | Maximum Operating Force (OF) | Contact form   |                |                |
|--------------------------------------------------------------------------------------------------------------|----------------|------------------------------|----------------|----------------|----------------|
|                                                                                                              |                |                              | SPDT           | SPST-NC        | SPST-NO        |
| Pin plunger               | ---            | 1.96N {200gf}                | D3V-16-1□5-Δ   | D3V-16-2□5-Δ   | D3V-16-3□5-Δ   |
| Short hinge lever         | Internal       | 1.96N {200gf}                | D3V-161-1□5-Δ  | D3V-161-2□5-Δ  | D3V-161-3□5-Δ  |
|                                                                                                              | M              |                              | D3V-161M-1□5-Δ | D3V-161M-2□5-Δ | D3V-161M-3□5-Δ |
| Hinge lever               | Internal       | 1.23N {125gf}                | D3V-162-1□5-Δ  | D3V-162-2□5-Δ  | D3V-162-3□5-Δ  |
|                                                                                                              | M              |                              | D3V-162M-1□5-Δ | D3V-162M-2□5-Δ | D3V-162M-3□5-Δ |
| Long hinge lever          | Internal       | 0.69N {70gf}                 | D3V-163-1□5-Δ  | D3V-163-2□5-Δ  | D3V-163-3□5-Δ  |
|                                                                                                              | M              |                              | D3V-163M-1□5-Δ | D3V-163M-2□5-Δ | D3V-163M-3□5-Δ |
| Simulated roller lever    | Internal       | 1.23N {125gf}                | D3V-164-1□5-Δ  | D3V-164-2□5-Δ  | D3V-164-3□5-Δ  |
|                                                                                                              | M              |                              | D3V-164M-1□5-Δ | D3V-164M-2□5-Δ | D3V-164M-3□5-Δ |
| Short hinge roller lever  | Internal       | 2.35N {240gf}                | D3V-165-1□5-Δ  | D3V-165-2□5-Δ  | D3V-165-3□5-Δ  |
|                                                                                                              | M              |                              | D3V-165M-1□5-Δ | D3V-165M-2□5-Δ | D3V-165M-3□5-Δ |
| Hinge roller lever        | Internal       | 1.23N {125gf}                | D3V-166-1□5-Δ  | D3V-166-2□5-Δ  | D3V-166-3□5-Δ  |
|                                                                                                              | M              |                              | D3V-166M-1□5-Δ | D3V-166M-2□5-Δ | D3V-166M-3□5-Δ |

**Note:** The □ in the model number is for the terminal code.  
 A: Solder terminals  
 C2: Quick-connect terminals (#187)  
 C: Quick-connect terminals (#250)  
 The Δ in the model number is for the mounting hole size.  
 None: 3.1 mm  
 K: 2.9 mm

- 16 A (OF: 0.98 N {100 gf})

| Actuator                                                                                                   | Hinge position | Maximum Operating Force (OF) | Contact form   |                |                |
|------------------------------------------------------------------------------------------------------------|----------------|------------------------------|----------------|----------------|----------------|
|                                                                                                            |                |                              | SPDT           | SPST-NC        | SPST-NO        |
| Pin plunger               | ---            | 0.98N {100gf}                | D3V-16-1□4-Δ   | D3V-16-2□4-Δ   | D3V-16-3□4-Δ   |
| Short hinge lever         | Internal       | 0.98N {100gf}                | D3V-161-1□4-Δ  | D3V-161-2□4-Δ  | D3V-161-3□4-Δ  |
|                                                                                                            | M              |                              | D3V-161M-1□4-Δ | D3V-161M-2□4-Δ | D3V-161M-3□4-Δ |
| Hinge lever               | Internal       | 0.59N {60gf}                 | D3V-162-1□4-Δ  | D3V-162-2□4-Δ  | D3V-162-3□4-Δ  |
|                                                                                                            | M              |                              | D3V-162M-1□4-Δ | D3V-162M-2□4-Δ | D3V-162M-3□4-Δ |
| Long hinge lever          | Internal       | 0.34N {35gf}                 | D3V-163-1□4-Δ  | D3V-163-2□4-Δ  | D3V-163-3□4-Δ  |
|                                                                                                            | M              |                              | D3V-163M-1□4-Δ | D3V-163M-2□4-Δ | D3V-163M-3□4-Δ |
| Simulated roller lever    | Internal       | 0.59N {60gf}                 | D3V-164-1□4-Δ  | D3V-164-2□4-Δ  | D3V-164-3□4-Δ  |
|                                                                                                            | M              |                              | D3V-164M-1□4-Δ | D3V-164M-2□4-Δ | D3V-164M-3□4-Δ |
| Short hinge roller lever  | Internal       | 1.18N {120gf}                | D3V-165-1□4-Δ  | D3V-165-2□4-Δ  | D3V-165-3□4-Δ  |
|                                                                                                            | M              |                              | D3V-165M-1□4-Δ | D3V-165M-2□4-Δ | D3V-165M-3□4-Δ |
| Hinge roller lever        | Internal       | 0.59N {60gf}                 | D3V-166-1□4-Δ  | D3V-166-2□4-Δ  | D3V-166-3□4-Δ  |
|                                                                                                            | M              |                              | D3V-166M-1□4-Δ | D3V-166M-2□4-Δ | D3V-166M-3□4-Δ |

- 11 A (OF: 1.96 N {200 gf})

| Actuator                                                                                                     | Hinge position | Maximum Operating Force (OF) | Contact form   |                |                |
|--------------------------------------------------------------------------------------------------------------|----------------|------------------------------|----------------|----------------|----------------|
|                                                                                                              |                |                              | SPDT           | SPST-NC        | SPST-NO        |
| Pin plunger                 | ---            | 1.96N {200gf}                | D3V-11-1□5-Δ   | D3V-11-2□5-Δ   | D3V-11-3□5-Δ   |
| Short hinge lever           | Internal       | 1.96N {200gf}                | D3V-111-1□5-Δ  | D3V-111-2□5-Δ  | D3V-111-3□5-Δ  |
|                                                                                                              | M              |                              | D3V-111M-1□5-Δ | D3V-111M-2□5-Δ | D3V-111M-3□5-Δ |
| Hinge lever               | Internal       | 1.23N {125gf}                | D3V-112-1□5-Δ  | D3V-112-2□5-Δ  | D3V-112-3□5-Δ  |
|                                                                                                              | M              |                              | D3V-112M-1□5-Δ | D3V-112M-2□5-Δ | D3V-112M-3□5-Δ |
| Long hinge lever          | Internal       | 0.69N {70gf}                 | D3V-113-1□5-Δ  | D3V-113-2□5-Δ  | D3V-113-3□5-Δ  |
|                                                                                                              | M              |                              | D3V-113M-1□5-Δ | D3V-113M-2□5-Δ | D3V-113M-3□5-Δ |
| Simulated roller lever    | Internal       | 1.23N {125gf}                | D3V-114-1□5-Δ  | D3V-114-2□5-Δ  | D3V-114-3□5-Δ  |
|                                                                                                              | M              |                              | D3V-114M-1□5-Δ | D3V-114M-2□5-Δ | D3V-114M-3□5-Δ |
| Short hinge roller lever  | Internal       | 2.35N {240gf}                | D3V-115-1□5-Δ  | D3V-115-2□5-Δ  | D3V-115-3□5-Δ  |
|                                                                                                              | M              |                              | D3V-115M-1□5-Δ | D3V-115M-2□5-Δ | D3V-115M-3□5-Δ |
| Hinge roller lever        | Internal       | 1.23N {125gf}                | D3V-116-1□5-Δ  | D3V-116-2□5-Δ  | D3V-116-3□5-Δ  |
|                                                                                                              | M              |                              | D3V-116M-1□5-Δ | D3V-116M-2□5-Δ | D3V-116M-3□5-Δ |

**Note:** The □ in the model number is for the terminal code.

A: Solder terminals

C2: Quick-connect terminals (#187)

C: Quick-connect terminals (#250)

The Δ in the model number is for the mounting hole size.

None: 3.1 mm

K: 2.9 mm

- 11 A (OF: 0.98 N {100 gf})

| Actuator                                                                                                   | Hinge position | Maximum Operating Force (OF) | Contact form   |                |                |
|------------------------------------------------------------------------------------------------------------|----------------|------------------------------|----------------|----------------|----------------|
|                                                                                                            |                |                              | SPDT           | SPST-NC        | SPST-NO        |
| Pin plunger               | ---            | 0.98N {100gf}                | D3V-11-1□4-Δ   | D3V-11-2□4-Δ   | D3V-11-3□4-Δ   |
| Short hinge lever         | Internal       | 0.98N {100gf}                | D3V-111-1□4-Δ  | D3V-111-2□4-Δ  | D3V-111-3□4-Δ  |
|                                                                                                            | M              |                              | D3V-111M-1□4-Δ | D3V-111M-2□4-Δ | D3V-111M-3□4-Δ |
| Hinge lever               | Internal       | 0.59N {60gf}                 | D3V-112-1□4-Δ  | D3V-112-2□4-Δ  | D3V-112-3□4-Δ  |
|                                                                                                            | M              |                              | D3V-112M-1□4-Δ | D3V-112M-2□4-Δ | D3V-112M-3□4-Δ |
| Long hinge lever          | Internal       | 0.34N {35gf}                 | D3V-113-1□4-Δ  | D3V-113-2□4-Δ  | D3V-113-3□4-Δ  |
|                                                                                                            | M              |                              | D3V-113M-1□4-Δ | D3V-113M-2□4-Δ | D3V-113M-3□4-Δ |
| Simulated roller lever    | Internal       | 0.59N {60gf}                 | D3V-114-1□4-Δ  | D3V-114-2□4-Δ  | D3V-114-3□4-Δ  |
|                                                                                                            | M              |                              | D3V-114M-1□4-Δ | D3V-114M-2□4-Δ | D3V-114M-3□4-Δ |
| Short hinge roller lever  | Internal       | 1.18N {120gf}                | D3V-115-1□4-Δ  | D3V-115-2□4-Δ  | D3V-115-3□4-Δ  |
|                                                                                                            | M              |                              | D3V-115M-1□4-Δ | D3V-115M-2□4-Δ | D3V-115M-3□4-Δ |
| Hinge roller lever        | Internal       | 0.59N {60gf}                 | D3V-116-1□4-Δ  | D3V-116-2□4-Δ  | D3V-116-3□4-Δ  |
|                                                                                                            | M              |                              | D3V-116M-1□4-Δ | D3V-116M-2□4-Δ | D3V-116M-3□4-Δ |

**Note:** The □ in the model number is for the terminal code.

A: Solder terminals

C2: Quick-connect terminals (#187)

C: Quick-connect terminals (#250)

The Δ in the model number is for the mounting hole size.

None: 3.1 mm

K: 2.9 mm

• 6 A (OF: 0.98 N {100 gf})

| Actuator                                                                                                   | Hinge position | Maximum Operating Force (OF) | Contact form  |               |               |
|------------------------------------------------------------------------------------------------------------|----------------|------------------------------|---------------|---------------|---------------|
|                                                                                                            |                |                              | SPDT          | SPST-NC       | SPST-NO       |
| Pin plunger               | ---            | 0.98N {100gf}                | D3V-6-1□4-Δ   | D3V-6-2□4-Δ   | D3V-6-3□4-Δ   |
| Short hinge lever         | Internal       | 0.98N {100gf}                | D3V-61-1□4-Δ  | D3V-61-2□4-Δ  | D3V-61-3□4-Δ  |
|                                                                                                            | M              |                              | D3V-61M-1□4-Δ | D3V-61M-2□4-Δ | D3V-61M-3□4-Δ |
| Hinge lever               | Internal       | 0.59N {60gf}                 | D3V-62-1□4-Δ  | D3V-62-2□4-Δ  | D3V-62-3□4-Δ  |
|                                                                                                            | M              |                              | D3V-62M-1□4-Δ | D3V-62M-2□4-Δ | D3V-62M-3□4-Δ |
| Long hinge lever          | Internal       | 0.34N {35gf}                 | D3V-63-1□4-Δ  | D3V-63-2□4-Δ  | D3V-63-3□4-Δ  |
|                                                                                                            | M              |                              | D3V-63M-1□4-Δ | D3V-63M-2□4-Δ | D3V-63M-3□4-Δ |
| Simulated roller lever    | Internal       | 0.59N {60gf}                 | D3V-64-1□4-Δ  | D3V-64-2□4-Δ  | D3V-64-3□4-Δ  |
|                                                                                                            | M              |                              | D3V-64M-1□4-Δ | D3V-64M-2□4-Δ | D3V-64M-3□4-Δ |
| Short hinge roller lever  | Internal       | 1.18N {120gf}                | D3V-65-1□4-Δ  | D3V-65-2□4-Δ  | D3V-65-3□4-Δ  |
|                                                                                                            | M              |                              | D3V-65M-1□4-Δ | D3V-65M-2□4-Δ | D3V-65M-3□4-Δ |
| Hinge roller lever        | Internal       | 0.59N {60gf}                 | D3V-66-1□4-Δ  | D3V-66-2□4-Δ  | D3V-66-3□4-Δ  |
|                                                                                                            | M              |                              | D3V-66M-1□4-Δ | D3V-66M-2□4-Δ | D3V-66M-3□4-Δ |

• 6 A (OF: 0.49 N {50 gf})

| Actuator                                                                                                     | Hinge position | Maximum Operating Force (OF) | Contact form   |                |                |
|--------------------------------------------------------------------------------------------------------------|----------------|------------------------------|----------------|----------------|----------------|
|                                                                                                              |                |                              | SPDT           | SPST-NC        | SPST-NO        |
| Pin plunger                 | ---            | 0.49N {50gf}                 | D3V-6G-1□3-Δ   | D3V-6G-2□3-Δ   | D3V-6G-3□3-Δ   |
| Short hinge lever           | Internal       | 0.49N {50gf}                 | D3V-6G1-1□3-Δ  | D3V-6G1-2□3-Δ  | D3V-6G1-3□3-Δ  |
|                                                                                                              | M              |                              | D3V-6G1M-1□3-Δ | D3V-6G1M-2□3-Δ | D3V-6G1M-3□3-Δ |
| Hinge lever               | Internal       | 0.59N {60gf}                 | D3V-6G2-1□3-Δ  | D3V-6G2-2□3-Δ  | D3V-6G2-3□3-Δ  |
|                                                                                                              | M              |                              | D3V-6G2M-1□3-Δ | D3V-6G2M-2□3-Δ | D3V-6G2M-3□3-Δ |
| Long hinge lever          | Internal       | 0.20N {20gf}                 | D3V-6G3-1□3-Δ  | D3V-6G3-2□3-Δ  | D3V-6G3-3□3-Δ  |
|                                                                                                              | M              |                              | D3V-6G3M-1□3-Δ | D3V-6G3M-2□3-Δ | D3V-6G3M-3□3-Δ |
| Simulated roller lever    | Internal       | 0.29N {30gf}                 | D3V-6G4-1□3-Δ  | D3V-6G4-2□3-Δ  | D3V-6G4-3□3-Δ  |
|                                                                                                              | M              |                              | D3V-6G4M-1□3-Δ | D3V-6G4M-2□3-Δ | D3V-6G4M-3□3-Δ |
| Short hinge roller lever  | Internal       | 0.59N {60gf}                 | D3V-6G5-1□3-Δ  | D3V-6G5-2□3-Δ  | D3V-6G5-3□3-Δ  |
|                                                                                                              | M              |                              | D3V-6G5M-1□3-Δ | D3V-6G5M-2□3-Δ | D3V-6G5M-3□3-Δ |
| Hinge roller lever        | Internal       | 0.29N {30gf}                 | D3V-6G6-1□3-Δ  | D3V-6G6-2□3-Δ  | D3V-6G6-3□3-Δ  |
|                                                                                                              | M              |                              | D3V-6G6M-1□3-Δ | D3V-6G6M-2□3-Δ | D3V-6G6M-3□3-Δ |

**Note:** The □ in the model number is for the terminal code.

A: Solder terminals

C2: Quick-connect terminals (#187)

C: Quick-connect terminals (#250)

The Δ in the model number is for the mounting hole size.

None: 3.1 mm

K: 2.9 mm

- 0.1 A (OF: 0.49 N {50 gf})

| Actuator                                                                                                   | Hinge position | Maximum Operating Force (OF) | Contact form   |                |                |
|------------------------------------------------------------------------------------------------------------|----------------|------------------------------|----------------|----------------|----------------|
|                                                                                                            |                |                              | SPDT           | SPST-NC        | SPST-NO        |
| Pin plunger               | ---            | 0.49N {50gf}                 | D3V-01-1□3-Δ   | D3V-01-2□3-Δ   | D3V-01-3□3-Δ   |
| Short hinge lever         | Internal       | 0.49N {50gf}                 | D3V-011-1□3-Δ  | D3V-011-2□3-Δ  | D3V-011-3□3-Δ  |
|                                                                                                            | M              |                              | D3V-011M-1□3-Δ | D3V-011M-2□3-Δ | D3V-011M-3□3-Δ |
| Hinge lever               | Internal       | 0.29N {30gf}                 | D3V-012-1□3-Δ  | D3V-012-2□3-Δ  | D3V-012-3□3-Δ  |
|                                                                                                            | M              |                              | D3V-012M-1□3-Δ | D3V-012M-2□3-Δ | D3V-012M-3□3-Δ |
| Long hinge lever          | Internal       | 0.20N {20gf}                 | D3V-013-1□3-Δ  | D3V-013-2□3-Δ  | D3V-013-3□3-Δ  |
|                                                                                                            | M              |                              | D3V-013M-1□3-Δ | D3V-013M-2□3-Δ | D3V-013M-3□3-Δ |
| Simulated roller lever    | Internal       | 0.29N {30gf}                 | D3V-014-1□3-Δ  | D3V-014-2□3-Δ  | D3V-014-3□3-Δ  |
|                                                                                                            | M              |                              | D3V-014M-1□3-Δ | D3V-014M-2□3-Δ | D3V-014M-3□3-Δ |
| Short hinge roller lever  | Internal       | 0.59N {60gf}                 | D3V-015-1□3-Δ  | D3V-015-2□3-Δ  | D3V-015-3□3-Δ  |
|                                                                                                            | M              |                              | D3V-015M-1□3-Δ | D3V-015M-2□3-Δ | D3V-015M-3□3-Δ |
| Hinge roller lever        | Internal       | 0.29N {30gf}                 | D3V-016-1□3-Δ  | D3V-016-2□3-Δ  | D3V-016-3□3-Δ  |
|                                                                                                            | M              |                              | D3V-016M-1□3-Δ | D3V-016M-2□3-Δ | D3V-016M-3□3-Δ |

- 0.1 A (OF: 0.25 N {25 gf})

| Actuator                                                                                      | Hinge position | Maximum Operating Force (OF) | Contact form |              |              |
|-----------------------------------------------------------------------------------------------|----------------|------------------------------|--------------|--------------|--------------|
|                                                                                               |                |                              | SPDT         | SPST-NC      | SPST-NO      |
| Pin plunger  | ---            | 0.25N {25gf}                 | D3V-01-1□2-Δ | D3V-01-2□2-Δ | D3V-01-3□2-Δ |

**Note:** The □ in the model number is for the terminal code.

A: Solder terminals

C2: Quick-connect terminals (#187)

C: Quick-connect terminals (#250)

The Δ in the model number is for the mounting hole size.

None: 3.1 mm

K: 2.9 mm

# Specifications

## Ratings

| Model  | Rated voltage | Resistive load |
|--------|---------------|----------------|
| D3V-21 | 250 VAC       | 21 A           |
|        | 125 VDC       | 0.6 A          |
|        | 250 VDC       | 0.3 A          |
| D3V-16 | 250 VAC       | 16 A           |
|        | 125 VDC       | 0.6 A          |
|        | 250 VDC       | 0.3 A          |
| D3V-11 | 250 VAC       | 11 A           |
|        | 125 VDC       | 0.6 A          |
|        | 250 VDC       | 0.3 A          |
| D3V-6  | 250 VAC       | 6 A            |
|        | 125 VDC       | 0.4 A          |
|        | 250 VDC       | 0.3 A          |
| D3V-01 | 125 VAC       | 0.1 A          |
|        | 30 VDC        | 0.1 A          |

- Note:**
1. The above current values are the normal current values of models with a contact gap of 1 mm (gap F), which vary with the normal current values of models with a contact gap of 0.5 mm (gap G).
  2. The ratings values apply under the following test conditions:  
Ambient temperature: 20±2°C  
Ambient humidity: 65±5%  
Operating frequency: 30 operations/min

## Characteristics

|                                                    |                                                                                                                                                                                                                       |
|----------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Permissible operating speed</b>                 | 0.1 mm to 1 m/s (pin plunger models)                                                                                                                                                                                  |
| <b>Permissible operating frequency</b>             | Mechanical: 600 operations/min max.<br>Electrical: 30 operations/min max.                                                                                                                                             |
| <b>Insulation resistance</b>                       | 100 MΩ min. (at 500 VDC)                                                                                                                                                                                              |
| <b>Contact resistance (initial values)</b>         | D3V-21: 50 mΩ max.<br>D3V-16, D3V-11, D3V-6: 30 mΩ max.<br>D3V-01, 0.49 N {50 gf}: 50 mΩ max.<br>0.25 N {25 gf}: 100 mΩ max.                                                                                          |
| <b>Dielectric strength (see note 2)</b>            | 1,000 VAC, 50/60 Hz for 1 min between terminals of the same polarity<br>2,000 VAC, 50/60 Hz for 1 min between current-carrying metal parts and ground, and between each terminal and non-current-carrying metal parts |
| <b>Vibration resistance (see note 3)</b>           | Malfunction: 10 to 55 Hz, 1.5-mm double amplitude                                                                                                                                                                     |
| <b>Shock resistance (see note 3)</b>               | Destruction: 400 m/s <sup>2</sup> {approx. 40G} max.<br>Malfunction: 100 m/s <sup>2</sup> {approx. 10G} max.                                                                                                          |
| <b>Durability (see note 4)</b>                     | Mechanical: 10,000,000 operations min.<br>Electrical: D3V-21: 50,000 operations min.<br>D3V-16: 100,000 operations min.<br>D3V-11: 200,000 operations min.<br>D3V-6, D3V-01: 500,000 operations min.                  |
| <b>Degree of protection</b>                        | IEC IP40                                                                                                                                                                                                              |
| <b>Degree of protection against electric shock</b> | Class I                                                                                                                                                                                                               |
| <b>Proof tracking index (PTI)</b>                  | 250                                                                                                                                                                                                                   |
| <b>Ambient operating temperature</b>               | D3V-21, D3V-01: -25°C to +85°C (at ambient humidity of 60% max.) (with no icing or condensation)<br>D3V-16, D3V-11, D3V-6: -25°C to +105°C (at ambient humidity of 60% max.) (with no icing or condensation)          |
| <b>Ambient operating humidity</b>                  | 85% max. (for 5°C to 35°C)                                                                                                                                                                                            |
| <b>Weight</b>                                      | Approx. 6.2 g (pin plunger models)                                                                                                                                                                                    |

- Note:**
1. The data given above are initial values.
  2. The dielectric strength values shown in the table are for models with a Separator.
  3. For the pin plunger models, the above values apply for use at both the free position and total travel position. For the lever models, they apply at the total travel position.
  4. For testing conditions, contact your OMRON sales representative.

## Approved Standards

Consult your OMRON sales representative for specific models with standard approvals.

### UL1054 (File No. E41515)/CSA C22.2 No.55 (File No. LR21642)

| Rated voltage | D3V-21G | D3V-16       | D3V-16G      | D3V-11       | D3V-11G      | D3V-6       | D3V-6G      | D3V-01 |
|---------------|---------|--------------|--------------|--------------|--------------|-------------|-------------|--------|
| 125 VAC       | ---     | 16 A, 1/2 HP | 16 A, 1/2 HP | 11 A, 1/2 HP | 11 A, 1/2 HP | 6 A, 1/4 HP | 6 A, 1/4 HP | 0.1 A  |
| 250 VAC       | 20.1 A  | 16 A, 1/2 HP | 16 A, 1/2 HP | 11 A, 1/2 HP | 11 A, 1/2 HP | 6 A, 1/4 HP | 6 A, 1/4 HP | ---    |
| 125 VDC       | ---     | 0.6 A        | 0.1 A        | 0.6 A        | 0.1 A        | ---         | ---         | ---    |
| 250 VDC       | ---     | 0.3 A        | ---          | 0.3 A        | ---          | ---         | ---         | ---    |

### EN 61058-1: 1992+A1: 1993 (License No. 40024894)

| Rated voltage | D3V-21G  | D3V-16   | D3V-11   | D3V-6   | D3V-01 |
|---------------|----------|----------|----------|---------|--------|
| 125 VAC       | ---      | ---      | ---      | ---     | 0.1 A  |
| 250 VAC       | 20 (4) A | 16 (3) A | 11 (3) A | 6 (2) A | ---    |

Testing conditions: 5E4 (50,000 operations), T85 (0°C to 85°C) for D3V-21/D3V-01, T105 (0°C to 105°C) for D3V-16/D3V-11/D3V-6

| Rated voltage | D3V-21G  |
|---------------|----------|
| 250 VAC       | 21 (8) A |

Testing conditions: 10,000 operations, T85 (0°C to 85°C)




## Contact Specifications

| Item                               |                      | D3V-21          | D3V-16                                   | D3V-11    | D3V-6     | D3V-01        |
|------------------------------------|----------------------|-----------------|------------------------------------------|-----------|-----------|---------------|
| Contact                            | Specification        | Rivet           |                                          |           |           | Crossbar      |
|                                    | Material             | Silver alloy    |                                          |           |           | Gold alloy    |
|                                    | Gap (standard value) | 0.5 mm          | 1 mm (F gap type) or 0.5 mm (G gap type) |           |           | 1.0 mm        |
| Inrush current                     | NC                   | 50 A max.       | 40 A max.                                | 24 A max. | 15 A max. | ---           |
|                                    | NO                   |                 |                                          |           |           |               |
| Minimum applicable load (see note) |                      | 160 mA at 5 VDC |                                          |           |           | 1 mA at 5 VDC |


**Note:** For more information on the minimum applicable load, refer to *Using Micro Loads* on page 17.

## Contact Form


### SPDT



### SPST-NC



### SPST-NO




## Dimensions

### Terminals

- Note:**
- All units are in millimeters unless otherwise indicated.
  - The table below is for the SPDT contact specifications. Two terminals will be available for SPST-NO or SPST-NC contact specifications. For terminal positions, refer to the above *Contact Form*.

| Solder Terminals(A)                                                   | Quick-connect Terminals (#187) (C2)                      | Quick-connect Terminals (#250) (C)                       |
|-----------------------------------------------------------------------|----------------------------------------------------------|----------------------------------------------------------|
| <p>t = 0.5<br/>Three, solder terminals</p>                            | <p>t = 0.5<br/>Three, quick-connect terminals (#187)</p> | <p>t = 0.8<br/>Three, quick-connect terminals (#250)</p> |
| <p>Note: Indicates the length to the center of the 1.6-dia. holes</p> |                                                          |                                                          |

### Mounting Holes



## Dimensions and Operating Characteristics

- Note:**
1. All units are in millimeters unless otherwise indicated.
  2. Unless otherwise specified, a tolerance of  $\pm 0.4$  mm applies to all dimensions.
  3. The following illustrations and drawings are for quick-connect terminals (#187) (terminals C2). D3V models incorporate terminals A and C. These models are different from #187 models in terminal size only. Terminals A and C are omitted from the following drawings. Refer to *Terminals* on page 9 for these terminals.
  4. The  $\square$  in the model number is for the terminal code.
  5. The  $\Delta$  in the model number is for the mounting hole size.  
The hole size in the following illustrations of models with a suffix "K" in the  $\Delta$  is 2.9 mm.
  6. The operating characteristics are for operation in the A direction (  $\downarrow$  ).

### Pin Plunger Models

D3V-21G-1 $\square$ 4A- $\Delta$

D3V-16-1 $\square$ 5- $\Delta$

D3V-11-1 $\square$ 5- $\Delta$



D3V-11-1 $\square$ 4- $\Delta$

D3V-6-1 $\square$ 4- $\Delta$

D3V-6G-1 $\square$ 3- $\Delta$

D3V-01-1 $\square$ 2- $\Delta$



D3V-01-1 $\square$ 3- $\Delta$



| Model   | D3V-21G-1 $\square$ 4A- $\Delta$ | D3V-16-1 $\square$ 5- $\Delta$<br>D3V-11-1 $\square$ 5- $\Delta$ | D3V-11-1 $\square$ 4- $\Delta$<br>D3V-6-1 $\square$ 4- $\Delta$ | D3V-6G-1 $\square$ 3- $\Delta$ | D3V-01-1 $\square$ 3- $\Delta$ | D3V-01-1 $\square$ 2- $\Delta$ |
|---------|----------------------------------|------------------------------------------------------------------|-----------------------------------------------------------------|--------------------------------|--------------------------------|--------------------------------|
| OF max. | 1.23 N {125 gf}                  | 1.96 N {200 gf}                                                  | 0.98 N {100 gf}                                                 | 0.49 N {50 gf}                 | 0.49 N {50 gf}                 | 0.25 N {25 gf}                 |
| RF min. | 0.20 N {20 gf}                   | 0.49 N {50 gf}                                                   | 0.15 N {15 gf}                                                  | 0.05 N {5 gf}                  | 0.05 N {5 gf}                  | 0.03 N {3 gf}                  |
| PT max. | 1.2 mm                           | 1.2 mm                                                           |                                                                 |                                | 1.2 mm                         |                                |
| OT min. | 1.0 mm                           | 1.0 mm                                                           |                                                                 |                                | 1.0 mm                         |                                |
| MD max. | 0.3 mm                           | 0.4 mm (F gap type) or 0.3 mm (G gap type)                       |                                                                 |                                | 0.4 mm                         |                                |
| OP      | 14.7 $\pm$ 0.4 mm                |                                                                  |                                                                 |                                |                                |                                |


## Short Hinge Lever Models

D3V-21G1-1□4A-Δ  
 D3V-161-1□5-Δ  
 D3V-111-1□5-Δ  
 D3V-111-1□4-Δ  
 D3V-61-1□4-Δ  
 D3V-6G1-1□3-Δ  
 D3V-011-1□3-Δ




| Model   | D3V-21G1-1□4A-Δ | D3V-161-1□5-Δ<br>D3V-111-1□5-Δ             | D3V-111-1□4-Δ<br>D3V-61-1□4-Δ | D3V-6G1-1□3-Δ  | D3V-011-1□3-Δ |
|---------|-----------------|--------------------------------------------|-------------------------------|----------------|---------------|
| OF max. | 1.23 N {125 gf} | 1.96 N {200 gf}                            | 0.98 N {100 gf}               | 0.49 N {50 gf} |               |
| RF min. | 0.20 N {20 gf}  | 0.49 N {50 gf}                             | 0.15 N {15 gf}                | 0.05 N {5 gf}  |               |
| PT max. | 1.6 mm          | 1.6 mm                                     |                               |                | 1.6 mm        |
| OT min. | 0.8 mm          | 0.8 mm                                     |                               |                | 0.8 mm        |
| MD max. | 0.5 mm          | 0.6 mm (F gap type) or 0.5 mm (G gap type) |                               |                | 0.6 mm        |
| OP      | 15.2±0.5 mm     |                                            |                               |                |               |

D3V-21G1M-1□4A-Δ  
 D3V-161M-1□5-Δ  
 D3V-111M-1□5-Δ  
 D3V-111M-1□4-Δ  
 D3V-61M-1□4-Δ  
 D3V-6G1M-1□3-Δ  
 D3V-011M-1□3-Δ



| Model   | D3V-21G1M-1□4A-Δ | D3V-161M-1□5-Δ<br>D3V-111M-1□5-Δ           | D3V-111M-1□4-Δ<br>D3V-61M-1□4-Δ | D3V-6G1M-1□3-Δ | D3V-011M-1□3-Δ |
|---------|------------------|--------------------------------------------|---------------------------------|----------------|----------------|
| OF max. | 1.23 N {125 gf}  | 1.96 N {200 gf}                            | 0.98 N {100 gf}                 | 0.49 N {50 gf} |                |
| RF min. | 0.20 N {20 gf}   | 0.49 N {50 gf}                             | 0.15 N {15 gf}                  | 0.05 N {5 gf}  |                |
| PT max. | 1.6 mm           | 1.6 mm                                     |                                 |                | 1.6 mm         |
| OT min. | 0.8 mm           | 0.8 mm                                     |                                 |                | 0.8 mm         |
| MD max. | 0.5 mm           | 0.6 mm (F gap type) or 0.5 mm (G gap type) |                                 |                | 0.6 mm         |
| OP      | 15.2±0.5 mm      |                                            |                                 |                |                |

D3V-21G1K-1□4A-Δ  
 D3V-161K-1□5-Δ  
 D3V-111K-1□5-Δ  
 D3V-111K-1□4-Δ  
 D3V-61K-1□4-Δ  
 D3V-6G1K-1□3-Δ  
 D3V-011K-1□3-Δ



| Model   | D3V-21G1K-1□4A-Δ | D3V-161K-1□5-Δ<br>D3V-111K-1□5-Δ           | D3V-111K-1□4-Δ<br>D3V-61K-1□4-Δ | D3V-6G1K-1□3-Δ | D3V-011K-1□3-Δ |
|---------|------------------|--------------------------------------------|---------------------------------|----------------|----------------|
| OF max. | 0.83 N {85 gf}   | 1.27 N {130 gf}                            | 0.64 N {65 gf}                  | 0.34 N {35 gf} |                |
| RF min. | 0.08 N {8 gf}    | 0.16 N {16 gf}                             | 0.08 N {8 gf}                   | 0.04 N {4 gf}  |                |
| PT max. | 3.5 mm           | 3.5 mm                                     |                                 |                | 3.5 mm         |
| OT min. | 1.1 mm           | 1.1 mm                                     |                                 |                | 1.1 mm         |
| MD max. | 1.1 mm           | 1.2 mm (F gap type) or 1.1 mm (G gap type) |                                 |                | 1.2 mm         |
| OP      | 15.2±1.2 mm      |                                            |                                 |                |                |

## Hinge Lever Models

D3V-21G2-1□4A-Δ

D3V-162-1□5-Δ


D3V-112-1□5-Δ

D3V-112-1□4-Δ

D3V-62-1□4-Δ

D3V-6G2-1□3-Δ

D3V-012-1□3-Δ



| Model   | D3V-21G2-1□4A-Δ | D3V-162-1□5-Δ<br>D3V-112-1□5-Δ             | D3V-112-1□4-Δ<br>D3V-62-1□4-Δ | D3V-6G2-1□3-Δ | D3V-012-1□3-Δ  |
|---------|-----------------|--------------------------------------------|-------------------------------|---------------|----------------|
| OF max. | 0.78 N {80 gf}  | 1.23 N {125 gf}                            | 0.59 N {60 gf}                |               | 0.29 N {30 gf} |
| RF min. | 0.06 N {6 gf}   | 0.14 N {14 gf}                             | 0.06 N {6 gf}                 |               | ---            |
| PT max. | 4.0 mm          | 4.0 mm                                     |                               |               | 4.0 mm         |
| OT min. | 1.6 mm          | 1.6 mm                                     |                               |               | 1.6 mm         |
| MD max. | 0.8 mm          | 1.5 mm (F gap type) or 0.8 mm (G gap type) |                               |               | 1.5 mm         |
| OP      | 15.2±1.2 mm     |                                            |                               |               |                |

D3V-21G2M-1□4A-Δ

D3V-162M-1□5-Δ


D3V-112M-1□5-Δ

D3V-112M-1□4-Δ

D3V-62M-1□4-Δ

D3V-6G2M-1□3-Δ

D3V-012M-1□3-Δ



| Model   | D3V-21G2M-1□4A-Δ | D3V-162M-1□5-Δ<br>D3V-112M-1□5-Δ           | D3V-112M-1□4-Δ<br>D3V-62M-1□4-Δ | D3V-6G2M-1□3-Δ | D3V-012M-1□3-Δ |
|---------|------------------|--------------------------------------------|---------------------------------|----------------|----------------|
| OF max. | 0.78 N {80 gf}   | 1.23 N {125 gf}                            | 0.59 N {60 gf}                  |                | 0.29 N {30 gf} |
| RF min. | 0.06 N {6 gf}    | 0.14 N {14 gf}                             | 0.06 N {6 gf}                   |                | ---            |
| PT max. | 4.0 mm           | 4.0 mm                                     |                                 |                | 4.0 mm         |
| OT min. | 1.6 mm           | 1.6 mm                                     |                                 |                | 1.6 mm         |
| MD max. | 0.8 mm           | 1.5 mm (F gap type) or 0.8 mm (G gap type) |                                 |                | 1.5 mm         |
| OP      | 15.2±1.2 mm      |                                            |                                 |                |                |

D3V-21G2K-1□4A-Δ

D3V-162K-1□5-Δ


D3V-112K-1□5-Δ

D3V-112K-1□4-Δ

D3V-62K-1□4-Δ

D3V-6G2K-1□3-Δ

D3V-012K-1□3-Δ



| Model   | D3V-21G2K-1□4A-Δ | D3V-162K-1□5-Δ<br>D3V-112K-1□5-Δ           | D3V-112K-1□4-Δ<br>D3V-62K-1□4-Δ | D3V-6G2K-1□3-Δ | D3V-012K-1□3-Δ |
|---------|------------------|--------------------------------------------|---------------------------------|----------------|----------------|
| OF max. | 0.44 N {45 gf}   | 0.69 N {70 gf}                             | 0.34 N {35 gf}                  | 0.20 N {20 gf} |                |
| RF min. | 0.04 N {4 gf}    | 0.08 N {8 gf}                              | 0.04 N {4 gf}                   | ---            |                |
| PT max. | 6.0 mm           | 6.0 mm                                     |                                 |                | 6.0 mm         |
| OT min. | 2.5 mm           | 2.5 mm                                     |                                 |                | 2.5 mm         |
| MD max. | 1.3 mm           | 2.0 mm (F gap type) or 1.3 mm (G gap type) |                                 |                | 2.0 mm         |
| OP      | 15.2±2.0 mm      |                                            |                                 |                |                |

## Long Hinge Lever Models

D3V-21G3-1□4A-Δ

D3V-163-1□5-Δ



D3V-113-1□5-Δ

D3V-113-1□4-Δ

D3V-63-1□4-Δ

D3V-6G3-1□3-Δ

D3V-013-1□3-Δ



| Model                         | D3V-21G3-1□4A-Δ                           | D3V-163-1□5-Δ<br>D3V-113-1□5-Δ                                 | D3V-113-1□4-Δ<br>D3V-63-1□4-Δ                                  | D3V-6G3-1□3-Δ              | D3V-013-1□3-Δ              |
|-------------------------------|-------------------------------------------|----------------------------------------------------------------|----------------------------------------------------------------|----------------------------|----------------------------|
| OF max.<br>RF min.            | 0.44 N {45 gf}<br>0.03 N {3 gf}           | 0.69 N {70 gf}<br>0.06 N {6 gf}                                | 0.34 N {35 gf}<br>---                                          | 0.20 N {20 gf}             | ---                        |
| PT max.<br>OT min.<br>MD max. | 9.0 mm<br>2.0 mm<br>2.0 mm                | 9.0 mm<br>2.0 mm<br>2.8 mm (F gap type) or 2.0 mm (G gap type) | 9.0 mm<br>3.2 mm<br>2.8 mm (F gap type) or 2.0 mm (G gap type) | 9.0 mm<br>3.2 mm<br>2.8 mm | 9.0 mm<br>3.2 mm<br>2.8 mm |
| OP                            | 15.2 <sup>+2.6</sup> / <sub>-3.2</sub> mm | 15.2±2.6 mm                                                    |                                                                |                            |                            |

D3V-21G3M-1□4A-Δ

D3V-163M-1□5-Δ


D3V-113M-1□5-Δ

D3V-113M-1□4-Δ

D3V-63M-1□4-Δ

D3V-6G3M-1□3-Δ

D3V-013M-1□3-Δ



Note: Stainless-steel lever

| Model                         | D3V-21G3M-1□4A-Δ                          | D3V-163M-1□5-Δ<br>D3V-113M-1□5-Δ                               | D3V-113M-1□4-Δ<br>D3V-63M-1□4-Δ                                | D3V-6G3M-1□3-Δ             | D3V-013M-1□3-Δ             |
|-------------------------------|-------------------------------------------|----------------------------------------------------------------|----------------------------------------------------------------|----------------------------|----------------------------|
| OF max.<br>RF min.            | 0.44 N {45 gf}<br>0.03 N {3 gf}           | 0.69 N {70 gf}<br>0.06 N {6 gf}                                | 0.34 N {35 gf}<br>---                                          | 0.20 N {20 gf}             | ---                        |
| PT max.<br>OT min.<br>MD max. | 9.0 mm<br>2.0 mm<br>2.0 mm                | 9.0 mm<br>2.0 mm<br>2.8 mm (F gap type) or 2.0 mm (G gap type) | 9.0 mm<br>3.2 mm<br>2.8 mm (F gap type) or 2.0 mm (G gap type) | 9.0 mm<br>3.2 mm<br>2.8 mm | 9.0 mm<br>3.2 mm<br>2.8 mm |
| OP                            | 15.2 <sup>+2.6</sup> / <sub>-3.2</sub> mm | 15.2±2.6 mm                                                    |                                                                |                            |                            |

D3V-21G3K-1□4A-Δ

D3V-163K-1□5-Δ


D3V-113K-1□5-Δ

D3V-113K-1□4-Δ

D3V-63K-1□4-Δ

D3V-6G3K-1□3-Δ

D3V-013K-1□3-Δ



| Model                         | D3V-21G3K-1□4A-Δ            | D3V-163K-1□5-Δ<br>D3V-113K-1□5-Δ                                | D3V-113K-1□4-Δ<br>D3V-63K-1□4-Δ | D3V-6G3K-1□3-Δ              | D3V-013K-1□3-Δ              |
|-------------------------------|-----------------------------|-----------------------------------------------------------------|---------------------------------|-----------------------------|-----------------------------|
| OF max.<br>RF min.            | 0.20 N {20 gf}<br>---       | 0.34 N {35 gf}<br>0.04 N {4 gf}                                 | 0.20 N {20 gf}<br>---           | 0.10 N {10 gf}              | ---                         |
| PT max.<br>OT min.<br>MD max. | 15.0 mm<br>4.0 mm<br>3.0 mm | 15.0 mm<br>4.0 mm<br>3.8 mm (F gap type) or 3.0 mm (G gap type) | 15.0 mm<br>4.0 mm<br>3.8 mm     | 15.0 mm<br>4.0 mm<br>3.8 mm | 15.0 mm<br>4.0 mm<br>3.8 mm |
| OP                            | 15.2±3.0 mm                 | 15.2±3.0 mm                                                     |                                 |                             |                             |

## Simulated Roller Lever Models

D3V-21G4-1□4A-Δ

D3V-164-1□5-Δ


D3V-114-1□5-Δ

D3V-114-1□4-Δ

D3V-64-1□4-Δ

D3V-6G4-1□3-Δ

D3V-014-1□3-Δ



| Model                         | D3V-21G4-1□4A-Δ                 | D3V-164-1□5-Δ<br>D3V-114-1□5-Δ                                 | D3V-114-1□4-Δ<br>D3V-64-1□4-Δ   | D3V-6G4-1□3-Δ         | D3V-014-1□3-Δ              |
|-------------------------------|---------------------------------|----------------------------------------------------------------|---------------------------------|-----------------------|----------------------------|
| OF max.<br>RF min.            | 0.83 N {85 gf}<br>0.07 N {7 gf} | 1.23 N {125 gf}<br>0.14 N {14 gf}                              | 0.59 N {60 gf}<br>0.06 N {6 gf} | 0.29 N {30 gf}<br>--- |                            |
| PT max.<br>OT min.<br>MD max. | 4.0 mm<br>1.6 mm<br>1.4 mm      | 4.0 mm<br>1.6 mm<br>1.5 mm (F gap type) or 0.8 mm (G gap type) |                                 |                       | 4.0 mm<br>1.6 mm<br>1.5 mm |
| OP                            | 18.7±1.2 mm                     |                                                                |                                 |                       |                            |

D3V-21G4M-1□4A-Δ

D3V-164M-1□5-Δ


D3V-114M-1□5-Δ

D3V-114M-1□4-Δ

D3V-64M-1□4-Δ

D3V-6G4M-1□3-Δ

D3V-014M-1□3-Δ



| Model                         | D3V-21G4M-1□4A-Δ                | D3V-164M-1□5-Δ<br>D3V-114M-1□5-Δ                               | D3V-114M-1□4-Δ<br>D3V-64M-1□4-Δ | D3V-6G4M-1□3-Δ        | D3V-014M-1□3-Δ             |
|-------------------------------|---------------------------------|----------------------------------------------------------------|---------------------------------|-----------------------|----------------------------|
| OF max.<br>RF min.            | 0.83 N {85 gf}<br>0.07 N {7 gf} | 1.23 N {125 gf}<br>0.14 N {14 gf}                              | 0.59 N {60 gf}<br>0.06 N {6 gf} | 0.29 N {30 gf}<br>--- |                            |
| PT max.<br>OT min.<br>MD max. | 4.0 mm<br>1.6 mm<br>1.4 mm      | 4.0 mm<br>1.6 mm<br>1.5 mm (F gap type) or 0.8 mm (G gap type) |                                 |                       | 4.0 mm<br>1.6 mm<br>1.5 mm |
| OP                            | 18.7±1.2 mm                     |                                                                |                                 |                       |                            |

D3V-21G4K-1□4A-Δ

D3V-164K-1□5-Δ


D3V-114K-1□5-Δ

D3V-114K-1□4-Δ

D3V-64K-1□4-Δ

D3V-6G4K-1□3-Δ

D3V-014K-1□3-Δ



| Model                         | D3V-21G4K-1□4A-Δ                | D3V-164K-1□5-Δ<br>D3V-114K-1□5-Δ                               | D3V-114K-1□4-Δ<br>D3V-64K-1□4-Δ | D3V-6G4K-1□3-Δ        | D3V-014K-1□3-Δ             |
|-------------------------------|---------------------------------|----------------------------------------------------------------|---------------------------------|-----------------------|----------------------------|
| OF max.<br>RF min.            | 0.54 N {55 gf}<br>0.03 N {3 gf} | 0.74 N {75 gf}<br>0.10 N {10 gf}                               | 0.39 N {40 gf}<br>0.03 N {3 gf} | 0.20 N {20 gf}<br>--- |                            |
| PT max.<br>OT min.<br>MD max. | 8.0 mm<br>1.5 mm<br>3.0 mm      | 8.0 mm<br>1.5 mm<br>3.5 mm (F gap type) or 3.0 mm (G gap type) |                                 |                       | 8.0 mm<br>1.5 mm<br>3.5 mm |
| OP                            | 18.7±2.0 mm                     |                                                                |                                 |                       |                            |

## Short Hinge Roller Lever Models

D3V-21G5-1□4A-Δ

D3V-165-1□5-Δ



D3V-115-1□5-Δ

D3V-115-1□4-Δ

D3V-65-1□4-Δ

D3V-6G5-1□3-Δ

D3V-015-1□3-Δ



| Model                         | D3V-21G5-1□4A-Δ                  | D3V-165-1□5-Δ<br>D3V-115-1□5-Δ                                 | D3V-115-1□4-Δ<br>D3V-65-1□4-Δ     | D3V-6G5-1□3-Δ                   | D3V-015-1□3-Δ              |
|-------------------------------|----------------------------------|----------------------------------------------------------------|-----------------------------------|---------------------------------|----------------------------|
| OF max.<br>RF min.            | 1.42 N {145 gf}<br>0.2 N {20 gf} | 2.35 N {240 gf}<br>0.49 N {50 gf}                              | 1.18 N {120 gf}<br>0.15 N {15 gf} | 0.59 N {60 gf}<br>0.06 N {6 gf} |                            |
| PT max.<br>OT min.<br>MD max. | 1.6 mm<br>0.8 mm<br>0.5 mm       | 1.6 mm<br>0.8 mm<br>0.6 mm (F gap type) or 0.5 mm (G gap type) |                                   |                                 | 1.6 mm<br>0.8 mm<br>0.6 mm |
| OP                            | 20.7±0.6 mm                      |                                                                |                                   |                                 |                            |

D3V-21G5M-1□4A-Δ

D3V-165M-1□5-Δ



D3V-115M-1□5-Δ

D3V-115M-1□4-Δ

D3V-65M-1□4-Δ

D3V-6G5M-1□3-Δ

D3V-015M-1□3-Δ



| Model                         | D3V-21G5M-1□4A-Δ                 | D3V-165M-1□5-Δ<br>D3V-115M-1□5-Δ                               | D3V-115M-1□4-Δ<br>D3V-65M-1□4-Δ   | D3V-6G5M-1□3-Δ                  | D3V-015M-1□3-Δ             |
|-------------------------------|----------------------------------|----------------------------------------------------------------|-----------------------------------|---------------------------------|----------------------------|
| OF max.<br>RF min.            | 1.42 N {145 gf}<br>0.2 N {20 gf} | 2.35 N {240 gf}<br>0.49 N {50 gf}                              | 1.18 N {120 gf}<br>0.15 N {15 gf} | 0.59 N {60 gf}<br>0.06 N {6 gf} |                            |
| PT max.<br>OT min.<br>MD max. | 1.6 mm<br>0.8 mm<br>0.5 mm       | 1.6 mm<br>0.8 mm<br>0.6 mm (F gap type) or 0.5 mm (G gap type) |                                   |                                 | 1.6 mm<br>0.8 mm<br>0.6 mm |
| OP                            | 20.7±0.6 mm                      |                                                                |                                   |                                 |                            |

D3V-21G5K-1□4A-Δ

D3V-165K-1□5-Δ



D3V-115K-1□5-Δ

D3V-115K-1□4-Δ

D3V-65K-1□4-Δ

D3V-6G5K-1□3-Δ

D3V-015K-1□3-Δ



| Model                         | D3V-21G5K-1□4A-Δ                 | D3V-165K-1□5-Δ<br>D3V-115K-1□5-Δ                               | D3V-115K-1□4-Δ<br>D3V-65K-1□4-Δ | D3V-6G5K-1□3-Δ                  | D3V-015K-1□3-Δ             |
|-------------------------------|----------------------------------|----------------------------------------------------------------|---------------------------------|---------------------------------|----------------------------|
| OF max.<br>RF min.            | 0.98 N {100 gf}<br>0.08 N {8 gf} | 1.57 N {160 gf}<br>0.15 N {15 gf}                              | 0.78 N {80 gf}<br>0.08 N {8 gf} | 0.39 N {40 gf}<br>0.04 N {4 gf} |                            |
| PT max.<br>OT min.<br>MD max. | 2.6 mm<br>1.0 mm<br>0.8 mm       | 2.6 mm<br>1.0 mm<br>0.9 mm (F gap type) or 0.8 mm (G gap type) |                                 |                                 | 2.6 mm<br>1.0 mm<br>0.9 mm |
| OP                            | 20.7±1.0 mm                      |                                                                |                                 |                                 |                            |

## Hinge Roller Lever Models

D3V-21G6-1□4A-Δ

D3V-166-1□5-Δ


D3V-116-1□5-Δ

D3V-116-1□4-Δ

D3V-66-1□4-Δ

D3V-6G6-1□3-Δ

D3V-016-1□3-Δ



| Model   | D3V-21G6-1□4A-Δ | D3V-166-1□5-Δ<br>D3V-116-1□5-Δ             | D3V-116-1□4-Δ<br>D3V-66-1□4-Δ | D3V-6G6-1□3-Δ  | D3V-016-1□3-Δ |
|---------|-----------------|--------------------------------------------|-------------------------------|----------------|---------------|
| OF max. | 0.79 N {80 gf}  | 1.23 N {125 gf}                            | 0.59 N {60 gf}                | 0.29 N {30 gf} |               |
| RF min. | 0.05 N {5 gf}   | 0.14 N {14 gf}                             | 0.06 N {6 gf}                 | ---            |               |
| PT max. | 4.0 mm          | 4.0 mm                                     |                               |                | 4.0 mm        |
| OT min. | 1.6 mm          | 1.6 mm                                     |                               |                | 1.6 mm        |
| MD max. | 0.8 mm          | 1.5 mm (F gap type) or 0.8 mm (G gap type) |                               |                | 1.5 mm        |
| OP      | 20.7±1.2 mm     |                                            |                               |                |               |

D3V-21G6M-1□4A-Δ

D3V-166M-1□5-Δ


D3V-116M-1□5-Δ

D3V-116M-1□4-Δ

D3V-66M-1□4-Δ

D3V-6G6M-1□3-Δ

D3V-016M-1□3-Δ



| Model   | D3V-21G6M-1□4A-Δ | D3V-166M-1□5-Δ<br>D3V-116M-1□5-Δ           | D3V-116M-1□4-Δ<br>D3V-66M-1□4-Δ | D3V-6G6M-1□3-Δ | D3V-016M-1□3-Δ |
|---------|------------------|--------------------------------------------|---------------------------------|----------------|----------------|
| OF max. | 0.79 N {80 gf}   | 1.23 N {125 gf}                            | 0.59 N {60 gf}                  | 0.29 N {30 gf} |                |
| RF min. | 0.05 N {5 gf}    | 0.14 N {14 gf}                             | 0.06 N {6 gf}                   | ---            |                |
| PT max. | 4.0 mm           | 4.0 mm                                     |                                 |                | 4.0 mm         |
| OT min. | 1.6 mm           | 1.6 mm                                     |                                 |                | 1.6 mm         |
| MD max. | 0.8 mm           | 1.5 mm (F gap type) or 0.8 mm (G gap type) |                                 |                | 1.5 mm         |
| OP      | 20.7±1.2 mm      |                                            |                                 |                |                |

D3V-21G6K-1□4A-Δ

D3V-166K-1□5-Δ



D3V-116K-1□5-Δ

D3V-116K-1□4-Δ

D3V-66K-1□4-Δ

D3V-6G6K-1□3-Δ

D3V-016K-1□3-Δ



| Model                         | D3V-21G6K-1□4A-Δ                | D3V-166K-1□5-Δ<br>D3V-116K-1□5-Δ                               | D3V-116K-1□4-Δ<br>D3V-66K-1□4-Δ | D3V-6G6K-1□3-Δ        | D3V-016K-1□3-Δ             |
|-------------------------------|---------------------------------|----------------------------------------------------------------|---------------------------------|-----------------------|----------------------------|
| OF max.<br>RF min.            | 0.49 N {50 gf}<br>0.03 N {3 gf} | 0.74 N {75 gf}<br>0.10 N {10 gf}                               | 0.39 N {40 gf}<br>0.03 N {3 gf} | 0.20 N {20 gf}<br>--- |                            |
| PT max.<br>OT min.<br>MD max. | 7.2 mm<br>2.0 mm<br>2.0 mm      | 7.2 mm<br>2.0 mm<br>2.7 mm (F gap type) or 2.0 mm (G gap type) |                                 |                       | 7.2 mm<br>2.0 mm<br>2.7 mm |
| OP                            | 20.7±2.2 mm                     |                                                                |                                 |                       |                            |



# Precautions

Refer to *General Information*.

## Cautions

### Handling

Be careful not to drop the switch. Doing so may cause damage to the switch's internal components because it is designed for a small load.

## Correct Use

### Mounting

Use two M3 mounting screws with an appropriate screwdriver to mount the switch. Tighten the screws to a torque of 0.39 to 0.59 N • m {4 to 6 kgf • cm}.

### Mounting Direction

Mount lever-operated switches with a maximum operating force of 0.49 N in a direction where the actuator weight will not be applied to the switch. Since the switch is designed for a small load, its resetting force is small. Therefore, resetting failure may occur if unnecessary load is applied to the switch.


### Insulation Distance

According to EN61058-1, the minimum insulation thickness for this switch should be 1.1 mm and minimum clearance distance between the terminal and mounting plate should be 1.9 mm. If the insulation distance cannot be provided in the product incorporating the switch, either use a switch with insulation barrier or use a Separator to ensure sufficient insulation distance.

## Using Micro Loads

Using a model for ordinary loads to open or close the contact of a micro load circuit may result faulty contact. Use models that operate in the following range. However, even when using micro load models within the operating range shown below, if inrush current occurs when the contact is opened or closed, it may increase contact wear and so decrease durability. Therefore, insert a contact protection circuit where necessary.

The minimum applicable load is the N-level reference value. This value indicates the malfunction reference level for the reliability level of 60% ( $\lambda 60$ ). The equation,  $\lambda 60 = 0.5 \times 10^{-6}/\text{operations}$  indicates that the estimated malfunction rate is less than 1/2,000,000 operations with a reliability level of 60%.



## Solder Terminal Approval Conditions

|                                           |
|-------------------------------------------|
| Soldering iron can be used.               |
| Soldering hook hole available.            |
| Soldering terminal types 1 and 2 are met. |

## Actuator (Sold Separately)

Various Actuators are available as shown on D3V/V/VX/D2MV/D2RV Common Accessories.

## Connector (Sold Separately)

Refer to Terminal Connectors.

- Application examples provided in this document are for reference only. In actual applications, confirm equipment functions and safety before using the product.
- Consult your OMRON representative before using the product under conditions which are not described in the manual or applying the product to nuclear control systems, railroad systems, aviation systems, vehicles, combustion systems, medical equipment, amusement machines, safety equipment, and other systems or equipment that may have a serious influence on lives and property if used improperly. Make sure that the ratings and performance characteristics of the product provide a margin of safety for the system or equipment, and be sure to provide the system or equipment with double safety mechanisms.

**Note: Do not use this document to operate the Unit.**

**OMRON Corporation**

ELECTRONIC AND MECHANICAL COMPONENTS COMPANY

Contact: [www.omron.com/ecb](http://www.omron.com/ecb)

Cat. No. B103-E1-04  
0812(0207)(O)