

MP SERIES

- High quality Nickel-plated brass housings
- Enhanced viewing angles with reflector use
- Daylight visible available
- Wide variety of connectors and flying leads available (subject to special quotation)
- All necessary stainless steel mounting hardware provided



Mounting Information:

MPx3 series: 0.235 [5.97mm] +0.003 [0.08mm] / -0.002 [0.05mm]

MPx5 series: 0.315 [8.00mm] +0.003 [0.08mm] / -0.002 [0.05mm]

Panel Thickness: 0.047 [1.2mm] to 0.250 [6.35mm]

Material Specifications:

Housing: Nickel-plated brass housing

Optional Wire Leads: 24AWG UL 1061 Cathode-Black, Anode-Red

Application Notes:

Wire leads from 2.5" to 48" are available subject to special quotation please consult Bivar at 1-800-SPACERS for additional information.

Many connectors are available as well as customer specified connectors. (Subject to quotation)



Ordering Information:

MPR **5** **G** **D** **5V** **W6** **-CC**
Series Size Color Lens Special Leads Options

Size: 3 3mm LED

5 5mm LED

Color: Please see Chart

Color Options and Suffixes:

Suffix	Color	Peak (nm)	Typ. Vf
G	Green	565nm	2.0
H	High Efficiency Red	635nm	2.0
Y	Yellow	585nm	2.0
SR	Super Red	660nm	2.0
O	Orange	635nm	2.0
A	Amber	610nm	2.0
BW	Blue	430nm	3.5
BC	Red/Green Bi-Color	635/565	2.0

Lens Choices:

D Color Diffused
C Water Clear
T Tinted Non-diffused

Special:

L 2ma Low Current
5V 5 Volt integrated resistor
12V 12 Volt integrated resistor

Leads:

"Blank" Terminal Leads


Wx 24AWG Wire Leads

Replace the "X" with the length in inches


Options:

-CC Standard 0.100" [2.54mm] pitch header connector
-CC2 Miniature 0.075" [2.54mm] pitch header connector


MPC3 Series Chrome Panel Mount



MPR3 Series Chrome Panel Mount



MPC5 Series Chrome Panel Mount



MPR5 Series Chrome Panel Mount

