




LOC		DIST		REVISIONS				
P	LTR	DESCRIPTION			DATE	DWN	APVD	
		B1	REVISED PER ECO-11-004917			11MAR11	RK	HMR

- ⚠ WIRE SIZE AND AMP LOGO APPEAR ON OUTSIDE OF WIRE BARREL.
- ⚠ SOCKET & STRIP CONTACT: 0.76 μ [.000030] MIN GOLD PER MIL-G-45204 ON CONTACT MATING END, GOLD FLASH ON REMAINDER , ALL OVER 1.27 μ m [.000050] MIN NICKEL PER QQ-N-390.
- RETENTION CLIP: 2.54 μ m [.000100] MIN NICKEL PER QQ-N-290.
- ⚠ RETENTION CLIP: PHOSPHOR BRONZE PER QQ-B-750.
- SOCKET CONTACT: COPPER PER QQ-C-576.
- CONTACT STRIP: BERYLLIUM COPPER PER QQ-C-533.
- ⚠ SOCKET CONTACT: 1.27 μ m [.000050] MIN SILVER PER QQ-S-365, ALL OVER 1.27 μ m [.000050] MIN NICKEL PER QQ-N-290.
- CONTACT STRIP: 5.08 μ m [.000200] MIN SILVER PER QQ-S-365, ALL OVER 1.02 μ m [.000040] MIN NICKEL PER QQ-N-290.
- RETENTION CLIP: 2.54 μ m [.000100] MIN NICKEL PER QQ-N-290.



⚠	DETAIL X	213847-4
⚠	DETAIL X	213847-3
⚠	-	213847-2
⚠	-	213847-1
FINISH	LOOSE PIECE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
W.G.LENKER

30 JUL 96

CHK
R.STONE

05 AUG 96

APVD
G.STEINHAUER

06 AUG 96

NAME

DIMENSIONS:
mm[INCHES]

0 PLC

± -

1 PLC

± -

2 PLC

± -

3 PLC

± -

4 PLC

± -

ANGLES

± -

TOLERANCES, UNLESS OTHERWISE SPECIFIED:

± -

MATERIAL

FINISH

SEE TABLE

APPLICATION SPEC

—

WEIGHT

—

SIZE

CAGE CODE

DRAWING NO

100779

213847

RESTRICTED TO

—

CUSTOMER DRAWING

SCALE

10:1

SHEET

1

OF

1

REV

B1

TE Connectivity

SOCKET CONTACT ASSEMBLY,
14-12 AWG, .125
POWERBAND