




13	12	11	10	9	8	7	6	5	4	3	2	1
MATERIAL NUMBER LOOSE PCS	ENGINEERING NUMBER LOOSE PCS	MATERIAL NUMBER ON STRIP	ENGINEERING NUMBER ON STRIP	MATERIAL NUMBER ON TAPE	ENGINEERING NUMBER ON TAPE	WIRE SIZE		ACCEPTS TAB SIZE				
190020044	C-5265	190020046	C-5265Z	190020045	C-5265T	12-10 AWG /2.7-6.6 mm ²		.250 X.032 /6.35 X 0.81				

D1


D1



PARTS ON TAPE



SECTION A-A



SALES DRAWING

NOTES:

- MATERIAL: TERMINAL BRASS .018/0.46 THK REF.
TERMINAL PLATING: ELECTRO TIN
FERRULE: BRASS
FERRULE PLATING: ELECTRO TIN
INSULATION: NYLON 94V2 COLOR YELLOW.

2. MWID = MAXIMUM WIRE INSULATION DIAMETER

- PART IS RoHS COMPLIANT

ADD DIMS. RMV 19606 EC NO: WNA2011-0458 DRWNE:THRODAHL 2011/03/08 CHKD:JMACNEIL 2011/03/08 APPR:JMACNEIL 2011/07/05	QUALITY SYMBOLS ▽=0 ▽=0	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION			
				IN/MM		---	INCH				
				mm	INCH	DRAWN BY		DATE		TITLE	
				4 PLACES ± --- ± ---	BENDERLE	2005/04/15					
				3 PLACES ± --- ± .005	CHECKED BY	DATE					
				2 PLACES ± 0.13 ± .01	R DEROSS	2005/04/15					
				1 PLACE ± 0.25 ± ---	APPROVED BY	DATE					
			R DEROSS	2005/04/15		MOLEX MOLEX INCORPORATED					
			ANGULAR ±1/2°		MATERIAL NO.		DOCUMENT NO.		SHEET NO.		
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-19002-005		1 OF 1		
D1	REV			SIZE C	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						