




REV.	DATE	ECR NO.	DESCRIPTION
B	10/22/10	XXXXX	MODIFY THE MATERIAL OF ITEM 3



RECOMMENDED
CABLE STRIPPING DIM'S



1. CRIMPED FERRULE
HEX CRIMP SIZE .255"
2. CRIMPED CONTACT PIN
HEX CRIMP SIZE .068"

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex							
						DRAWN	M.ZHANG		10/22/10								
5	FERRULE	BRASS	NICKEL	1		CHECKED			PART DESCRIPTION								
4	CONTACT PIN	BRASS	GOLD	1		ISSUED			UHF CRIMP PLUG (FOR RG–8X, LMR240 CABLE)								
3	INSULATOR	PHENOLIC	YELLOW	1		SHEET	1 OF 1		PART NO.								
2	BODY	BRASS	NICKEL	1	182115												
1	SHELL	BRASS	NICKEL	1	DWG. NO.					182115.DWG		REV.	B	SIZE	A	SCALE	NA
DESCRIPTION					MATERIAL	FINISH	QTY	C:/CONNEX/182115.DWG									