

# Hermetically Sealed Threaded Case Filters

This series of filters features hermetic glass seals and high EMI filtering performance. They are excellent for critical applications that demand high reliability in the toughest environmental conditions and provide broad-band high performance EMI filtering from 10 KHz to over 10 GHz.

## Features

- MIL-F-15733 and MIL-F-28861, DSCC 84084 QPL filters available
- Popular .375", .410" and .690" case diameters
- Voltage ratings from 50 V to 400 VDC/240 AC, 400 Hz
- Impervious to high moisture environments, solvents and severe environmental conditions
- High temperature terminal construction
- D-slotted bushings
- High reliability testing available



Thread length: A - 0.187 (4.76) B - 0.312 (7.92)




Figure 1




Figure 2

Dimensions in inches (mm)

Note: ø .410 Max. for M28861 parts

# Hermetically Sealed Threaded Case Filters

## .375 ø C Circuit Standard

| Part Number     | MIL No | See Pg. LP26 for Fig. | Rated Voltage |   |       |     | I Amp | Min Cap μF | DCR Max Ohms | Max L |          | Thd Lgth | Minimum Insertion Loss (dB) |         |         |       |        |         |       |  |
|-----------------|--------|-----------------------|---------------|---|-------|-----|-------|------------|--------------|-------|----------|----------|-----------------------------|---------|---------|-------|--------|---------|-------|--|
|                 |        |                       | 85°C          |   | 125°C |     |       |            |              | In    | (mm)     |          | 30 KHz                      | 150 KHz | 300 KHz | 1 MHz | 10 MHz | 100 MHz | 1 GHz |  |
| † 54-367-008    | —      | 1                     | 80            | — | 50    | —   | 15    | 1.400      | 0.005        | 0.387 | (9.830)  | A        | 15                          | 28      | 33      | 44    | 60     | 70      | 70    |  |
| 54-370-007      | —      | 1                     | 80            | — | 50    | —   | 15    | 2.800      | 0.005        | 0.576 | (14.630) | A        | 20                          | 34      | 39      | 50    | 60     | 70      | 70    |  |
| 54-371-001      | —      | 1                     | 80            | — | 50    | —   | 15    | 4.000      | 0.005        | 0.688 | (17.475) | A        | 26                          | 40      | 46      | 55    | 60     | 70      | 70    |  |
| 54-367-005      | —      | 1                     | 150           | — | 100   | —   | 15    | 0.450      | 0.005        | 0.387 | (9.830)  | A        | 6                           | 19      | 25      | 36    | 55     | 70      | 70    |  |
| † 9920-100-6002 | —      | 1                     | 200           | — | 150   | 125 | 15    | 0.150      | 0.005        | 0.387 | (9.830)  | A        | —                           | 6       | 15      | 26    | 42     | 55      | 70    |  |
| 54-367-007      | —      | 1                     | 250           | — | 200   | 125 | 15    | 0.015      | 0.005        | 0.387 | (9.830)  | A        | —                           | —       | —       | 6     | 25     | 45      | 50    |  |
| † 54-367-006    | —      | 1                     | 250           | — | 200   | 125 | 15    | 0.250      | 0.005        | 0.387 | (9.830)  | A        | —                           | 14      | 19      | 30    | 50     | 65      | 70    |  |
| 54-370-006      | —      | 1                     | 250           | — | 200   | 125 | 15    | 0.500      | 0.005        | 0.630 | (16.002) | A        | 7                           | 20      | 28      | 39    | 55     | 70      | 70    |  |
| 9923-100-6004   | —      | 1                     | 400           | — | 400   | 240 | 15    | 0.060      | 0.005        | 0.415 | (10.541) | A        | —                           | 5       | 10      | 18    | 38     | 55      | 70    |  |


## .375 ø C Circuit MIL Qualified (See MIL index on pages CF9-11 for complete MIL part number listing)

| Part Number | M15733<br>M28861<br>MIL No | See Pg.<br>LP26<br>for Fig. | Rated Voltage |   |       |     | I<br>Amp | Min<br>Cap<br>µF | DCR<br>Max<br>Ohms | Max<br>L |          | Thd<br>Lgth | Minimum Insertion Loss (dB) |            |            |          |           |            |          |  |
|-------------|----------------------------|-----------------------------|---------------|---|-------|-----|----------|------------------|--------------------|----------|----------|-------------|-----------------------------|------------|------------|----------|-----------|------------|----------|--|
|             |                            |                             | 85°C          |   | 125°C |     |          |                  |                    | In       | (mm)     |             | 30<br>KHz                   | 150<br>KHz | 300<br>KHz | 1<br>MHz | 10<br>MHz | 100<br>MHz | 1<br>GHz |  |
| 54-367-054  | 1-012◇                     | 1                           | —             | — | 50    | —   | 15       | 1.200            | 0.008              | 0.410    | (10.414) | B           | 15                          | 28         | 33         | 40       | 40        | 70         | 70       |  |
| 54-367-049  | 1-002◇                     | 1                           | —             | — | 50    | —   | 15       | 1.200            | 0.008              | 0.410    | (10.414) | A           | 15                          | 28         | 33         | 40       | 40        | 70         | 70       |  |
| 54-370-032  | 49-0008                    | 1                           | —             | — | 50    | —   | 15       | 2.100            | 0.010              | 0.576    | (14.630) | A           | 20                          | 33         | 40         | 50       | 65        | 70         | 70       |  |
| 54-367-055  | 1-014◇                     | 1                           | —             | — | 70    | —   | 15       | 0.700            | 0.008              | 0.410    | (10.414) | B           | 10                          | 24         | 30         | 40       | 40        | 64         | 70       |  |
| 54-370-030  | 34-0035                    | 2                           | —             | — | 100   | —   | 10       | 0.300            | 0.004              | 0.474    | (12.040) | A           | 7                           | 19         | 25         | 35       | 55        | 70         | 70       |  |
| 54-367-051  | 1-006◇                     | 1                           | —             | — | 100   | —   | 15       | 0.450            | 0.008              | 0.410    | (10.414) | A           | 6                           | 19         | 25         | 36       | 40        | 60         | 70       |  |
| 54-367-056  | 1-016◇                     | 1                           | —             | — | 100   | —   | 15       | 0.450            | 0.008              | 0.410    | (10.414) | B           | 6                           | 19         | 25         | 36       | 40        | 60         | 70       |  |
| 54-367-057  | 1-018◇                     | 1                           | —             | — | 150   | —   | 15       | 0.250            | 0.008              | 0.410    | (10.414) | B           | —                           | 14         | 20         | 31       | 40        | 56         | 70       |  |
| 54-367-053  | 1-010◇                     | 1                           | —             | — | 200   | 125 | 15       | 0.150            | 0.008              | 0.410    | (10.414) | A           | —                           | 10         | 16         | 26       | 40        | 52         | 70       |  |
| 54-367-058  | 1-020◇                     | 1                           | —             | — | 200   | 125 | 15       | 0.150            | 0.008              | 0.410    | (10.414) | B           | —                           | 10         | 16         | 26       | 40        | 52         | 70       |  |
| 54-370-034  | 49-0010                    | 1                           | —             | — | 330   | —   | 15       | 0.062            | 0.004              | 0.680    | (17.272) | A           | —                           | 2          | 7          | 17       | 37        | 55         | 70       |  |

† Also available through API's authorized distributors.

# Hermetically Sealed Threaded Case Filters


## .375 ø L Circuit



## L-C Filter LT



## L-C Filter LB



## .375 ø L Standard Low Profile

| Part Number     | MIL No | Figure           | Rated Voltage |         |          |          | I Amp | Min Cap µF | DCR Max Ohms | CKT | Max L In       | Thd Lgth | Minimum Insertion Loss (dB) |         |         |       |        |         |       |
|-----------------|--------|------------------|---------------|---------|----------|----------|-------|------------|--------------|-----|----------------|----------|-----------------------------|---------|---------|-------|--------|---------|-------|
|                 |        |                  | 85°C DC       | 85°C AC | 125°C DC | 125°C AC |       |            |              |     | (mm)           |          | 30 KHz                      | 150 KHz | 300 KHz | 1 MHz | 10 MHz | 100 MHz | 1 GHz |
| † 9051-100-0000 | —      | 1                | 80            | —       | 50       | —        | 15    | 1.200      | 0.005        | LB  | 0.370 (9.398)  | A        | 15                          | 25      | 34      | 44    | 60     | 70      | 70    |
| † 51-359-001 €  | —      | 1                | 80            | —       | 50       | —        | 15    | 1.400      | 0.005        | LB  | 0.370 (9.398)  | A        | 15                          | 28      | 33      | 44    | 60     | 70      | 70    |
| SCI-1021-000    | —      | 2*               | 80            | —       | 50       | —        | 15    | 1.400      | 0.003        | LB  | 0.280 (7.112)  | A        | 15                          | 28      | 33      | 44    | 60     | 70      | 70    |
| † 9053-100-0001 | —      | 1                | 80            | —       | 50       | —        | 15    | 1.400      | 0.005        | LB  | 0.370 (9.398)  | A        | 15                          | 25      | 34      | 44    | 60     | 70      | 70    |
| † 51-717-001 €  | —      | 2*               | 80            | —       | 50       | —        | 15    | 1.400      | 0.005        | LB  | 0.325 (8.255)  | A        | 15                          | 28      | 33      | 44    | 60     | 70      | 70    |
| 51-344-006      | —      | 4                | 80            | —       | 50       | —        | 15    | 1.400      | 0.005        | LB  | 0.330 (8.382)  | A        | 15                          | 28      | 33      | 44    | 60     | 70      | 70    |
| † SCI-1020-000  | —      | 1                | 80            | —       | 50       | —        | 15    | 1.400      | 0.003        | LB  | 0.370 (9.398)  | A        | 15                          | 28      | 33      | 44    | 60     | 70      | 70    |
| SCI-1021-020    | —      | 2 <sup>0</sup> * | 80            | —       | 50       | —        | 15    | 1.400      | 0.003        | LB  | 0.280 (7.112)  | B        | 15                          | 28      | 33      | 44    | 60     | 70      | 70    |
| † SCI-1020-020  | —      | 1                | 80            | —       | 50       | —        | 15    | 1.400      | 0.003        | LB  | 0.370 (9.398)  | B        | 15                          | 28      | 33      | 44    | 60     | 70      | 70    |
| SCI-1150-001    | —      | 1                | 80            | —       | 50       | —        | 15    | 2.800      | 0.003        | LB  | 0.450 (11.430) | B        | 20                          | 34      | 40      | 49    | 60     | 70      | 70    |
| 9051-101-0018   | —      | 5                | 80            | —       | 50       | —        | 25    | 1.400      | 0.001        | LB  | 0.450 (11.430) | A        | 15                          | 25      | 34      | 44    | 60     | 70      | 70    |
| † 9053-100-0008 | —      | 1                | 100           | —       | 70       | —        | 15    | 0.700      | 0.005        | LB  | 0.370 (9.398)  | A        | 9                           | 20      | 29      | 39    | 52     | 70      | 70    |

\* Part is resin sealed, this is not a hermetic part.


† Also available through API's authorized distributors.

€ Also available through API's authorized European distributors/agents.


◇ Note: 0.462" (11.73mm) length from mounting surface to end of lead — not 0.347" (8.8mm).

## Hermetically Sealed Threaded Case Filters

### L-C Filter LT



### L-C Filter LB



### .375 ø L Standard Low Profile *continued*

| Part Number     | MIL No | See Pg. LP28 for Fig | Rated Voltage |     |       |     | I Amp | Min Cap µF | DCR Max Ohms | CKT | Max L In (mm)  | Thd Lgth | Minimum Insertion Loss (dB) |         |         |       |        |         |       |  |
|-----------------|--------|----------------------|---------------|-----|-------|-----|-------|------------|--------------|-----|----------------|----------|-----------------------------|---------|---------|-------|--------|---------|-------|--|
|                 |        |                      | 85°C          |     | 125°C |     |       |            |              |     |                |          | 30 KHz                      | 150 KHz | 300 KHz | 1 MHz | 10 MHz | 100 MHz | 1 GHz |  |
|                 |        |                      | DC            | AC  | DC    | AC  |       |            |              |     |                |          |                             |         |         |       |        |         |       |  |
| + 9050-100-0008 | —      | 2*                   | 100           | —   | 70    | —   | 15    | 0.750      | 0.005        | LB  | 0.325 (8.255)  | A        | 9                           | 20      | 29      | 39    | 52     | 70      | 70    |  |
| + 9053-100-0002 | —      | 1                    | 150           | —   | 100   | —   | 15    | 0.500      | 0.005        | LB  | 0.370 (9.398)  | A        | 4                           | 12      | 21      | 31    | 48     | 70      | 70    |  |
| SCI-1250-001    | —      | 1                    | 150           | —   | 100   | —   | 15    | 0.500      | 0.003        | LB  | 0.450 (11.430) | B        | 8                           | 20      | 25      | 34    | 50     | 64      | 70    |  |
| €SCI-2150-000   | —      | 1                    | 150           | —   | 100   | —   | 15    | 1.000      | 0.003        | LB  | 0.450 (11.430) | A        | 10                          | 25      | 30      | 41    | 56     | 70      | 70    |  |
| SCI-2150-001    | —      | 1                    | 150           | —   | 100   | —   | 15    | 1.000      | 0.003        | LB  | 0.450 (11.430) | B        | 10                          | 25      | 30      | 41    | 56     | 70      | 70    |  |
| + 51-717-007    | —      | 2*                   | 250           | 125 | 200   | 125 | 15    | 0.015      | 0.005        | LB  | 0.325 (8.255)  | A        | —                           | —       | —       | 6     | 25     | 38      | 45    |  |
| + 51-359-007    | —      | 1                    | 250           | 125 | 200   | 125 | 15    | 0.012      | 0.005        | LB  | 0.370 (9.398)  | A        | —                           | —       | —       | 6     | 25     | 38      | 50    |  |
| 9050-100-0011   | —      | 2                    | 350           | 125 | 300   | 125 | 15    | 0.150      | 0.008        | LB  | 0.325 (8.255)  | A        | —                           | 10      | 15      | 25    | 40     | 52      | 60    |  |
| €SCI-2350-000   | —      | 1                    | 300           | 125 | 300   | 125 | 15    | 0.250      | 0.003        | LB  | 0.450 (11.430) | A        | 4                           | 15      | 21      | 31    | 50     | 70      | 70    |  |
| SCI-2350-001    | —      | 1                    | 300           | 125 | 300   | 125 | 15    | 0.250      | 0.003        | LB  | 0.450 (11.430) | B        | 4                           | 15      | 21      | 31    | 50     | 70      | 70    |  |

\* Part is resin sealed, this is not a hermetic part.

(See MIL index on pages CF9-11 for complete MIL part number listing)

### .375 ø L Circuit MIL Qualified Low Profile


| Part Number  | M15733<br>M28861<br>MIL No | See Pg.<br>LP28<br>for Fig | Rated Voltage |   |       |     | I<br>Amp | Min<br>Cap<br>µF | DCR<br>Max<br>Ohms | CKT | Max<br>L |          | Thd<br>Lgth | Minimum Insertion Loss (dB) |            |            |          |           |            |          |  |
|--------------|----------------------------|----------------------------|---------------|---|-------|-----|----------|------------------|--------------------|-----|----------|----------|-------------|-----------------------------|------------|------------|----------|-----------|------------|----------|--|
|              |                            |                            | 85°C          |   | 125°C |     |          |                  |                    |     | In       | (mm)     |             | 30<br>KHz                   | 150<br>KHz | 300<br>KHz | 1<br>MHz | 10<br>MHz | 100<br>MHz | 1<br>GHz |  |
| + 51-359-021 | 38-0004                    | 1                          |               | — | 50    | —   | 10       | 1.400            | 0.008              | LB  | 0.370    | (9.398)  | A           | 15                          | 28         | 33         | 44       | 60        | 70         | 70       |  |
| + 51-359-024 | 38-0005                    | 1                          | 80            | — | 50    | —   | 10       | 1.400            | 0.008              | LB  | 0.370    | (9.398)  | A           | 15                          | 28         | 33         | 44       | 60        | 70         | 70       |  |
| + 51-359-051 | 58-0001                    | 1                          | 80            | — | 50    | —   | 10       | 1.400            | 0.008              | LB  | 0.545    | (13.843) | A           | 15                          | 28         | 33         | 44       | 60        | 70         | 70       |  |
| 51-359-105   | 58-0004                    | 1                          | 80            | — | 50    | —   | 10       | 1.400            | 0.008              | LT  | 0.545    | (13.843) | B           | 15                          | 28         | 33         | 44       | 60        | 70         | 70       |  |
| + 51-359-044 | 49-0006                    | 1                          | 100           | — | 50    | —   | 15       | 1.200            | 0.010              | LB  | 0.370    | (9.398)  | A           | 15                          | 28         | 33         | 44       | 60        | 70         | 70       |  |
| + 51-359-055 | 49-0007                    | 3                          | 100           | — | 50    | —   | 15       | 1.200            | 0.010              | LB  | 0.450    | (11.43)  | A           | 15                          | 28         | 33         | 44       | 60        | 70         | 70       |  |
| 51-359-081   | 1-001◇                     | 1                          | —             | — | 50    | —   | 15       | 1.400            | 0.008              | LB  | 0.410    | (10.414) | A           | 15                          | 28         | 33         | 40       | 40        | 70         | 70       |  |
| 51-359-086   | 1-011◇                     | 1                          | —             | — | 50    | —   | 15       | 1.400            | 0.008              | LB  | 0.410    | (10.414) | B           | 15                          | 28         | 33         | 40       | 40        | 70         | 70       |  |
| + 51-359-053 | 49-0001                    | 4                          | 100           | — | 50    | —   | 15       | 0.680            | 0.010              | LB  | 0.319    | (8.103)  | A           | 8                           | 20         | 28         | 38       | 55        | 70         | 70       |  |
| 51-359-082   | 1-003◇                     | 1                          | —             | — | 70    | —   | 15       | 0.700            | 0.008              | LB  | 0.410    | (10.414) | A           | 10                          | 24         | 30         | 40       | 40        | 64         | 70       |  |
| 51-359-083   | 1-005◇                     | 1                          | —             | — | 100   | —   | 15       | 0.450            | 0.008              | LB  | 0.410    | (10.414) | A           | 6                           | 19         | 25         | 36       | 40        | 60         | 70       |  |
| 51-359-088   | 1-015◇                     | 1                          | —             | — | 100   | —   | 15       | 0.450            | 0.008              | LB  | 0.410    | (10.414) | B           | 6                           | 19         | 25         | 36       | 40        | 60         | 70       |  |
| 51-359-084   | 1-007◇                     | 1                          | —             | — | 150   | —   | 15       | 0.250            | 0.008              | LB  | 0.410    | (10.414) | A           | —                           | 14         | 20         | 31       | 40        | 56         | 70       |  |
| 51-359-050   | 38-0008                    | 1                          | —             | — | 200   | 125 | 15       | 0.150            | 0.008              | LB  | 0.370    | (9.398)  | A           | —                           | —          | —          | 6        | 25        | 42         | 60       |  |
| 51-359-085   | 1-009◇                     | 1                          | —             | — | 200   | 125 | 15       | 0.150            | 0.008              | LB  | 0.410    | (10.414) | A           | —                           | 10         | 16         | 26       | 40        | 52         | 70       |  |
| 51-359-090   | 1-019◇                     | 1                          | —             | — | 200   | 125 | 15       | 0.150            | 0.008              | LB  | 0.410    | (10.414) | B           | —                           | 10         | 16         | 26       | 40        | 52         | 70       |  |

† Also available through API's authorized distributors.

€ Also available through API's authorized European distributors/agents.

# Hermetically Sealed Threaded Case Filters

## .375 ø L Circuit




## .375 ø L Circuit Standard Product

| Part Number     | MIL No | Figure | Rated Voltage |   |       |   | I<br>Amp | Min<br>Cap<br>µF | DCR<br>Max<br>Ohms | CKT | Max<br>L |          | Thd<br>Lgth | Minimum Insertion Loss (dB) |            |            |          |           |            |          |  |
|-----------------|--------|--------|---------------|---|-------|---|----------|------------------|--------------------|-----|----------|----------|-------------|-----------------------------|------------|------------|----------|-----------|------------|----------|--|
|                 |        |        | 85°C          |   | 125°C |   |          |                  |                    |     | In       | (mm)     |             | 30<br>KHz                   | 150<br>KHz | 300<br>KHz | 1<br>MHz | 10<br>MHz | 100<br>MHz | 1<br>GHz |  |
| 51-353-007      | —      | 1      | 80            | — | 50    | — | 0.06     | 1.400            | 70.000             | LB  | 0.770    | (19.558) | A           | 44                          | 70         | 70         | 70       | 70        | 70         | 70       |  |
| 51-353-095      | —      | 1      | 80            | — | 50    | — | 0.15     | 1.400            | 12.000             | LT  | 0.960    | (24.384) | A           | 21                          | 52         | 64         | 70       | 70        | 70         | 70       |  |
| 51-353-003      | —      | 1      | 80            | — | 50    | — | 0.45     | 1.400            | 1.200              | LB  | 0.770    | (19.558) | A           | 16                          | 31         | 37         | 55       | 70        | 70         | 70       |  |
| 51-353-099      | —      | 1      | 80            | — | 50    | — | 1.00     | 1.400            | 0.250              | LT  | 0.770    | (19.558) | A           | 16                          | 33         | 44         | 70       | 70        | 70         | 70       |  |
| 51-353-100      | —      | 1      | 80            | — | 50    | — | 5.00     | 1.400            | 0.015              | LT  | 0.770    | (19.558) | A           | 15                          | 28         | 33         | 46       | 70        | 70         | 70       |  |
| † 9200-300-0025 | —      | 1      | 80            | — | 50    | — | 10.00    | 1.200            | 0.010              | LB  | 0.450    | (11.430) | A           | 15                          | 28         | 33         | 44       | 60        | 70         | 70       |  |


† Also available through API's authorized distributors.

# Hermetically Sealed Threaded Case Filters

## L-C Filter LT



## L-C Filter LB



## .375 ø L Circuit Standard Product *continued*

| Part Number     | MIL No | See Pg. LP30 for Fig | Rated Voltage |    |          |     | I Amp | Min Cap µF | DCR Max Ohms | CKT | Max L |          | Thd Lgth | Minimum Insertion Loss (dB) |         |         |       |        |         |       |
|-----------------|--------|----------------------|---------------|----|----------|-----|-------|------------|--------------|-----|-------|----------|----------|-----------------------------|---------|---------|-------|--------|---------|-------|
|                 |        |                      | 85°C DC       | AC | 125°C DC | AC  |       |            |              |     | In    | (mm)     |          | 30 KHz                      | 150 KHz | 300 KHz | 1 MHz | 10 MHz | 100 MHz | 1 GHz |
| † 9200-303-0095 | —      | 1                    | 80            | —  | 50       | —   | 10.00 | 1.200      | 0.010        | LB  | 0.450 | (11.430) | B        | 15                          | 28      | 33      | 44    | 60     | 70      | 70    |
| 51-353-101      | —      | 1                    | 80            | —  | 50       | —   | 10.00 | 1.400      | 0.010        | LT  | 0.450 | (11.430) | A        | 14                          | 28      | 33      | 44    | 60     | 70      | 70    |
| 51-353-109      | —      | 1                    | 80            | —  | 50       | —   | 10.00 | 1.400      | 0.010        | LT  | 0.450 | (11.430) | B        | 15                          | 28      | 33      | 44    | 60     | 70      | 70    |
| 51-353-120      | —      | 1                    | 150           | —  | 100      | —   | 1.00  | 0.750      | 0.250        | LB  | 0.758 | (19.253) | A        | 9                           | 27      | 36      | 57    | 70     | 70      | 70    |
| 9000-103-0019   | —      | 1                    | 150           | —  | 100      | —   | 5.00  | 0.450      | 0.015        | LT  | 0.758 | (19.253) | B        | 6                           | 20      | 26      | 37    | 68     | 70      | 70    |
| SCI-2120-014    | —      | 1                    | 150           | —  | 100      | —   | 10.00 | 1.000      | 0.003        | LB  | 0.450 | (11.430) | B        | 14                          | 28      | 34      | 44    | 52     | 70      | 70    |
| 51-353-110      | —      | 1                    | 250           | —  | 200      | 125 | 1.00  | 0.250      | 0.250        | LT  | 0.758 | (19.253) | A        | —                           | 17      | 29      | 50    | 70     | 70      | 70    |
| † 51-353-111    | —      | 1                    | 250           | —  | 200      | 125 | 1.00  | 0.250      | 0.250        | LB  | 0.758 | (19.253) | A        | —                           | 17      | 29      | 50    | 70     | 70      | 70    |
| 51-353-112      | —      | 1                    | 250           | —  | 200      | 125 | 3.00  | 0.250      | 0.050        | LT  | 0.758 | (19.253) | A        | —                           | 13      | 20      | 35    | 70     | 70      | 70    |
| † 51-353-113    | —      | 1                    | 250           | —  | 200      | 125 | 3.00  | 0.250      | 0.050        | LB  | 0.758 | (19.253) | A        | —                           | 13      | 20      | 35    | 70     | 70      | 70    |
| 51-353-114      | —      | 1                    | 250           | —  | 200      | 125 | 5.00  | 0.250      | 0.015        | LT  | 0.758 | (19.253) | A        | —                           | 12      | 20      | 30    | 62     | 70      | 70    |
| 51-353-116      | —      | 1                    | 250           | —  | 200      | 125 | 10.00 | 0.250      | 0.010        | LT  | 0.450 | (11.430) | A        | —                           | 15      | 20      | 30    | 50     | 70      | 70    |
| SCI-2320-010    | —      | 1                    | 300           | —  | 300      | 125 | 0.50  | 0.150      | 1.000        | LB  | 0.758 | (19.253) | B        | —                           | 23      | 35      | 56    | 70     | 70      | 70    |
| SCI-2320-004    | —      | 1                    | 300           | —  | 300      | 125 | 1.00  | 0.150      | 0.250        | LB  | 0.758 | (19.253) | A        | —                           | 10      | 21      | 41    | 70     | 70      | 70    |
| SCI-2320-005    | —      | 1                    | 300           | —  | 300      | 125 | 2.00  | 0.150      | 0.063        | LB  | 0.758 | (19.253) | A        | —                           | 8       | 14      | 30    | 70     | 70      | 70    |
| SCI-2320-006    | —      | 1                    | 300           | —  | 300      | 125 | 3.00  | 0.150      | 0.027        | LB  | 0.758 | (19.253) | A        | —                           | 8       | 14      | 26    | 64     | 70      | 70    |
| SCI-2320-007    | —      | 1                    | 300           | —  | 300      | 125 | 10.00 | 0.150      | 0.003        | LB  | 0.450 | (11.430) | A        | —                           | 8       | 14      | 25    | 45     | 52      | 70    |
| SCI-2320-014    | —      | 1                    | 300           | —  | 300      | 125 | 10.00 | 0.150      | 0.003        | LB  | 0.450 | (11.430) | B        | —                           | 8       | 14      | 25    | 45     | 52      | 70    |

(See MIL index on pages CF9-11 for complete MIL part number listing)


## .375 ø L Circuit MIL Qualified Profile

| Part Number  | M15733<br>MIL<br>No | See Pg.<br>LP30<br>for Fig | Rated Voltage |   |       |   | I<br>Amp | Min<br>Cap<br>µF | DCR<br>Max<br>Ohms | CKT | Max<br>L |          | Thd<br>Lgth | Minimum Insertion Loss (dB) |            |            |          |           |            |          |  |
|--------------|---------------------|----------------------------|---------------|---|-------|---|----------|------------------|--------------------|-----|----------|----------|-------------|-----------------------------|------------|------------|----------|-----------|------------|----------|--|
|              |                     |                            | 85°C          |   | 125°C |   |          |                  |                    |     | In       | (mm)     |             | 30<br>KHz                   | 150<br>KHz | 300<br>KHz | 1<br>MHz | 10<br>MHz | 100<br>MHz | 1<br>GHz |  |
| 51-390-018   | 23-0026             | 1                          | —             | — | 50    | — | 0.50     | 1.400            | 0.360              | LB  | 0.630    | (16.002) | A           | 12                          | 36         | 48         | 69       | 70        | 70         | 70       |  |
| 51-390-026   | 23-0038             | 1                          | —             | — | 50    | — | 1.00     | 1.400            | 0.140              | LB  | 0.630    | (16.002) | A           | 11                          | 26         | 36         | 55       | 70        | 70         | 70       |  |
| 51-390-034   | 23-0050             | 1                          | —             | — | 50    | — | 2.00     | 1.400            | 0.070              | LB  | 0.630    | (16.002) | A           | 10                          | 24         | 32         | 48       | 70        | 70         | 70       |  |
| + 51-353-067 | 24-0006             | 1                          | 80            | — | 50    | — | 10.00    | 1.400            | 0.010              | LB  | 0.760    | (19.304) | B           | 15                          | 28         | 31         | 42       | 56        | 70         | 70       |  |
| 51-353-207   | 34-0007             | 1                          | —             | — | 50    | — | 10.00    | 1.400            | 0.010              | LB  | 0.760    | (19.304) | A           | 15                          | 28         | 31         | 42       | 56        | 70         | 70       |  |
| 51-444-072   | 58-0002             | 1                          | 80            | — | 50    | — | 10.00    | 1.400            | 0.008              | LT  | 0.545    | (13.843) | A           | 15                          | 28         | 33         | 44       | 60        | 70         | 70       |  |
| + 51-353-066 | 24-0005             | 1                          | 80            | — | 50    | — | 10.00    | 1.400            | 0.010              | LB  | 0.760    | (19.304) | A           | 15                          | 28         | 31         | 42       | 56        | 70         | 70       |  |
| 51-353-287   | 39-0014             | 1                          | —             | — | 50    | — | 10.00    | 1.400            | 0.003              | LT  | 0.760    | (19.304) | B           | 14                          | 28         | 34         | 44       | 52        | 70         | 70       |  |
| + 51-444-060 | 24-0008             | 1                          | 80            | — | 50    | — | 10.00    | 1.400            | 0.010              | LT  | 0.740    | (18.796) | B           | 15                          | 28         | 31         | 42       | 56        | 70         | 70       |  |
| + 51-343-028 | 38-0002             | 1                          | —             | — | 50    | — | 15.00    | 1.400            | 0.008              | LB  | 0.481    | (12.217) | A           | 15                          | 28         | 33         | 44       | 64        | 70         | 70       |  |
| + 51-343-034 | 38-0006             | 1                          | —             | — | 50    | — | 15.00    | 1.400            | 0.008              | LB  | 0.481    | (12.217) | B           | 15                          | 28         | 33         | 44       | 64        | 70         | 70       |  |
| 51-353-053   | 25-0003             | 1                          | —             | — | 100   | — | 1.00     | 0.450            | 0.250              | LB  | 0.738    | (18.745) | A           | 6                           | 23         | 34         | 55       | 70        | 70         | 70       |  |
| + 51-353-054 | 25-0005             | 1                          | —             | — | 100   | — | 5.00     | 0.450            | 0.015              | LT  | 0.758    | (19.253) | A           | 6                           | 17         | 23         | 35       | 69        | 70         | 70       |  |
| + 51-353-055 | 25-0008             | 1                          | —             | — | 100   | — | 5.00     | 0.450            | 0.015              | LB  | 0.738    | (18.745) | A           | 6                           | 17         | 23         | 35       | 69        | 70         | 70       |  |
| 51-353-155   | 39-0008             | 1                          | —             | — | 100   | — | 5.00     | 0.450            | 0.015              | LB  | 0.760    | (19.304) | A           | 6                           | 20         | 26         | 35       | 60        | 60         | 70       |  |
| 51-444-039   | 25-0017             | 1                          | —             | — | 100   | — | 5.00     | 0.450            | 0.015              | LT  | 0.758    | (19.253) | B           | 6                           | 17         | 23         | 35       | 69        | 70         | 70       |  |


† Also available through API's authorized distributors.

## Hermetically Sealed Threaded Case Filters

### L-C Filter LT



### L-C Filter LB



### .375 ø L Circuit MIL Qualified Profile *continued*

(See MIL index on pages CF9-11 for  
complete MIL part number listing)


| Part Number | M15733<br>MIL<br>No | See Pg.<br>LP30<br>for Fig | Rated Voltage |    |       |     | I<br>Amp | Min<br>Cap<br>µF | DCR<br>Max<br>Ohms | CKT | Max<br>L |          | Thd<br>Lgth | Minimum Insertion Loss (dB) |            |            |          |           |            |          |  |
|-------------|---------------------|----------------------------|---------------|----|-------|-----|----------|------------------|--------------------|-----|----------|----------|-------------|-----------------------------|------------|------------|----------|-----------|------------|----------|--|
|             |                     |                            | 85°C          |    | 125°C |     |          |                  |                    |     | In       | (mm)     |             | 30<br>KHz                   | 150<br>KHz | 300<br>KHz | 1<br>MHz | 10<br>MHz | 100<br>MHz | 1<br>GHz |  |
|             |                     |                            | DC            | AC | DC    | AC  |          |                  |                    |     |          |          |             |                             |            |            |          |           |            |          |  |
| 51-444-040  | 25-0020             | 1                          | —             | —  | 100   |     | 5.00     | 0.450            | 0.015              | LB  | 0.738    | (18.745) | B           | 6                           | 17         | 23         | 35       | 69        | 70         | 70       |  |
| 51-353-156  | 39-0009             | 1                          | —             | —  | 100   |     | 10.00    | 0.450            | 0.003              | LT  | 0.760    | (19.304) | A           | 6                           | 20         | 26         | 35       | 56        | 60         | 70       |  |
| 51-353-157  | 39-0010             | 1                          | —             | —  | 100   |     | 10.00    | 0.450            | 0.003              | LB  | 0.760    | (19.304) | A           | 6                           | 20         | 26         | 35       | 56        | 60         | 70       |  |
| +51-353-076 | 26-0001             | 1                          | —             | —  | 150   | 125 | 1.00     | 0.250            | 0.250              | LT  | 0.758    | (19.253) | A           | —                           | 13         | 24         | 45       | 80        | 70         | 70       |  |
| +51-353-077 | 26-0003             | 1                          | —             | —  | 150   | 125 | 1.00     | 0.250            | 0.250              | LB  | 0.738    | (18.745) | A           | —                           | 13         | 24         | 45       | 80        | 70         | 70       |  |
| 51-444-043  | 26-0013             | 1                          | —             | —  | 150   | 125 | 1.00     | 0.250            | 0.250              | LT  | 0.758    | (19.253) | B           | —                           | 13         | 24         | 45       | 80        | 70         | 70       |  |
| 51-444-044  | 26-0015             | 1                          | —             | —  | 150   | 125 | 1.00     | 0.250            | 0.250              | LB  | 0.738    | (18.745) | B           | —                           | 13         | 24         | 45       | 80        | 70         | 70       |  |
| 51-390-040  | 23-0058             | 1                          | —             | —  | 150   |     | 2.00     | 0.250            | 0.070              | LT  | 0.630    | (16.002) | A           | 3                           | 15         | 23         | 38       | 60        | 70         | 60       |  |
| 51-390-039  | 23-0057             | 1                          | —             | —  | 150   |     | 2.00     | 0.250            | 0.070              | LT  | 0.630    | (16.002) | B           | 3                           | 15         | 23         | 38       | 60        | 70         | 60       |  |
| 51-444-005  | 34-0015             | 1                          | —             | —  | 150   | 125 | 3.00     | 0.150            | 0.050              | LT  | 0.758    | (19.253) | B           | —                           | 8          | 15         | 30       | 68        | 70         | 70       |  |
| +51-353-078 | 26-0004             | 1                          | —             | —  | 150   | 125 | 3.00     | 0.250            | 0.050              | LT  | 0.758    | (19.253) | A           | —                           | 8          | 15         | 30       | 68        | 70         | 70       |  |
| +51-353-079 | 26-0006             | 1                          | —             | —  | 150   | 125 | 3.00     | 0.250            | 0.050              | LB  | 0.738    | (18.745) | A           | —                           | 8          | 15         | 30       | 68        | 70         | 70       |  |
| +51-444-046 | 26-0018             | 1                          | —             | —  | 150   | 125 | 3.00     | 0.250            | 0.050              | LB  | 0.738    | (18.745) | B           | —                           | 8          | 15         | 30       | 68        | 70         | 70       |  |
| 51-444-047  | 26-0019             | 1                          | —             | —  | 150   | 125 | 5.00     | 0.250            | 0.015              | LT  | 0.758    | (19.253) | B           | —                           | 8          | 14         | 25       | 58        | 70         | 70       |  |
| +51-353-080 | 26-0007             | 1                          | —             | —  | 150   | 125 | 5.00     | 0.250            | 0.015              | LT  | 0.758    | (19.253) | A           | —                           | 8          | 14         | 25       | 58        | 70         | 70       |  |
| 51-353-081  | 26-0010             | 1                          | —             | —  | 150   | 125 | 5.00     | 0.250            | 0.015              | LB  | 0.738    | (18.745) | A           | —                           | 8          | 14         | 25       | 58        | 70         | 70       |  |
| 51-444-027  | 34-0030             | 1                          | —             | —  | 200   | 125 | 5.00     | 0.250            | 0.150              | LB  | 0.900    | (22.860) | A           | 2                           | 15         | 21         | 32       | 60        | 70         | 70       |  |
| 51-444-117  | 54-0018             | 2                          | —             | —  | 300   | 125 | 1.00     | 0.150            | 0.250              | LB  | 0.740    | (18.796) | A           | —                           | 10         | 21         | 41       | 70        | 70         | 70       |  |

† Also available through API's authorized distributors.

# Hermetically Sealed Threaded Case Filters



## .375 ø Pi Circuit



## .375 ø Pi Circuit Standard Product

| Part Number     | MIL No | Figure | Rated Voltage |     |       |     | I Amp | Min Cap μF | DCR Max Ohms | Max L |          | Thd Lgth | Minimum Insertion Loss (dB) |         |         |       |        |         |       |  |
|-----------------|--------|--------|---------------|-----|-------|-----|-------|------------|--------------|-------|----------|----------|-----------------------------|---------|---------|-------|--------|---------|-------|--|
|                 |        |        | 85°C          |     | 125°C |     |       |            |              | In    | L (mm)   |          | 30 KHz                      | 150 KHz | 300 KHz | 1 MHz | 10 MHz | 100 MHz | 1 GHz |  |
| SCI-2030-010    | —      | 2      | 80            | —   | 50    | —   | 0.50  | 1.500      | 1.000        | 0.758 | (19.253) | B        | 24                          | 66      | 70      | 70    | 70     | 70      |       |  |
| SCI-2030-004    | —      | 2      | 80            | —   | 50    | —   | 1.00  | 1.500      | 0.250        | 0.758 | (19.253) | A        | 15                          | 54      | 70      | 70    | 70     | 70      |       |  |
| SCI-2030-005    | —      | 2      | 80            | —   | 50    | —   | 2.00  | 1.500      | 0.063        | 0.758 | (19.253) | A        | —                           | 45      | 62      | 70    | 70     | 70      |       |  |
| SCI-2030-006    | —      | 2      | 80            | —   | 50    | —   | 3.00  | 1.500      | 0.027        | 0.758 | (19.253) | A        | —                           | 35      | 55      | 70    | 70     | 70      |       |  |
| SCI-2030-013    | —      | 2      | 80            | —   | 50    | —   | 3.00  | 1.500      | 0.027        | 0.758 | (19.253) | B        | —                           | 35      | 55      | 70    | 70     | 70      |       |  |
| † 9001-100-1080 | —      | 1      | 80            | —   | 50    | —   | 5.00  | 2.800      | 0.015        | 0.758 | (19.253) | A        | —                           | 18      | 60      | 70    | 70     | 70      |       |  |
| † 9001-100-1081 | —      | 1      | 80            | —   | 50    | —   | 10.0  | 2.800      | 0.005        | 0.758 | (19.253) | A        | 21                          | 32      | 40      | 35    | 68     | 70      |       |  |
| SCI-2130-009    | —      | 1      | 150           | —   | 100   | —   | 0.25  | 1.000      | 4.000        | 0.758 | (19.253) | B        | 28                          | 70      | 70      | 70    | 70     | 70      |       |  |
| 51-311-319      | —      | 1      | 150           | —   | 100   | —   | 0.50  | 1.000      | 0.600        | 0.758 | (19.253) | A        | —                           | 51      | 69      | 70    | 70     | 70      |       |  |
| † 9001-100-1010 | —      | 1      | 150           | —   | 100   | —   | 0.50  | 1.000      | 0.600        | 0.758 | (19.253) | A        | 6                           | 39      | 68      | 70    | 70     | 70      |       |  |
| 51-311-320      | —      | 1      | 150           | —   | 100   | —   | 1.00  | 1.000      | 0.250        | 0.758 | (19.253) | A        | —                           | 41      | 60      | 70    | 70     | 70      |       |  |
| † 9001-100-1013 | —      | 1      | 150           | —   | 100   | —   | 1.00  | 1.000      | 0.250        | 0.758 | (19.253) | A        | —                           | 28      | 59      | 70    | 70     | 70      |       |  |
| 51-311-321      | —      | 1      | 150           | —   | 100   | —   | 3.00  | 1.000      | 0.060        | 0.758 | (19.253) | A        | —                           | 16      | 41      | 70    | 70     | 70      |       |  |
| † 51-311-322    | —      | 1      | 150           | —   | 100   | —   | 5.00  | 1.000      | 0.015        | 0.758 | (19.253) | A        | —                           | —       | 28      | 65    | 70     | 70      |       |  |
| SCI-2130-007    | —      | 1      | 150           | —   | 100   | —   | 10.0  | 1.000      | 0.003        | 0.758 | (19.253) | A        | 9                           | 24      | 29      | 40    | 70     | 70      |       |  |
| SCI-2130-014    | —      | 1      | 150           | —   | 100   | —   | 10.0  | 1.000      | 0.005        | 0.758 | (19.253) | B        | 9                           | 24      | 29      | 40    | 70     | 70      |       |  |
| 51-311-316      | —      | 1      | 250           | 125 | 200   | 125 | 1.00  | 0.300      | 0.250        | 0.758 | (19.253) | A        | —                           | 20      | 40      | 70    | 70     | 70      |       |  |
| 51-311-317      | —      | 1      | 250           | 125 | 200   | 125 | 3.00  | 0.300      | 0.050        | 0.758 | (19.253) | A        | —                           | —       | 20      | 55    | 70     | 70      |       |  |
| † 9001-100-1025 | —      | 1      | 250           | 125 | 200   | 125 | 5.00  | 0.300      | 0.015        | 0.758 | (19.253) | A        | —                           | —       | 12      | 50    | 70     | 80      |       |  |
| SCI-2330-009    | —      | 1      | 300           | 125 | 300   | 125 | 0.25  | 0.300      | 4.000        | 0.758 | (19.253) | B        | 8                           | 50      | 66      | 70    | 70     | 70      |       |  |
| SCI-2330-010    | —      | 1      | 300           | 125 | 300   | 125 | 0.50  | 0.300      | 1.000        | 0.758 | (19.253) | B        | —                           | 40      | 56      | 70    | 70     | 70      |       |  |
| SCI-2330-012    | —      | 1      | 300           | 125 | 300   | 125 | 2.00  | 0.300      | 0.063        | 0.758 | (19.253) | B        | —                           | 18      | 33      | 63    | 70     | 70      |       |  |
| SCI-2330-007    | —      | 1      | 300           | 125 | 300   | 125 | 10.0  | 0.300      | 0.003        | 0.758 | (19.253) | A        | —                           | 14      | 20      | 30    | 70     | 70      |       |  |

† Also available through API's authorized distributors.

# Hermetically Sealed Threaded Case Filters

## .375 ø Pi Circuit MIL Qualified Product

(See MIL index on pages CF9-11 for complete MIL part number listing)

| Part Number  | M15733 MIL No | See Pg. LP33 for Fig. | Rated Voltage |         |          |          | I Amp | Min Cap µF | DCR Max Ohms | Max L |          | Thd Lgth | Minimum Insertion Loss (dB) |         |         |       |        |         |       |  |
|--------------|---------------|-----------------------|---------------|---------|----------|----------|-------|------------|--------------|-------|----------|----------|-----------------------------|---------|---------|-------|--------|---------|-------|--|
|              |               |                       | 85°C DC       | 85°C AC | 125°C DC | 125°C AC |       |            |              | In    | (mm)     |          | 30 KHz                      | 150 KHz | 300 KHz | 1 MHz | 10 MHz | 100 MHz | 1 GHz |  |
| 51-390-305   | 23-0017       | 1                     | —             | —       | 50       | —        | 0.30  | 2.800      | 0.770        | 0.730 | (18.542) | B        | 29                          | 73      | 80      | 80    | 80     | 80      | 80    |  |
| 51-390-314   | 23-0042       | 1                     | —             | —       | 50       | —        | 1.00  | 2.800      | 0.140        | 0.730 | (18.542) | A        | 8                           | 52      | 71      | 80    | 80     | 80      | 80    |  |
| + 51-390-318 | 23-0054       | 1                     | —             | —       | 50       | —        | 2.00  | 1.500      | 0.070        | 0.730 | (18.542) | A        | —                           | 46      | 65      | 80    | 80     | 80      | 80    |  |
| + 51-390-317 | 23-0053       | 1                     | —             | —       | 50       | —        | 2.00  | 1.500      | 0.070        | 0.730 | (18.542) | B        | —                           | 46      | 65      | 80    | 80     | 80      | 80    |  |
| 51-311-311   | 25-0010       | 1                     | —             | —       | 100      | —        | 0.25  | 0.900      | 1.500        | 0.793 | (20.142) | A        | —                           | 48      | 66      | 80    | 80     | 80      | 70    |  |
| + 51-311-308 | 25-0002       | 1                     | —             | —       | 100      | —        | 1.00  | 0.500      | 0.250        | 0.793 | (20.142) | A        | —                           | 33      | 52      | 80    | 80     | 80      | 70    |  |
| + 51-311-309 | 25-0004       | 1                     | —             | —       | 100      | —        | 3.00  | 0.660      | 0.050        | 0.793 | (20.142) | A        | —                           | 17      | 34      | 68    | 80     | 80      | 70    |  |
| + 51-311-310 | 25-0006       | 1                     | —             | —       | 100      | —        | 5.00  | 0.900      | 0.015        | 0.793 | (20.142) | A        | —                           | —       | 17      | 57    | 80     | 80      | 70    |  |
| 51-353-344   | 39-0011       | 1                     | —             | —       | 100      | —        | 10.0  | 0.990      | 0.003        | 0.760 | (19.304) | A        | 9                           | 24      | 29      | 40    | 70     | 70      | 70    |  |
| 51-353-345   | 39-0012       | 1                     | —             | —       | 100      | —        | 10.0  | 0.990      | 0.003        | 0.760 | (19.304) | A        | 9                           | 24      | 29      | 40    | 70     | 70      | 70    |  |
| + 51-311-314 | 26-0011       | 1                     | —             | —       | 150      | 125      | 0.25  | 0.300      | 1.500        | 0.793 | (20.142) | A        | —                           | 29      | 47      | 70    | 80     | 80      | 70    |  |
| 51-390-312   | 23-0036       | 1                     | —             | —       | 150      | —        | 0.50  | 0.500      | 0.360        | 0.730 | (18.542) | A        | —                           | 48      | 66      | 70    | 70     | 70      | 70    |  |
| 51-390-311   | 23-0035       | 1                     | —             | —       | 150      | —        | 0.50  | 0.500      | 0.360        | 0.730 | (18.542) | B        | —                           | 48      | 66      | 70    | 70     | 70      | 70    |  |
| + 51-353-336 | 26-0002       | 1                     | —             | —       | 150      | 125      | 1.00  | 0.300      | 0.250        | 0.793 | (20.142) | A        | —                           | 11      | 32      | 63    | 80     | 80      | 70    |  |
| 51-390-315   | 23-0047       | 1                     | —             | —       | 150      | —        | 1.00  | 0.500      | 0.140        | 0.730 | (18.542) | B        | —                           | 32      | 51      | 70    | 70     | 70      | 70    |  |
| 51-311-312   | 26-0005       | 1                     | —             | —       | 150      | 125      | 3.00  | 0.300      | 0.050        | 0.793 | (20.142) | A        | —                           | 5       | 6       | 47    | 80     | 80      | 70    |  |
| 51-311-408   | 54-0005       | 2                     | —             | —       | 300      | 115      | 1.00  | 0.300      | 0.250        | 0.761 | (19.329) | A        | —                           | 23      | 43      | 70    | 70     | 70      | 70    |  |

† Also available through API's authorized distributors.

## Transient Suppression Pi Filters

| Part Number | See Pg. LP33 for Fig. | Rated Volt. VDC | I Amp | Min Cap µF | DCR Min Mohms | Max RDC Ohms | Transient Suppressor* |           |          |          | Length<br>In (mm) |          | Max Thd Lgth | Minimum Insertion Loss (dB) |         |       |        |         |       |
|-------------|-----------------------|-----------------|-------|------------|---------------|--------------|-----------------------|-----------|----------|----------|-------------------|----------|--------------|-----------------------------|---------|-------|--------|---------|-------|
|             |                       |                 |       |            |               |              | VR* (VDC)             | BV* (VDC) | IT* (MA) | IPP* (A) |                   |          |              | 30 KHz                      | 300 KHz | 1 MHz | 10 MHz | 100 MHz | 1 GHz |
| 51-570-300  | 1                     | 5               | 0.50  | 1.400      | 0.500         | 0.600        | 6.5                   | 7.22/7.98 | 10       | 44.7     | 1.179             | (29.947) | A            | 23                          | 57      | 70    | 70     | 70      | 70    |
| 51-570-301  | 1                     | 5               | 1.00  | 1.400      | 0.500         | 0.350        | 6.5                   | 7.22/7.98 | 10       | 44.7     | 1.179             | (29.947) | A            | 3                           | 47      | 70    | 70     | 70      | 70    |
| 51-570-302  | 1                     | 5               | 3.00  | 1.400      | 0.500         | 0.060        | 6.5                   | 7.22/7.98 | 10       | 44.7     | 1.179             | (29.947) | A            | —                           | 23      | 58    | 70     | 70      | 70    |
| 51-570-303  | 1                     | 5               | 5.00  | 1.400      | 0.500         | 0.015        | 6.5                   | 7.22/7.98 | 10       | 44.7     | 1.179             | (29.947) | A            | —                           | 17      | 48    | 70     | 70      | 70    |
| 51-570-304  | 1                     | 5               | 10.00 | 1.400      | 0.500         | 0.005        | 6.5                   | 7.22/7.98 | 10       | 44.7     | 1.179             | (29.947) | A            | 16                          | 26      | 35    | 40     | 60      | 70    |
| 51-570-310  | 1                     | 28              | 0.50  | 1.400      | 30.000        | 0.600        | 33.0                  | 36.7/40.6 | 1        | 9.4      | 1.179             | (29.947) | A            | 23                          | 57      | 70    | 70     | 70      | 70    |
| 51-570-311  | 1                     | 28              | 1.00  | 1.400      | 30.000        | 0.350        | 33.0                  | 36.7/40.6 | 1        | 9.4      | 1.179             | (29.947) | A            | 3                           | 47      | 70    | 70     | 70      | 70    |
| 51-570-312  | 1                     | 28              | 3.00  | 1.400      | 30.000        | 0.060        | 33.0                  | 36.7/40.6 | 1        | 9.4      | 1.179             | (29.947) | A            | —                           | 23      | 58    | 70     | 70      | 70    |
| 51-570-313  | 1                     | 28              | 5.00  | 1.400      | 30.000        | 0.015        | 33.0                  | 36.7/40.6 | 1        | 9.4      | 1.179             | (29.947) | A            | —                           | 17      | 48    | 70     | 70      | 70    |
| 51-570-314  | 1                     | 28              | 10.00 | 1.400      | 30.000        | 0.005        | 33.0                  | 36.7/40.6 | 1        | 9.4      | 1.179             | (29.947) | A            | 16                          | 26      | 35    | 40     | 60      | 70    |
| 51-570-320  | 1                     | 50              | 0.50  | 1.400      | 50.000        | 0.600        | 58.0                  | 64.4/71.2 | 1        | 5.3      | 1.179             | (29.947) | A            | 23                          | 57      | 70    | 70     | 70      | 70    |
| 51-570-321  | 1                     | 50              | 1.00  | 1.400      | 50.000        | 0.350        | 58.0                  | 64.4/71.2 | 1        | 5.3      | 1.179             | (29.947) | A            | 3                           | 47      | 70    | 70     | 70      | 70    |
| 51-570-322  | 1                     | 50              | 3.00  | 1.400      | 50.000        | 0.060        | 58.0                  | 64.4/71.2 | 1        | 5.3      | 1.179             | (29.947) | A            | —                           | 23      | 58    | 70     | 70      | 70    |
| 51-570-323  | 1                     | 50              | 5.00  | 1.400      | 50.000        | 0.015        | 58.0                  | 64.4/71.2 | 1        | 5.3      | 1.179             | (29.947) | A            | —                           | 17      | 48    | 70     | 70      | 70    |
| 51-570-324  | 1                     | 50              | 10.00 | 1.400      | 50.000        | 0.005        | 58.0                  | 64.4/71.2 | 1        | 5.3      | 1.179             | (29.947) | A            | 16                          | 26      | 35    | 40     | 60      | 70    |

\* Transient Suppression definitions and ratings

VR = Reverse standoff voltage  
BV = Breakdown voltage

IPP = Max. peak pulse current  
IT = Test current

# Hermetically Sealed Threaded Case Filters



## .375 ø T Circuit

Thread length: A - 0.187 (4.76) B - 0.312 (7.92)




Figure 1

Note: Max. O.D. is ø .416" for Military QPL Filters.

Dimensions in inches (mm)

## .375 ø T Circuit Standard Product

| Part Number     | MIL No | Figure | Rated Voltage |   |       |     | I Amp | Min Cap μF | DCR Max Ohms | Max L |          | Thd Lgth | Minimum Insertion Loss (dB) |         |         |       |        |         |       |  |
|-----------------|--------|--------|---------------|---|-------|-----|-------|------------|--------------|-------|----------|----------|-----------------------------|---------|---------|-------|--------|---------|-------|--|
|                 |        |        | 85°C          |   | 125°C |     |       |            |              | In    | (mm)     |          | 30 KHz                      | 150 KHz | 300 KHz | 1 MHz | 10 MHz | 100 MHz | 1 GHz |  |
| SCI-2040-012    | —      | 1      | 80            | — | 50    | —   | 2.00  | 1.400      | 0.126        | 1.071 | (27.203) | B        | 8                           | 22      | 30      | 55    | 70     | 70      | 70    |  |
| SCI-2040-013    | —      | 1      | 80            | — | 50    | —   | 3.00  | 1.400      | 0.054        | 1.071 | (27.203) | B        | 8                           | 22      | 28      | 43    | 70     | 70      | 70    |  |
| † 9004-100-2017 | —      | 1      | 80            | — | 50    | —   | 15.0  | 1.400      | 0.005        | 1.179 | (29.947) | A        | 17                          | 27      | 34      | 44    | 60     | 70      | 70    |  |
| SCI-2140-004    | —      | 1      | 150           | — | 100   | —   | 1.00  | 0.500      | 0.500        | 1.070 | (27.178) | A        | 4                           | 25      | 40      | 70    | 70     | 70      | 70    |  |
| SCI-2140-006    | —      | 1      | 150           | — | 100   | —   | 3.00  | 0.500      | 0.054        | 1.071 | (27.203) | A        | 4                           | 19      | 24      | 39    | 70     | 70      | 70    |  |
| SCI-2140-007    | —      | 1      | 150           | — | 100   | —   | 10.0  | 0.500      | 0.010        | 1.071 | (27.203) | A        | 4                           | 19      | 24      | 34    | 57     | 70      | 70    |  |
| SCI-2340-009    | —      | 1      | 300           | — | 300   | 125 | 0.25  | 0.150      | 8.000        | 1.071 | (27.203) | B        | 11                          | 57      | 70      | 70    | 70     | 70      | 70    |  |
| SCI-2340-004    | —      | 1      | 300           | — | 300   | 125 | 1.00  | 0.150      | 0.500        | 1.071 | (27.203) | A        | —                           | 13      | 29      | 59    | 70     | 70      | 70    |  |
| SCI-2340-013    | —      | 1      | 300           | — | 300   | 125 | 3.00  | 0.150      | 0.054        | 1.071 | (27.203) | B        | —                           | 8       | 14      | 29    | 70     | 70      | 70    |  |
| SCI-2340-014    | —      | 1      | 300           | — | 300   | 125 | 10.0  | 0.150      | 0.010        | 1.071 | (27.203) | B        | —                           | 8       | 14      | 24    | 47     | 70      | 70    |  |

† Also available through API's authorized distributors.

(See MIL index on pages CF8-10 for complete MIL part number listing)

## .375 ø T Circuit MIL Qualified Product

| Part Number  | M15733<br>MIL<br>No | Figure | Rated Voltage |    |             |     | I<br>Amp | Min<br>Cap<br>µF | DCR<br>Max<br>Ohms | Max<br>L<br><i>(mm)</i>  | Thd<br>Lgth | Minimum Insertion Loss (dB) |            |            |          |           |            |          |  |
|--------------|---------------------|--------|---------------|----|-------------|-----|----------|------------------|--------------------|--------------------------|-------------|-----------------------------|------------|------------|----------|-----------|------------|----------|--|
|              |                     |        | 85°C<br>DC    | AC | 125°C<br>DC | AC  |          |                  |                    |                          |             | 30<br>KHz                   | 150<br>KHz | 300<br>KHz | 1<br>MHz | 10<br>MHz | 100<br>MHz | 1<br>GHz |  |
| 51-382-609   | 25-0024             | 1      | —             | —  | 100         | —   | 2.00     | 0.750            | 0.100              | 1.179<br><i>(29.947)</i> | B           | 10                          | 22         | 31         | 55       | 80        | 70         | 70       |  |
| 51-382-603   | 25-0007             | 1      | —             | —  | 100         | —   | 4.00     | 0.750            | 0.063              | 1.345<br><i>(34.163)</i> | A           | 10                          | 22         | 28         | 43       | 80        | 70         | 70       |  |
| † 51-351-604 | 26-0012             | 1      | —             | —  | 150         | 125 | 2.00     | 0.250            | 0.100              | 1.179<br><i>(29.947)</i> | A           | —                           | 13         | 21         | 43       | 80        | 70         | 70       |  |
| 51-351-603   | 26-0008             | 1      | —             | —  | 150         | 125 | 4.00     | 0.250            | 0.063              | 1.345<br><i>(34.163)</i> | A           | —                           | 11         | 18         | 33       | 80        | 70         | 70       |  |

† Also available through API's authorized distributors.

# Hermetically Sealed Threaded Case Filters


## .375 ø TT Circuit Standard Product

| Part Number  | MIL No | See Pg. LP35 for Fig. | Rated Voltage |    |     |     | I Amp | Min Cap μF | DCR Max Ohms | Max L |          | Thd Lgth | Minimum Insertion Loss (dB) |         |         |       |        |         |       |  |
|--------------|--------|-----------------------|---------------|----|-----|-----|-------|------------|--------------|-------|----------|----------|-----------------------------|---------|---------|-------|--------|---------|-------|--|
|              |        |                       | DC            | AC | DC  | AC  |       |            |              | In    | (mm)     |          | 30 KHz                      | 150 KHz | 300 KHz | 1 MHz | 10 MHz | 100 MHz | 1 GHz |  |
| SCI-2060-009 | —      | 1                     | —             | —  | 50  | —   | 0.25  | 1.500      | 12.000       | 1.241 | (31.521) | B        | 70                          | 70      | 70      | 70    | 70     | 70      | 70    |  |
| SCI-2060-013 | —      | 1                     | —             | —  | 50  | —   | 3.00  | 1.500      | 0.081        | 1.241 | (31.521) | B        | —                           | 33      | 54      | 70    | 70     | 70      | 70    |  |
| SCI-2060-007 | —      | 1                     | —             | —  | 50  | —   | 10.0  | 1.500      | 0.006        | 1.241 | (31.521) | A        | 15                          | 29      | 35      | 42    | 55     | 70      | 70    |  |
| SCI-2060-014 | —      | 1                     | —             | —  | 50  | —   | 10.0  | 1.500      | 0.006        | 1.241 | (31.521) | B        | 15                          | 29      | 35      | 42    | 55     | 70      | 70    |  |
| SCI-2160-011 | —      | 1                     | —             | —  | 100 | —   | 1.00  | 1.500      | 0.750        | 1.241 | (31.521) | B        | 12                          | 52      | 70      | 70    | 70     | 70      | 70    |  |
| SCI-2160-012 | —      | 1                     | —             | —  | 100 | —   | 2.00  | 1.500      | 0.189        | 1.241 | (31.521) | B        | —                           | 33      | 56      | 70    | 70     | 70      | 70    |  |
| SCI-2160-013 | —      | 1                     | —             | —  | 100 | —   | 3.00  | 1.500      | 0.081        | 1.241 | (31.521) | B        | —                           | 24      | 54      | 70    | 70     | 70      | 70    |  |
| SCI-2160-014 | —      | 1                     | —             | —  | 100 | —   | 10.0  | 1.400      | 0.006        | 1.241 | (31.521) | B        | 12                          | 25      | 32      | 42    | 55     | 70      | 70    |  |
| SCI-2360-011 | —      | 1                     | —             | —  | 300 | 125 | 1.00  | 0.500      | 0.750        | 1.241 | (31.521) | B        | —                           | 48      | 70      | 70    | 70     | 70      | 70    |  |
| SCI-2360-006 | —      | 1                     | —             | —  | 300 | 125 | 3.00  | 0.500      | 0.080        | 1.241 | (31.521) | A        | —                           | 12      | 38      | 70    | 70     | 70      | 70    |  |
| SCI-2360-007 | —      | 1                     | —             | —  | 300 | 125 | 10.0  | 0.500      | 0.006        | 1.241 | (31.521) | A        | 5                           | 18      | 24      | 34    | 55     | 70      | 70    |  |
| SCI-2360-014 | —      | 1                     | —             | —  | 300 | 125 | 10.0  | 0.500      | 0.006        | 1.241 | (31.521) | B        | 5                           | 18      | 24      | 34    | 55     | 70      | 70    |  |

# Hermetically Sealed Threaded Case Filters



## .690 ø C Circuit



## .690 ø C Circuit Standard Product

| Part Number     | MIL No | Figure | Rated Voltage |     |       |     | I Amp | Min Cap $\mu$ F | DCR Max Ohms | Max L |          | Minimum Insertion Loss (dB) |         |         |       |        |         |       |  |
|-----------------|--------|--------|---------------|-----|-------|-----|-------|-----------------|--------------|-------|----------|-----------------------------|---------|---------|-------|--------|---------|-------|--|
|                 |        |        | 85°C          |     | 125°C |     |       |                 |              | In    | L (mm)   | 30 KHz                      | 150 KHz | 300 KHz | 1 MHz | 10 MHz | 100 MHz | 1 GHz |  |
| † 9932-100-6004 | —      | 1      | 200           | —   | 150   |     | 15    | 2.600           | 0.005        | 0.702 | (17.831) | 10                          | 29      | 39      | 50    | 60     | 70      | 70    |  |
| 54-310-001      | —      | 1      | 300           | —   | 300   | 125 | 15    | 0.500           | 0.005        | 0.560 | (14.224) | 6                           | 19      | 25      | 36    | 50     | 70      | 70    |  |
| 54-310-005      | —      | 2      | 250           | —   | 200   | 125 | 25    | 0.500           | 0.005        | 0.750 | (19.050) | 6                           | 19      | 25      | 36    | 50     | 70      | 70    |  |
| 54-310-009      | —      | 1      | 450           | 240 | 400   | 240 | 15    | 0.250           | 0.005        | 0.560 | (14.224) | —                           | 14      | 19      | 30    | 45     | 60      | 70    |  |
| † 9932-100-6005 | —      | 1      | 450           | 240 | 400   | 240 | 15    | 0.250           | 0.005        | 0.560 | (14.224) | —                           | 14      | 19      | 30    | 50     | 70      | 70    |  |

## .690 ø C Circuit MIL Qualified Product

| Part Number | M15733<br>MIL<br>No | Figure | Rated Voltage |   |       |     | I<br>Amp | Min<br>Cap<br>μF | DCR<br>Max<br>Ohms | Max<br>L |          | Minimum Insertion Loss (dB) |            |            |          |           |            |          |  |
|-------------|---------------------|--------|---------------|---|-------|-----|----------|------------------|--------------------|----------|----------|-----------------------------|------------|------------|----------|-----------|------------|----------|--|
|             |                     |        | 85°C          |   | 125°C |     |          |                  |                    | In       | (mm)     | 30<br>KHz                   | 150<br>KHz | 300<br>KHz | 1<br>MHz | 10<br>MHz | 100<br>MHz | 1<br>GHz |  |
| 54-310-039  | 34-0037             | 1      | —             | — | 275   | 125 | 15       | 0.200            | 0.005              | 0.575    | (14.605) | 5                           | 15         | 21         | 31       | 51        | 70         | 70       |  |

## .690 ø C Circuit DSCC 84084 Product


| Part Number | 84084 No | Figure | Rated Voltage |    |       |     | I Amp | Min Cap $\mu$ F | DCR Max Ohms | Max L |          | Minimum Insertion Loss (dB) |         |         |       |        |         |       |
|-------------|----------|--------|---------------|----|-------|-----|-------|-----------------|--------------|-------|----------|-----------------------------|---------|---------|-------|--------|---------|-------|
|             |          |        | 85°C          |    | 125°C |     |       |                 |              | In    | L (mm)   | 30 KHz                      | 150 KHz | 300 KHz | 1 MHz | 10 MHz | 100 MHz | 1 GHz |
|             |          |        | DC            | AC | DC    | AC  |       |                 |              |       |          |                             |         |         |       |        |         |       |
| 54-310-042  | -001     | 1      | —             | —  | 400   | 230 | 15    | 0.150           | 0.005        | 0.700 | (17.780) | —                           | 10      | 16      | 26    | 40     | 52      | 70    |

† Also available through API's authorized distributors.

# Hermetically Sealed Threaded Case Filters



## .690 ø L Circuit




## .690 ø L Circuit Standard Product

| Part Number   | MIL No | Figure | Rated Voltage |     |     |     | I Amp | Min Cap µF | DCR Max Ohms | CKT | Max L |          | Minimum Insertion Loss (dB) |         |         |       |        |         |       |
|---------------|--------|--------|---------------|-----|-----|-----|-------|------------|--------------|-----|-------|----------|-----------------------------|---------|---------|-------|--------|---------|-------|
|               |        |        | DC            | AC  | DC  | AC  |       |            |              |     | In    | L (mm)   | 30 KHz                      | 150 KHz | 300 KHz | 1 MHz | 10 MHz | 100 MHz | 1 GHz |
| 9010-100-0049 | —      | 1      | 150           | —   | 100 | —   | 10.0  | 1.400      | 0.005        | LT  | 0.905 | (22.987) | 16                          | 24      | 34      | 44    | 60     | 70      | 70    |
| SCI-6120-008  | —      | 1      | 150           | —   | 100 | —   | 10.0  | 2.600      | 0.006        | LB  | 0.959 | (24.359) | 18                          | 32      | 39      | 49    | 70     | 70      | 70    |
| SCI-6120-009  | —      | 1      | 150           | —   | 100 | —   | 20.0  | 2.600      | 0.001        | LB  | 0.905 | (22.987) | 18                          | 32      | 39      | 49    | 60     | 70      | 70    |
| 51-320-041    | —      | 1      | 250           | —   | 200 | 125 | 10.0  | 0.500      | 0.008        | LT  | 0.905 | (22.987) | 5                           | 19      | 25      | 35    | 50     | 70      | 70    |
| 51-320-024    | —      | 1      | 450           | 240 | 400 | 240 | 1.00  | 0.360      | 0.210        | LT  | 0.905 | (22.987) | 5                           | 30      | 38      | 60    | 70     | 70      | 70    |
| 51-320-100    | —      | 1      | 450           | 240 | 400 | 240 | 1.00  | 0.250      | 0.210        | LT  | 0.905 | (22.987) | —                           | 21      | 33      | 55    | 70     | 70      | 70    |
| † 51-320-026  | —      | 1      | 450           | 240 | 400 | 240 | 3.00  | 0.360      | 0.030        | LT  | 0.905 | (22.987) | 5                           | 19      | 25      | 45    | 70     | 70      | 70    |
| 51-320-103    | —      | 1      | 450           | 240 | 400 | 240 | 5.00  | 0.360      | 0.010        | LB  | 0.905 | (22.987) | —                           | 12      | 18      | 30    | 60     | 70      | 70    |
| 51-322-007    | —      | 1      | 450           | 240 | 400 | 240 | 15.0  | 0.360      | 0.007        | LB  | 0.650 | (16.510) | 5                           | 19      | 25      | 35    | 48     | 62      | 70    |
| 51-322-015    | —      | 2      | 450           | 240 | 400 | 240 | 25.0  | 0.360      | 0.007        | LT  | 0.750 | (19.050) | 5                           | 17      | 23      | 34    | 48     | 62      | 70    |
| 51-322-036    | —      | 2      | 450           | 240 | 400 | 240 | 25.0  | 0.250      | 0.007        | LB  | 0.750 | (19.050) | —                           | 10      | 16      | 29    | 45     | 60      | 70    |
| 9010-100-0054 | —      | 1      | 450           | 240 | 300 | 240 | 1.00  | 0.150      | 0.250        | LT  | 0.905 | (22.987) | —                           | 14      | 32      | 52    | 70     | 70      | 70    |
| SCI-6320-004  | —      | 1      | 300           | —   | 300 | 125 | 1.00  | 0.400      | 0.300        | LB  | 0.959 | (24.359) | 6                           | 24      | 35      | 56    | 70     | 70      | 70    |


† Also available through API's authorized distributors.

## Hermetically Sealed Threaded Case Filters

### L-C Filter LT



### L-C Filter LB



### .690 ø L Circuit MIL Qualified Product

(See MIL index on pages CF9-11 for complete  
MIL part number listing)

| Part Number  | M15733<br>MIL<br>No | See Pg.<br>LP38<br>for Fig. | Rated Voltage |    |             |     | I<br>Amp | Min<br>Cap<br>µF | DCR<br>Max<br>Ohms | CKT | Max<br>L |          | Minimum Insertion Loss (dB) |            |            |          |           |            |          |  |
|--------------|---------------------|-----------------------------|---------------|----|-------------|-----|----------|------------------|--------------------|-----|----------|----------|-----------------------------|------------|------------|----------|-----------|------------|----------|--|
|              |                     |                             | 85°C<br>DC    | AC | 125°C<br>DC | AC  |          |                  |                    |     | In       | (mm)     | 30<br>KHz                   | 150<br>KHz | 300<br>KHz | 1<br>MHz | 10<br>MHz | 100<br>MHz | 1<br>GHz |  |
| † 51-320-015 | 27-0005             | 1                           | —             | —  | 200         | 125 | 3.00     | 0.250            | 0.033              | LT  | 0.900    | (22.860) | —                           | 14         | 21         | 39       | 80        | 70         | 70       |  |
| 51-320-017   | 27-0008             | 1                           | —             | —  | 200         | 125 | 5.00     | 0.250            | 0.016              | LT  | 0.900    | (22.860) | —                           | 13         | 19         | 32       | 69        | 70         | 70       |  |
| 51-320-018   | 27-0009             | 1                           | —             | —  | 200         | 125 | 5.00     | 0.250            | 0.016              | LB  | 0.900    | (22.860) | —                           | 13         | 19         | 32       | 69        | 70         | 70       |  |
| 51-323-003   | 27-0011             | 1                           | —             | —  | 200         | 125 | 10.0     | 0.250            | 0.005              | LT  | 1.031    | (26.187) | —                           | 13         | 19         | 30       | 61        | 70         | 70       |  |
| 51-323-004   | 27-0012             | 1                           | —             | —  | 200         | 125 | 10.0     | 0.250            | 0.005              | LB  | 1.031    | (26.187) | —                           | 13         | 19         | 30       | 61        | 70         | 70       |  |
| † 51-322-009 | 27-0014             | 2                           | —             | —  | 200         | 125 | 15.0     | 0.250            | 0.007              | LT  | 1.763    | (44.780) | —                           | 19         | 25         | 36       | 60        | 70         | 70       |  |
| 51-322-017   | 34-0002             | 2                           | —             | —  | 200         | 125 | 20.0     | 0.360            | 0.050              | LB  | 1.763    | (44.780) | —                           | 19         | 25         | 35       | 57        | 70         | 70       |  |


### .690 ø L Circuit DSCC 84084 Product

| Part Number | 84084<br>No | See Pg.<br>LP38<br>for Fig. | Rated Voltage |   |       |     | I<br>Amp | Min<br>Cap<br>µF | DCR<br>Max<br>Ohms | CKT | Max<br>L |          | Minimum Insertion Loss (dB) |            |            |          |           |            |          |  |
|-------------|-------------|-----------------------------|---------------|---|-------|-----|----------|------------------|--------------------|-----|----------|----------|-----------------------------|------------|------------|----------|-----------|------------|----------|--|
|             |             |                             | 85°C          |   | 125°C |     |          |                  |                    |     | In       | (mm)     | 30<br>KHz                   | 150<br>KHz | 300<br>KHz | 1<br>MHz | 10<br>MHz | 100<br>MHz | 1<br>GHz |  |
| 51-320-162  | -004        | 1                           | —             | — | 400   | 230 | 1.00     | 0.150            | 0.150              | LT  | 0.905    | (22.987) | —                           | 19         | 30         | 46       | 60        | 70         | 70       |  |
| 51-320-163  | -005        | 1                           | —             | — | 400   | 230 | 1.00     | 0.150            | 0.150              | LB  | 0.905    | (22.987) | —                           | 19         | 30         | 46       | 60        | 70         | 70       |  |
| 51-320-164  | -006        | 1                           | —             | — | 400   | 230 | 3.00     | 0.150            | 0.026              | LT  | 0.905    | (22.987) | —                           | 11         | 19         | 36       | 60        | 70         | 70       |  |
| 51-320-165  | -007        | 1                           | —             | — | 400   | 230 | 3.00     | 0.150            | 0.026              | LB  | 0.905    | (22.987) | —                           | 11         | 19         | 36       | 60        | 70         | 70       |  |
| 51-320-166  | -008        | 1                           | —             | — | 400   | 230 | 5.00     | 0.150            | 0.013              | LT  | 0.905    | (22.987) | —                           | 10         | 16         | 28       | 54        | 70         | 70       |  |
| 51-320-167  | -009        | 1                           | —             | — | 400   | 230 | 5.00     | 0.150            | 0.013              | LB  | 0.905    | (22.987) | —                           | 10         | 16         | 28       | 54        | 70         | 70       |  |
| 51-320-168  | -010        | 1                           | —             | — | 400   | 230 | 10.0     | 0.150            | 0.008              | LT  | 0.905    | (22.987) | —                           | 10         | 16         | 25       | 48        | 70         | 70       |  |
| 51-320-169  | -011        | 1                           | —             | — | 400   | 230 | 10.0     | 0.150            | 0.008              | LB  | 0.905    | (22.987) | —                           | 10         | 16         | 25       | 48        | 70         | 70       |  |

† Also available through API's authorized distributors.

# Hermetically Sealed Threaded Case Filters

## .690 ø Pi Circuit



## .690 ø Pi Circuit Standard Product

| Part Number  | MIL No | Figure | Rated Voltage |     |       |      | I Amp | Min Cap $\mu$ F | DCR Max Ohms | Max L |          | Minimum Insertion Loss (dB) |         |         |       |        |         |       |
|--------------|--------|--------|---------------|-----|-------|------|-------|-----------------|--------------|-------|----------|-----------------------------|---------|---------|-------|--------|---------|-------|
|              |        |        | 85°C          |     | 125°C |      |       |                 |              | In    | L (mm)   | 30 KHz                      | 150 KHz | 300 KHz | 1 MHz | 10 MHz | 100 MHz | 1 GHz |
| 51-321-322   | —      | 1      | 150           | —   | 100   | —    | 1.00  | 2.800           | 0.210        | 1.195 | (30.353) | 35                          | 69      | 70      | 70    | 70     | 70      | 70    |
| SCI-6130-009 | —      | 1      | 150           | —   | 100   | —    | 20.0  | 5.200           | 0.001        | 1.195 | (30.353) | 23                          | 31      | 35      | 35    | 70     | 70      | 70    |
| 51-321-317   | —      | 1      | 450           | 240 | 400   | *240 | 1.00  | 0.720           | 0.400        | 1.195 | (30.353) | —                           | 53      | 70      | 70    | 70     | 70      | 70    |
| †51-321-318  | —      | 1      | 450           | 240 | 400   | *240 | 3.00  | 0.720           | 0.030        | 1.195 | (30.353) | —                           | 31      | 51      | 70    | 70     | 70      | 70    |
| †51-321-319  | —      | 1      | 450           | 240 | 400   | *240 | 5.00  | 0.720           | 0.020        | 1.195 | (30.353) | —                           | 11      | 30      | 65    | 70     | 70      | 70    |

\* 0-60 Hz

## .690 ø Pi Circuit MIL Qualified Product

(See MIL index on pages CF8-10 for complete MIL part number listing)

| Part Number  | M15733<br>MIL<br>No | Figure | Rated Voltage |    |             |     | I<br>Amp | Min<br>Cap<br>μF | DCR<br>Max<br>Ohms | Max<br>L<br><i>(mm)</i> |             | Minimum Insertion Loss (dB) |            |            |          |           |            |          |
|--------------|---------------------|--------|---------------|----|-------------|-----|----------|------------------|--------------------|-------------------------|-------------|-----------------------------|------------|------------|----------|-----------|------------|----------|
|              |                     |        | 85°C<br>DC    | AC | 125°C<br>DC | AC  |          |                  |                    | In                      | <i>(mm)</i> | 30<br>KHz                   | 150<br>KHz | 300<br>KHz | 1<br>MHz | 10<br>MHz | 100<br>MHz | 1<br>GHz |
| 51-321-312   | 27-0004             | 1      | —             | —  | 200         | 125 | 1.00     | 0.500            | 0.250              | 1.195                   | (30.353)    | —                           | 47         | 65         | 80       | 80        | 70         | 70       |
| 51-323-313   | 27-0003             | 1      | —             | —  | 200         | 125 | 1.00     | 0.500            | 0.270              | 1.031                   | (26.187)    | —                           | 43         | 61         | 80       | 80        | 70         | 70       |
| 51-321-313   | 27-0010             | 1      | —             | —  | 200         | 125 | 5.00     | 0.500            | 0.024              | 1.195                   | (30.353)    | —                           | 10         | 28         | 64       | 80        | 70         | 70       |
| † 51-321-314 | 27-0013             | 1      | —             | —  | 200         | 125 | 10.0     | 0.500            | 0.008              | 1.195                   | (30.353)    | —                           | 16         | 18         | 48       | 80        | 70         | 70       |
| 51-321-329   | 34-0005             | 1      | —             | —  | 200         | 125 | 10.0     | 0.500            | 0.075              | 1.195                   | (30.353)    | —                           | 16         | 18         | 48       | 80        | 70         | 70       |


## .690 ø Pi Circuit DSCC 84084 Product

| Part Number | 84084 No | Figure | Rated Voltage |   |       |     | I<br>Amp | Min<br>Cap<br>μF | DCR<br>Max<br>Ohms | Max   |          | Minimum Insertion Loss (dB) |            |            |          |           |            |          |
|-------------|----------|--------|---------------|---|-------|-----|----------|------------------|--------------------|-------|----------|-----------------------------|------------|------------|----------|-----------|------------|----------|
|             |          |        | 85°C          |   | 125°C |     |          |                  |                    | L     | In       | 30<br>KHz                   | 150<br>KHz | 300<br>KHz | 1<br>MHz | 10<br>MHz | 100<br>MHz | 1<br>GHz |
| 51-321-398  | -013     | 2      | —             | — | 400   | 230 | 1.00     | 0.200            | 0.150              | 1.200 | (30.480) | —                           | 27         | 46         | 74       | 80        | 80         | 80       |
| 51-321-399  | -014     | 2      | —             | — | 400   | 230 | 3.00     | 0.200            | 0.026              | 1.200 | (30.480) | —                           | —          | 30         | 60       | 80        | 80         | 80       |
| 51-321-400  | -015     | 2      | —             | — | 400   | 230 | 5.00     | 0.200            | 0.013              | 1.200 | (30.480) | —                           | —          | 12         | 50       | 80        | 80         | 80       |
| 51-321-401  | -016     | 2      | —             | — | 400   | 230 | 10.0     | 0.200            | 0.008              | 1.200 | (30.480) | —                           | —          | —          | 30       | 80        | 80         | 80       |

† Also available through API's authorized distributors.

# Hermetically Sealed Threaded Case Filters

## .690 ø T Circuit



## .690 ø T Circuit Standard Product

| Part Number  | MIL No | Figure | Rated Voltage |     |       |     | I Amp | Min Cap μF | DCR Max Ohms | Max L |          | Minimum Insertion Loss (dB) |         |         |       |        |         |       |
|--------------|--------|--------|---------------|-----|-------|-----|-------|------------|--------------|-------|----------|-----------------------------|---------|---------|-------|--------|---------|-------|
|              |        |        | 85°C          |     | 125°C |     |       |            |              | In    | (mm)     | 30 KHz                      | 150 KHz | 300 KHz | 1 MHz | 10 MHz | 100 MHz | 1 GHz |
| SCI-6140-004 | —      | 1      | 150           | —   | 100   | —   | 1.00  | 2.600      | 0.600        | 1.195 | (30.353) | 23                          | 54      | 70      | 70    | 70     | 70      |       |
| SCI-6140-006 | —      | 1      | 150           | —   | 100   | —   | 3.00  | 2.600      | 0.100        | 1.195 | (30.353) | 21                          | 35      | 46      | 70    | 70     | 70      |       |
| SCI-6140-007 | —      | 1      | 150           | —   | 100   | —   | 5.00  | 2.600      | 0.060        | 1.195 | (30.353) | 21                          | 34      | 41      | 58    | 70     | 70      |       |
| SCI-6140-009 | —      | 1      | 150           | —   | 100   | —   | 20.0  | 2.600      | 0.002        | 1.195 | (30.353) | 21                          | 35      | 41      | 50    | 60     | 70      |       |
| 51-321-649   | —      | 1      | 250           | 125 | 200   | 125 | 2.00  | 0.360      | 0.090        | 1.195 | (30.353) | —                           | 24      | 38      | 65    | 70     | 70      |       |
| † 51-321-610 | —      | 1      | 450           | 240 | 400   | 240 | 1.00  | 0.360      | 0.600        | 1.195 | (30.353) | 7                           | 43      | 60      | 70    | 70     | 70      |       |

## .690 ø T Circuit MIL Qualified Product

(See MIL index on pages CF8-10 for complete MIL part number listing)

| Part Number | M15733<br>MIL<br>No | Figure | Rated Voltage |   |       |     | I<br>Amp | Min<br>Cap<br>µF | DCR<br>Max<br>Ohms | Max<br>L |          | Minimum Insertion Loss (dB) |            |            |          |           |            |          |
|-------------|---------------------|--------|---------------|---|-------|-----|----------|------------------|--------------------|----------|----------|-----------------------------|------------|------------|----------|-----------|------------|----------|
|             |                     |        | 85°C          |   | 125°C |     |          |                  |                    | In       | (mm)     | 30<br>KHz                   | 150<br>KHz | 300<br>KHz | 1<br>MHz | 10<br>MHz | 100<br>MHz | 1<br>GHz |
| 51-321-607  | 27-0017             | 1      | —             | — | 200   | 125 | 1.50     | 0.250            | 0.133              | 1.195    | (30.353) | —                           | 19         | 32         | 62       | 70        | 70         | 70       |
| 51-321-608  | 27-0018             | 1      | —             | — | 200   | 125 | 4.00     | 0.250            | 0.025              | 1.195    | (30.353) | —                           | 14         | 21         | 36       | 70        | 70         | 70       |
| 51-321-670  | 54-0017             | 2      | —             | — | 300   | 115 | 10.0     | 0.500            | 0.006              | 1.177    | (29.896) | 5                           | 20         | 23         | 35       | 60        | 70         | 60       |

† Also available through API's authorized distributors.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## API Technologies:

[54-367-054](#) [51-717-001](#) [SCI-2330-007](#) [9001-100-1025](#) [9001-100-1010](#) [9000-100-0048](#) [51-353-080](#) [9920-100-6002](#) [51-353-078](#) [51-353-079](#) [51-353-054](#) [51-353-077](#) [9050-100-0008](#) [M15733/26-0001](#) [M15733/24-0006](#) [M15733/44-0002](#) [M15733/61-0008](#) [51-444-060](#) [51-311-316](#) [M15733/38-0006](#) [54-310-009](#) [54-367-057](#) [54-370-006](#) [9001-100-1081](#) [9010-100-0018A](#) [9051-101-0018](#) [51-311-310](#) [51-321-672](#) [51-322-015](#) [51-344-006](#) [51-353-109](#) [51-359-007](#) [51-444-002](#) [M15733/23-0053](#) [M15733/23-0058](#) [M15733/25-0003](#) [M15733/25-0006](#) [M15733/25-0007](#) [M15733/25-0008](#) [M15733/27-0014](#) [M15733/34-0001](#) [M15733/38-0002](#) [M15733/38-0004](#) [M28861/01-003TB](#) [M28861/01-006TB](#) [M28861/01-010TB](#) [M28861/01-018TB](#) [M28861/02-006TB](#) [SCI-1021-000](#) [SCI-1021-020](#) [SCI-2030-004](#) [SCI-2060-007](#) [SCI-2120-014](#) [SCI-2120-014Q](#) [SCI-2140-007](#) [SCI-2320-006](#) [SCI-6130-009](#) [51-359-086](#) [9051F-100-0000](#) [M15733/23-0038](#) [M15733/58-0002](#) [SCI-2320-002](#) [SCI-1020-000](#) [51-359-024](#) [51-359-021](#) [51-353-336](#) [51-359-001](#) [M15733/62-0004](#) [51-359-044](#) [9053-100-0002](#) [9053-100-0001](#) [9200-300-0025](#) [51-390-318](#) [9932-100-6004](#) [9932-100-6005](#) [M15733/25-0004](#) [51-359-051](#) [51-359-055](#) [54-367-007](#) [54-367-006](#) [54-367-008](#) [9051-100-0000](#) [M15733/49-0008](#) [51-322-009](#) [51-359-053](#) [SCI-6140-007A](#) [9000-103-0019](#) [51-359-088](#) [51F-717-001](#) [51-353-345](#) [51-311-312](#) [51-321-312](#) [54-310-039](#) [54-367-051](#) [51-321-670](#) [51-323-313](#) [51-359-085G](#) [51-359-086G](#) [M15733/27-0013](#) [SCI-1020-020](#)