

## CMOS Dual Precision Monostable Multivibrator

High-Voltage Types (20-Volt Rating)

### Features:

- Retriggerable/resettable capability
- Trigger and reset propagation delays independent of  $R_X$ ,  $C_X$
- Triggering from leading or trailing edge
- Q and  $\bar{Q}$  buffered outputs available
- Separate resets
- Replaces CD4538B Type

■ CD14538B dual precision monostable multivibrator provides stable retriggerable/resettable one-shot operation for any fixed-voltage timing application.

An external resistor ( $R_X$ ) and an external capacitor ( $C_X$ ) control the timing and accuracy for the circuit. Adjustment of  $R_X$  and  $C_X$  provides a wide range of output pulse widths from the Q and  $\bar{Q}$  terminals. The time delay from trigger input to output transition (trigger propagation delay) and the time delay from reset input to output transition (reset propagation delay) are independent of  $R_X$  and  $C_X$ . Precision control of output pulse widths is achieved through linear CMOS techniques.

Leading-edge-triggering (+TR) and trailing-edge-triggering (-TR) inputs are provided for triggering from either edge of an input pulse. An unused +TR input should be tied to  $V_{SS}$ . An unused -TR input should be tied to  $V_{DD}$ . A RESET (on low level) is provided for immediate termination of the output pulse or to prevent output pulses when power is turned on. An unused RESET input should be tied to  $V_{DD}$ . However, if an entire section of the CD14538B is not used, its inputs must be tied to either  $V_{DD}$  or  $V_{SS}$ . See Table 1.


In normal operation the circuit retriggers (extends the output pulse one period) on the application of each new trigger pulse. For operation in the non-retriggerable mode,  $\bar{Q}$  is connected to -TR when leading-edge triggering (+TR) is used or Q is connected to +TR when trailing-edge triggering (-TR) is used. The time period (T) for this multivibrator can be calculated by:  $T = R_X C_X$ .

The minimum value of external resistance,  $R_X$ , is 4 K $\Omega$ . The minimum and maximum values of external capacitance,  $C_X$ , are 0 pF and 100  $\mu$ F, respectively.

The CD14538B is interchangeable with type MC14538 and is similar to and pin-compatible with the CD4098B\* and CD4538B. It can replace the CD4538B which type is not recommended for new designs.

The CD14538B types are supplied in 16-lead hermetic dual-in-line ceramic packages (F3A suffix), 16-lead dual-in-line plastic packages (E suffix), 16-lead small-outline packages (M, M96, MT, and NSR suffixes), and 16-lead thin shrink small-outline packages (PW and PWR suffixes).


\* $T = 0.5 R_X C_X$  for  $C_X \geq 1000$  pF    \* $T = R_X C_X$ ;  $C_{Xmin} = 5000$  pF



- Wide range of output-pulse widths
- Schmitt-trigger input allows unlimited rise and fall times on +TR and -TR inputs
- 100% tested for maximum quiescent current at 20 V
- Maximum input current of 1  $\mu$ A at 18 V over full package-temperature range; 100 nA at 18 V and 25°C
- Noise margin (full package-temperature range):
  - 1 V at  $V_{DD} = 5$  V
  - 2 V at  $V_{DD} = 10$  V
  - 2.5 V at  $V_{DD} = 15$  V
- 5-V, 10-V, and 15-V parametric ratings
- Standardized, symmetrical output characteristics
- Meets all requirements of JEDEC Tentative Standard No. 13B, "Standard Specifications for Description of 'B' Series CMOS Devices."

### Applications:

- Pulse delay and timing
- Pulse shaping



TERMINALS 1, 8, 15 ARE  
ELECTRICALLY CONNECTED  
INTERNALLY

92CS-24848R1

### Terminal Assignment

## CD14538B Types

### MAXIMUM RATINGS, Absolute-Maximum Values:

DC SUPPLY-VOLTAGE RANGE, ( $V_{DD}$ )

Voltages referenced to  $V_{SS}$  Terminal) ..... -0.5V to +20V

INPUT VOLTAGE RANGE, ALL INPUTS

..... -0.5V to  $V_{DD} + 0.5V$

DC INPUT CURRENT, ANY ONE INPUT

.....  $\pm 10mA$

POWER DISSIPATION PER PACKAGE ( $P_D$ ):

For  $T_A = -55^\circ C$  to  $+100^\circ C$  ..... 500mW

For  $T_A = +100^\circ C$  to  $+125^\circ C$  ..... Derate Linearly at 12mW/ $^\circ C$  to 200mW

DEVICE DISSIPATION PER OUTPUT TRANSISTOR

FOR  $T_A =$  FULL PACKAGE-TEMPERATURE RANGE (All Package Types) ..... 100mW

OPERATING-TEMPERATURE RANGE ( $T_A$ )

.....  $-55^\circ C$  to  $+125^\circ C$

STORAGE TEMPERATURE RANGE ( $T_{stg}$ )

.....  $-65^\circ C$  to  $+150^\circ C$

LEAD TEMPERATURE (DURING SOLDERING):

At distance  $1/16 \pm 1/32$  inch ( $1.59 \pm 0.79mm$ ) from case for 10s max .....  $+265^\circ C$

### RECOMMENDED OPERATING CONDITIONS

For maximum reliability, nominal operating conditions should be selected so that operating is always within the following ranges:

| CHARACTERISTIC                                                   | $V_{DD}$<br>(V) | LIMITS |      | UNITS |
|------------------------------------------------------------------|-----------------|--------|------|-------|
|                                                                  |                 | Min.   | Max. |       |
| Supply-Voltage Range (For $T_A$ =Full Package-Temperature-Range) | —               | 3      | 18   | V     |
| Input Pulse Width<br>+TR, -TR, or RESET<br>$t_{WH}, t_{WL}$      | 5               | 140    | —    | ns    |
|                                                                  | 10              | 80     | —    |       |
|                                                                  | 15              | 60     | —    |       |

TABLE I  
CD4538B FUNCTIONAL TERMINAL CONNECTIONS

| FUNCTION                                    | $V_{DD}$ TO<br>TERM. NO. |                   | $V_{SS}$ TO<br>TERM. NO. |                   | INPUT PULSE<br>TO TERM. NO. |                   | OTHER<br>CONNECTIONS |                   |
|---------------------------------------------|--------------------------|-------------------|--------------------------|-------------------|-----------------------------|-------------------|----------------------|-------------------|
|                                             | MONO <sub>1</sub>        | MONO <sub>2</sub> | MONO <sub>1</sub>        | MONO <sub>2</sub> | MONO <sub>1</sub>           | MONO <sub>2</sub> | MONO <sub>1</sub>    | MONO <sub>2</sub> |
| Leading-Edge Trigger/<br>Retriggerable      | 3, 5                     | 11, 13            |                          |                   | 4                           | 12                |                      |                   |
| Leading-Edge Trigger/<br>Non-Retriggerable  | 3                        | 13                |                          |                   | 4                           | 12                | 5-7                  | 11-9              |
| Trailing-Edge Trigger/<br>Retriggerable     | 3                        | 13                | 4                        | 12                | 5                           | 11                |                      |                   |
| Trailing-Edge Trigger/<br>Non-Retriggerable | 3                        | 13                |                          |                   | 5                           | 11                | 4-6                  | 12-10             |

#### NOTES:

1. A RETRIGGERABLE ONE-SHOT MULTIVIBRATOR HAS AN OUTPUT PULSE WIDTH WHICH IS EXTENDED ONE FULL TIME PERIOD (T) AFTER APPLICATION OF THE LAST TRIGGER PULSE.
2. A NON-RETRIGGERABLE ONE-SHOT MULTIVIBRATOR HAS A TIME PERIOD (T) REFERENCED FROM THE APPLICATION OF THE FIRST TRIGGER PULSE.

INPUT PULSE TRAIN



RETRIGGERABLE MODE PULSE  
WIDTH (+TR MODE)



NON-RETRIGGERABLE MODE  
PULSE WIDTH  
(+TR MODE)



# CD14538B Types

## STATIC ELECTRICAL CHARACTERISTICS

| CHARACTERISTIC                                        | CONDITIONS            |                        |                        | LIMITS AT INDICATED TEMPERATURES (°C) |       |       |       |       |                   |      | UNITS |
|-------------------------------------------------------|-----------------------|------------------------|------------------------|---------------------------------------|-------|-------|-------|-------|-------------------|------|-------|
|                                                       | V <sub>O</sub><br>(V) | V <sub>IN</sub><br>(V) | V <sub>DD</sub><br>(V) | -55                                   | -40   | +85   | +125  | Min.  | +25<br>Typ.       | Max. |       |
| Quiescent Device<br>Current, I <sub>DD</sub> Max.     | —                     | 0,5                    | 5                      | 5                                     | 5     | 150   | 150   | —     | 0.04              | 5    | μA    |
|                                                       | —                     | 0,10                   | 10                     | 10                                    | 10    | 300   | 300   | —     | 0.04              | 10   |       |
|                                                       | —                     | 0,15                   | 15                     | 20                                    | 20    | 600   | 600   | —     | 0.04              | 20   |       |
|                                                       | —                     | 0,20                   | 20                     | 100                                   | 100   | 3000  | 3000  | —     | 0.08              | 100  |       |
| Output Low (Sink)<br>Current, I <sub>OL</sub> Min.    | 0.4                   | 0,5                    | 5                      | 0.64                                  | 0.61  | 0.42  | 0.36  | 0.51  | 1                 | —    | mA    |
|                                                       | 0.5                   | 0,10                   | 10                     | 1.6                                   | 1.5   | 1.1   | 0.9   | 1.3   | 2.6               | —    |       |
|                                                       | 1.5                   | 0,15                   | 15                     | 4.2                                   | 4     | 2.8   | 2.4   | 3.4   | 6.8               | —    |       |
| Output High (Source)<br>Current, I <sub>OH</sub> Min. | 4.6                   | 0,5                    | 5                      | -0.64                                 | -0.61 | -0.42 | -0.36 | -0.51 | -1                | —    | mA    |
|                                                       | 2.5                   | 0,5                    | 5                      | -2                                    | -1.8  | -1.3  | -1.15 | -1.6  | -3.2              | —    |       |
|                                                       | 9.5                   | 0,10                   | 10                     | -1.6                                  | -1.5  | -1.1  | -0.9  | -1.3  | -2.6              | —    |       |
|                                                       | 13.5                  | 0,15                   | 15                     | -4.2                                  | -4    | -2.8  | -2.4  | -3.4  | -6.8              | —    |       |
| Output Voltage:<br>Low-Level, V <sub>OL</sub> Max.    | —                     | 0,5                    | 5                      | 0.05                                  |       |       |       | —     | 0                 | 0.05 | V     |
|                                                       | —                     | 0,10                   | 10                     | 0.05                                  |       |       |       | —     | 0                 | 0.05 |       |
|                                                       | —                     | 0,15                   | 15                     | 0.05                                  |       |       |       | —     | 0                 | 0.05 |       |
| Output Voltage:<br>High-Level, V <sub>OH</sub> Min.   | —                     | 0,5                    | 5                      | 4.95                                  |       |       |       | 4.95  | 5                 | —    | V     |
|                                                       | —                     | 0,10                   | 10                     | 9.95                                  |       |       |       | 9.95  | 10                | —    |       |
|                                                       | —                     | 0,15                   | 15                     | 14.95                                 |       |       |       | 14.95 | 15                | —    |       |
| Input Low Voltage,<br>V <sub>IL</sub> Max.            | 0.5, 4.5              | —                      | 5                      | 1.5                                   |       |       |       | —     | —                 | 1.5  | V     |
|                                                       | 1, 9                  | —                      | 10                     | 3                                     |       |       |       | —     | —                 | 3    |       |
|                                                       | 1.5, 13.5             | —                      | 15                     | 4                                     |       |       |       | —     | —                 | 4    |       |
| Input High Voltage,<br>V <sub>IH</sub> Min.           | 0.5, 4.5              | —                      | 5                      | 3.5                                   |       |       |       | 3.5   | —                 | —    | V     |
|                                                       | 1, 9                  | —                      | 10                     | 7                                     |       |       |       | 7     | —                 | —    |       |
|                                                       | 1.5, 13.5             | —                      | 15                     | 11                                    |       |       |       | 11    | —                 | —    |       |
| Input Current,<br>I <sub>IN</sub> Max.                | —                     | 0,18                   | 18                     | ±0.1                                  | ±0.1  | ±1    | ±1    | —     | ±10 <sup>-5</sup> | ±0.1 | μA    |




Fig. 1 - Logic diagram (1/2 of device shown).

## CD14538B Types

**DYNAMIC ELECTRICAL CHARACTERISTICS, At  $T_A=25^\circ\text{C}$ ; Input  $t_r, t_f=20\text{ ns}$ ,  $C_L=50\text{ pF}$**

| CHARACTERISTIC                                                                                                    | TEST CONDITIONS<br>$V_{DD}$ (V) | LIMITS |         |      | UNITS         |
|-------------------------------------------------------------------------------------------------------------------|---------------------------------|--------|---------|------|---------------|
|                                                                                                                   |                                 | Min.   | Typ.    | Max. |               |
| Transition Time<br>$t_{TLH}, t_{THL}$                                                                             | 5                               | —      | 100     | 200  | ns            |
|                                                                                                                   | 10                              | —      | 50      | 100  |               |
|                                                                                                                   | 15                              | —      | 40      | 80   |               |
| Propagation Delay Time:<br>+TR or -TR to Q or $\bar{Q}$                                                           | 5                               | —      | 300     | 600  |               |
|                                                                                                                   | 10                              | —      | 150     | 300  |               |
|                                                                                                                   | 15                              | —      | 100     | 220  |               |
| Reset to Q or $\bar{Q}$                                                                                           | 5                               | —      | 250     | 500  |               |
|                                                                                                                   | 10                              | —      | 125     | 250  |               |
|                                                                                                                   | 15                              | —      | 95      | 190  |               |
| Minimum Input Pulse Width:<br>+TR, -TR or Reset                                                                   | 5                               | —      | 80      | 140  |               |
|                                                                                                                   | 10                              | —      | 40      | 80   |               |
|                                                                                                                   | 15                              | —      | 30      | 60   |               |
| Output Pulse Width - Q or $\bar{Q}$ :<br>$C_x = 0.002\text{ }\mu\text{F}$ , $R_x = 100\text{ K}\Omega$            | 5                               | 198    | 210     | 230  | $\mu\text{s}$ |
|                                                                                                                   | 10                              | 200    | 212     | 232  |               |
|                                                                                                                   | 15                              | 202    | 214     | 234  |               |
| $C_x=0.1\text{ }\mu\text{F}$ , $R_x=100\text{ K}\Omega$                                                           | 5                               | 9.4    | 9.97    | 10.5 | ms            |
|                                                                                                                   | 10                              | 9.4    | 9.95    | 10.6 |               |
|                                                                                                                   | 15                              | 9.5    | 10      | 10.6 |               |
| $C_x=10\text{ }\mu\text{F}$ , $R_x=100\text{ K}\Omega$                                                            | 5                               | 0.95   | 1       | 1.06 | s             |
|                                                                                                                   | 10                              | 0.95   | 1       | 1.06 |               |
|                                                                                                                   | 15                              | 0.96   | 1.01    | 1.07 |               |
| Pulse Width Match between<br>circuits in same package:<br>$C_x=0.1\text{ }\mu\text{F}$ , $R_x=100\text{ K}\Omega$ | 5                               | —      | $\pm 1$ | —    | %             |
|                                                                                                                   | 10                              | —      | $\pm 1$ | —    |               |
|                                                                                                                   | 15                              | —      | $\pm 1$ | —    |               |
| Minimum Retrigger Time<br>$t_{rr}$                                                                                | 5                               | 0      | —       | —    | ns            |
|                                                                                                                   | 10                              | 0      | —       | —    |               |
|                                                                                                                   | 15                              | 0      | —       | —    |               |
| Input Capacitance<br>$C_{IN}$                                                                                     | Any Input                       | —      | 5       | 7.5  | pF            |

\*Note: Minimum  $R_x$  value=4 K $\Omega$ , minimum  $C_x$  value=5000 pF.




Fig. 2 - Typical output low (sink) current characteristics.




Fig. 3 - Minimum output low (sink) current characteristics.

# CD14538B Types




Fig. 4 - Typical output high (source) current characteristics.




Fig. 5 - Minimum output high (source) current characteristics.




Fig. 6 - Typical propagation delay time as a function of load capacitance (+TR or -TR to Q or  $\bar{Q}$ ).




Fig. 7 - Typical propagation delay time as a function of load capacitance (RESET to Q or  $\bar{Q}$ ).




Fig. 8 - Typical transition time as a function of load capacitance.




Fig. 9 - Typical pulse-width variation as a function of supply voltage.




Fig. 10 - Typical pulse-width variation as a function of temperature ( $R_X = 100\text{ K}\Omega$ ,  $C_X = 0.1\text{ }\mu\text{F}$ ).




Fig. 11 - Typical pulse-width variation as a function of temperature ( $R_X = 100\text{ K}\Omega$ ,  $C_X = 2000\text{ pF}$ ).



## CD14538B Types




Fig. 12 - Typical total supply current as a function of output duty cycle.





Fig. 13 - Typical total supply current as a function of load capacitance.



92CS-27441R1

Fig. 14 - Input voltage test circuit.

### NOTE:

1. Test any combination of inputs.
2. When measuring  $V_{IH}$  or  $V_{IL}$  for Schmitt trigger inputs (+TR, -TR), the input must first be brought to  $V_{DD}$  or  $V_{SS}$ , respectively, then reduced to the specified limit.





Fig. 15 - Input leakage-current test circuit.



92CS-27401R1

Fig. 16 - Quiescent device current test circuit.

### Power-Down Mode

During a rapid power-down condition, as would occur with a power-supply short circuit or with a poorly filtered power supply, the energy stored in  $C_X$  could discharge into Pin 2 or 14. To avoid possible device damage in this mode, when  $C_X$  is  $\geq 0.5$  microfarad, a protection diode with a 1-ampere or higher rating (1N5395 or equivalent) and a separate ground return for  $C_X$  should be provided as shown in Fig. 17.




Fig. 17 - Rapid power-down protection circuit.

An alternate protection method is shown in Fig. 18, where a 51-ohm current-limiting resistor is inserted in series with  $C_X$ . Note that a small pulse width decrease will occur however, and  $R_X$  must be appropriately increased to obtain the originally desired pulse width.





Fig. 18 - Alternate rapid power-down protection circuit.

## CD14538B Types



Dimensions in parentheses are in millimeters and are derived from the basic inch dimensions as indicated. Grid graduations are in mils (10<sup>-3</sup> inch).

Dimensions and pad layout for CD14538BH.

**PACKAGING INFORMATION**

| Orderable Device | Status<br>(1) | Package Type | Package<br>Drawing | Pins | Package<br>Qty | Eco Plan<br>(2)            | Lead/Ball Finish<br>(6) | MSL Peak Temp<br>(3) | Op Temp (°C) | Device Marking<br>(4/5)       | Samples                 |
|------------------|---------------|--------------|--------------------|------|----------------|----------------------------|-------------------------|----------------------|--------------|-------------------------------|-------------------------|
| 5962-9055701EA   | ACTIVE        | CDIP         | J                  | 16   | 1              | TBD                        | A42                     | N / A for Pkg Type   | -55 to 125   | 5962-9055701EA<br>CD14538BF3A | <a href="#">Samples</a> |
| CD14538B-W       | ACTIVE        | WAFERSALE    | YS                 | 0    |                | TBD                        | Call TI                 | Call TI              |              |                               | <a href="#">Samples</a> |
| CD14538BE        | ACTIVE        | PDIP         | N                  | 16   | 25             | Pb-Free<br>(RoHS)          | CU NIPDAU               | N / A for Pkg Type   | -55 to 125   | CD14538BE                     | <a href="#">Samples</a> |
| CD14538BF        | ACTIVE        | CDIP         | J                  | 16   | 1              | TBD                        | A42                     | N / A for Pkg Type   | -55 to 125   | CD14538BF                     | <a href="#">Samples</a> |
| CD14538BF3A      | ACTIVE        | CDIP         | J                  | 16   | 1              | TBD                        | A42                     | N / A for Pkg Type   | -55 to 125   | 5962-9055701EA<br>CD14538BF3A | <a href="#">Samples</a> |
| CD14538BM        | ACTIVE        | SOIC         | D                  | 16   | 40             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | -55 to 125   | CD14538BM                     | <a href="#">Samples</a> |
| CD14538BM96      | ACTIVE        | SOIC         | D                  | 16   | 2500           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | -55 to 125   | CD14538BM                     | <a href="#">Samples</a> |
| CD14538BMT       | ACTIVE        | SOIC         | D                  | 16   | 250            | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | -55 to 125   | CD14538BM                     | <a href="#">Samples</a> |
| CD14538BNSR      | ACTIVE        | SO           | NS                 | 16   | 2000           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | -55 to 125   | CD14538B                      | <a href="#">Samples</a> |
| CD14538BNSRE4    | ACTIVE        | SO           | NS                 | 16   | 2000           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | -55 to 125   | CD14538B                      | <a href="#">Samples</a> |
| CD14538BPW       | ACTIVE        | TSSOP        | PW                 | 16   | 90             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | -55 to 125   | CM538B                        | <a href="#">Samples</a> |
| CD14538BPWG4     | ACTIVE        | TSSOP        | PW                 | 16   | 90             | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | -55 to 125   | CM538B                        | <a href="#">Samples</a> |
| CD14538BPWR      | ACTIVE        | TSSOP        | PW                 | 16   | 2000           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | -55 to 125   | CM538B                        | <a href="#">Samples</a> |
| CD14538BPWRG4    | ACTIVE        | TSSOP        | PW                 | 16   | 2000           | Green (RoHS<br>& no Sb/Br) | CU NIPDAU               | Level-1-260C-UNLIM   | -55 to 125   | CM538B                        | <a href="#">Samples</a> |

<sup>(1)</sup> The marketing status values are defined as follows:

**ACTIVE:** Product device recommended for new designs.

**LIFEBUY:** TI has announced that the device will be discontinued, and a lifetime-buy period is in effect.

**NRND:** Not recommended for new designs. Device is in production to support existing customers, but TI does not recommend using this part in a new design.

**PREVIEW:** Device has been announced but is not in production. Samples may or may not be available.

**OBSOLETE:** TI has discontinued the production of the device.



<sup>(2)</sup> Eco Plan - The planned eco-friendly classification: Pb-Free (RoHS), Pb-Free (RoHS Exempt), or Green (RoHS & no Sb/Br) - please check <http://www.ti.com/productcontent> for the latest availability information and additional product content details.

**TBD:** The Pb-Free/Green conversion plan has not been defined.

**Pb-Free (RoHS):** TI's terms "Lead-Free" or "Pb-Free" mean semiconductor products that are compatible with the current RoHS requirements for all 6 substances, including the requirement that lead not exceed 0.1% by weight in homogeneous materials. Where designed to be soldered at high temperatures, TI Pb-Free products are suitable for use in specified lead-free processes.

**Pb-Free (RoHS Exempt):** This component has a RoHS exemption for either 1) lead-based flip-chip solder bumps used between the die and package, or 2) lead-based die adhesive used between the die and leadframe. The component is otherwise considered Pb-Free (RoHS compatible) as defined above.

**Green (RoHS & no Sb/Br):** TI defines "Green" to mean Pb-Free (RoHS compatible), and free of Bromine (Br) and Antimony (Sb) based flame retardants (Br or Sb do not exceed 0.1% by weight in homogeneous material)

<sup>(3)</sup> MSL, Peak Temp. - The Moisture Sensitivity Level rating according to the JEDEC industry standard classifications, and peak solder temperature.


<sup>(4)</sup> There may be additional marking, which relates to the logo, the lot trace code information, or the environmental category on the device.

<sup>(5)</sup> Multiple Device Markings will be inside parentheses. Only one Device Marking contained in parentheses and separated by a "~" will appear on a device. If a line is indented then it is a continuation of the previous line and the two combined represent the entire Device Marking for that device.

<sup>(6)</sup> Lead/Ball Finish - Orderable Devices may have multiple material finish options. Finish options are separated by a vertical ruled line. Lead/Ball Finish values may wrap to two lines if the finish value exceeds the maximum column width.

**Important Information and Disclaimer:** The information provided on this page represents TI's knowledge and belief as of the date that it is provided. TI bases its knowledge and belief on information provided by third parties, and makes no representation or warranty as to the accuracy of such information. Efforts are underway to better integrate information from third parties. TI has taken and continues to take reasonable steps to provide representative and accurate information but may not have conducted destructive testing or chemical analysis on incoming materials and chemicals. TI and TI suppliers consider certain information to be proprietary, and thus CAS numbers and other limited information may not be available for release.


In no event shall TI's liability arising out of such information exceed the total purchase price of the TI part(s) at issue in this document sold by TI to Customer on an annual basis.

**TAPE AND REEL INFORMATION**


\*All dimensions are nominal

| Device      | Package Type | Package Drawing | Pins | SPQ  | Reel Diameter (mm) | Reel Width W1 (mm) | A0 (mm) | B0 (mm) | K0 (mm) | P1 (mm) | W (mm) | Pin1 Quadrant |
|-------------|--------------|-----------------|------|------|--------------------|--------------------|---------|---------|---------|---------|--------|---------------|
| CD14538BM96 | SOIC         | D               | 16   | 2500 | 330.0              | 16.4               | 6.5     | 10.3    | 2.1     | 8.0     | 16.0   | Q1            |
| CD14538BPWR | TSSOP        | PW              | 16   | 2000 | 330.0              | 12.4               | 6.9     | 5.6     | 1.6     | 8.0     | 12.0   | Q1            |

## TAPE AND REEL BOX DIMENSIONS




\*All dimensions are nominal

| Device      | Package Type | Package Drawing | Pins | SPQ  | Length (mm) | Width (mm) | Height (mm) |
|-------------|--------------|-----------------|------|------|-------------|------------|-------------|
| CD14538BM96 | SOIC         | D               | 16   | 2500 | 333.2       | 345.9      | 28.6        |
| CD14538BPWR | TSSOP        | PW              | 16   | 2000 | 367.0       | 367.0      | 35.0        |


J (R-GDIP-T\*\*)

14 LEADS SHOWN

# CERAMIC DUAL IN-LINE PACKAGE



| PINS **<br>DIM | 14                     | 16                     | 18                     | 20                     |
|----------------|------------------------|------------------------|------------------------|------------------------|
| A              | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC | 0.300<br>(7,62)<br>BSC |
| B MAX          | 0.785<br>(19,94)       | .840<br>(21,34)        | 0.960<br>(24,38)       | 1.060<br>(26,92)       |
| B MIN          | —                      | —                      | —                      | —                      |
| C MAX          | 0.300<br>(7,62)        | 0.300<br>(7,62)        | 0.310<br>(7,87)        | 0.300<br>(7,62)        |
| C MIN          | 0.245<br>(6,22)        | 0.245<br>(6,22)        | 0.220<br>(5,59)        | 0.245<br>(6,22)        |




4040083/F 03/03

- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - C. This package is hermetically sealed with a ceramic lid using glass frit.
  - D. Index point is provided on cap for terminal identification only on press ceramic glass frit seal only.
  - E. Falls within MIL STD 1835 GDIP1-T14, GDIP1-T16, GDIP1-T18 and GDIP1-T20.


## N (R-PDIP-T\*\*)

16 PINS SHOWN

## PLASTIC DUAL-IN-LINE PACKAGE




| PINS **             | 14               | 16               | 18               | 20               |
|---------------------|------------------|------------------|------------------|------------------|
| DIM                 |                  |                  |                  |                  |
| A MAX               | 0.775<br>(19,69) | 0.775<br>(19,69) | 0.920<br>(23,37) | 1.060<br>(26,92) |
| A MIN               | 0.745<br>(18,92) | 0.745<br>(18,92) | 0.850<br>(21,59) | 0.940<br>(23,88) |
| MS-001<br>VARIATION | AA               | BB               | AC               | AD               |



14/18 Pin Only  
20 Pin vendor option

4040049/E 12/2002


- NOTES:
- A. All linear dimensions are in inches (millimeters).
  - B. This drawing is subject to change without notice.
  - Falls within JEDEC MS-001, except 18 and 20 pin minimum body length (Dim A).
  - The 20 pin end lead shoulder width is a vendor option, either half or full width.





D (R-PDSO-G16)


PLASTIC SMALL OUTLINE



- NOTES:
- A. All linear dimensions are in millimeters.
  - B. This drawing is subject to change without notice.
  - C. Publication IPC-7351 is recommended for alternate designs.
  - D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC-7525 for other stencil recommendations.
  - E. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.


PW (R-PDSO-G16)

PLASTIC SMALL OUTLINE



4040064-4/G 02/11

- NOTES:
- A. All linear dimensions are in millimeters. Dimensioning and tolerancing per ASME Y14.5M-1994.
  - B. This drawing is subject to change without notice.
  - C. Body length does not include mold flash, protrusions, or gate burrs. Mold flash, protrusions, or gate burrs shall not exceed 0,15 each side.
  - D. Body width does not include interlead flash. Interlead flash shall not exceed 0,25 each side.
  - E. Falls within JEDEC MO-153



4211284-3/F 12/12

NOTES:


- A. All linear dimensions are in millimeters.
- B. This drawing is subject to change without notice.
- C. Publication IPC-7351 is recommended for alternate designs.
- D. Laser cutting apertures with trapezoidal walls and also rounding corners will offer better paste release. Customers should contact their board assembly site for stencil design recommendations. Refer to IPC-7525 for other stencil recommendations.
- E. Customers should contact their board fabrication site for solder mask tolerances between and around signal pads.

# MECHANICAL DATA

NS (R-PDSO-G\*\*)

PLASTIC SMALL-OUTLINE PACKAGE

14-PINS SHOWN



- NOTES:
- A. All linear dimensions are in millimeters.
  - B. This drawing is subject to change without notice.
  - C. Body dimensions do not include mold flash or protrusion, not to exceed 0,15.

## IMPORTANT NOTICE

Texas Instruments Incorporated and its subsidiaries (TI) reserve the right to make corrections, enhancements, improvements and other changes to its semiconductor products and services per JESD46, latest issue, and to discontinue any product or service per JESD48, latest issue. Buyers should obtain the latest relevant information before placing orders and should verify that such information is current and complete. All semiconductor products (also referred to herein as "components") are sold subject to TI's terms and conditions of sale supplied at the time of order acknowledgment.

TI warrants performance of its components to the specifications applicable at the time of sale, in accordance with the warranty in TI's terms and conditions of sale of semiconductor products. Testing and other quality control techniques are used to the extent TI deems necessary to support this warranty. Except where mandated by applicable law, testing of all parameters of each component is not necessarily performed.

TI assumes no liability for applications assistance or the design of Buyers' products. Buyers are responsible for their products and applications using TI components. To minimize the risks associated with Buyers' products and applications, Buyers should provide adequate design and operating safeguards.

TI does not warrant or represent that any license, either express or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, machine, or process in which TI components or services are used. Information published by TI regarding third-party products or services does not constitute a license to use such products or services or a warranty or endorsement thereof. Use of such information may require a license from a third party under the patents or other intellectual property of the third party, or a license from TI under the patents or other intellectual property of TI.

Reproduction of significant portions of TI information in TI data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. TI is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of TI components or services with statements different from or beyond the parameters stated by TI for that component or service voids all express and any implied warranties for the associated TI component or service and is an unfair and deceptive business practice. TI is not responsible or liable for any such statements.

Buyer acknowledges and agrees that it is solely responsible for compliance with all legal, regulatory and safety-related requirements concerning its products, and any use of TI components in its applications, notwithstanding any applications-related information or support that may be provided by TI. Buyer represents and agrees that it has all the necessary expertise to create and implement safeguards which anticipate dangerous consequences of failures, monitor failures and their consequences, lessen the likelihood of failures that might cause harm and take appropriate remedial actions. Buyer will fully indemnify TI and its representatives against any damages arising out of the use of any TI components in safety-critical applications.

In some cases, TI components may be promoted specifically to facilitate safety-related applications. With such components, TI's goal is to help enable customers to design and create their own end-product solutions that meet applicable functional safety standards and requirements. Nonetheless, such components are subject to these terms.

No TI components are authorized for use in FDA Class III (or similar life-critical medical equipment) unless authorized officers of the parties have executed a special agreement specifically governing such use.

Only those TI components which TI has specifically designated as military grade or "enhanced plastic" are designed and intended for use in military/aerospace applications or environments. Buyer acknowledges and agrees that any military or aerospace use of TI components which have **not** been so designated is solely at the Buyer's risk, and that Buyer is solely responsible for compliance with all legal and regulatory requirements in connection with such use.

TI has specifically designated certain components as meeting ISO/TS16949 requirements, mainly for automotive use. In any case of use of non-designated products, TI will not be responsible for any failure to meet ISO/TS16949.

### Products

|                              |                                                                                      |
|------------------------------|--------------------------------------------------------------------------------------|
| Audio                        | <a href="http://www.ti.com/audio">www.ti.com/audio</a>                               |
| Amplifiers                   | <a href="http://amplifier.ti.com">amplifier.ti.com</a>                               |
| Data Converters              | <a href="http://dataconverter.ti.com">dataconverter.ti.com</a>                       |
| DLP® Products                | <a href="http://www.dlp.com">www.dlp.com</a>                                         |
| DSP                          | <a href="http://dsp.ti.com">dsp.ti.com</a>                                           |
| Clocks and Timers            | <a href="http://www.ti.com/clocks">www.ti.com/clocks</a>                             |
| Interface                    | <a href="http://interface.ti.com">interface.ti.com</a>                               |
| Logic                        | <a href="http://logic.ti.com">logic.ti.com</a>                                       |
| Power Mgmt                   | <a href="http://power.ti.com">power.ti.com</a>                                       |
| Microcontrollers             | <a href="http://microcontroller.ti.com">microcontroller.ti.com</a>                   |
| RFID                         | <a href="http://www.ti-rfid.com">www.ti-rfid.com</a>                                 |
| OMAP Applications Processors | <a href="http://www.ti.com/omap">www.ti.com/omap</a>                                 |
| Wireless Connectivity        | <a href="http://www.ti.com/wirelessconnectivity">www.ti.com/wirelessconnectivity</a> |

### Applications

|                               |                                                                                          |
|-------------------------------|------------------------------------------------------------------------------------------|
| Automotive and Transportation | <a href="http://www.ti.com/automotive">www.ti.com/automotive</a>                         |
| Communications and Telecom    | <a href="http://www.ti.com/communications">www.ti.com/communications</a>                 |
| Computers and Peripherals     | <a href="http://www.ti.com/computers">www.ti.com/computers</a>                           |
| Consumer Electronics          | <a href="http://www.ti.com/consumer-apps">www.ti.com/consumer-apps</a>                   |
| Energy and Lighting           | <a href="http://www.ti.com/energy">www.ti.com/energy</a>                                 |
| Industrial                    | <a href="http://www.ti.com/industrial">www.ti.com/industrial</a>                         |
| Medical                       | <a href="http://www.ti.com/medical">www.ti.com/medical</a>                               |
| Security                      | <a href="http://www.ti.com/security">www.ti.com/security</a>                             |
| Space, Avionics and Defense   | <a href="http://www.ti.com/space-avionics-defense">www.ti.com/space-avionics-defense</a> |
| Video and Imaging             | <a href="http://www.ti.com/video">www.ti.com/video</a>                                   |

### TI E2E Community

[e2e.ti.com](http://e2e.ti.com)