



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D2	REVISED PER ECO-16-002589	25FEB2016	NK	JO






- △1 HOUSING: HIGH TEMPERATURE, GLASS FILLED NYLON, COLOR: BLACK.
CONTACTS: PHOSPHOR BRONZE.
SCREWLOCKS: STEEL.
- △2 CONTACTS: 0.000381 MIN GOLD ON MATING RECEPTACLE END, 0.00254 BRIGHT TIN-LEAD ON REMAINDER, ALL OVER 0.001270 NICKEL.
SCREWLOCKS: CLEAR CHROMATE OVER ZINC.
- △3 NO CONTACT IN THIS POSITION FOR PART NUMBER 1375965-2 & -5 ONLY.
- △4 NO CONTACT IN THIS POSITION FOR PART NUMBER 1375965-3 & -6 ONLY.
- △5 CONTACTS: 0.000381 MIN GOLD ON MATING RECEPTACLE END, 0.00254-0.00508 MATTE TIN ON REMAINDER, ALL OVER 0.001270 NICKEL.
SCREWLOCKS: CLEAR CHROMATE OVER ZINC.
- △6 ROHS 2002/95/EC COMPLIANT PART TO BE USED WITH ROHS 2002/95/EC COMPLIANT PCB's.



△6	△5	YES △4	1375965-6
△6	△5	YES △3	1375965-5
△6	△5	NO	1375965-4
	△2	YES △4	1375965-3
	△2	YES △3	1375965-2
	△2	NO	1375965-1
FINISH		KEYED CIRCUITS	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN W.G. LENKER CHK L.L. BREKOSKY APVD	20JUN2000 15JAN2001 -
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:	
mm		0 PLC ± 1 PLC ± 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ± FINISH	
MATERIAL		WEIGHT	
△1		△5 △2	
CUSTOMER DRAWING		SCALE 5:1	
		SHEET 1 OF 2	
		REV D2	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN W.G.LENKER CHK L.L.BREKOSKY APVD	20JUN2000 15JAN2001 -
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ± FINISH	
MATERIAL - -		PRODUCT SPEC 108-1956 APPLICATION SPEC 114-13021 WEIGHT -	
CUSTOMER DRAWING		SIZE A1	NAME ASSEMBLY, PC/104-PLUS, NON-STACKTHROUGH CONTACTS, 2 STANDOFFS, SOLDER
SCALE 5:1		CAGE CODE 100779	DRAWING NO. 1375965
SHEET 2		OF 2	REV 02