






LOC	DIST	REVISIONS					
AF	50	P	LTR	DESCRIPTION	DATE	DWN	APVD
			T1	REVISED PER ECR-14-010405	22JUL14	jr	DC



SECTION B-B



SECTION C-C



PART NO	WIRE		INSULATION DIAMETER (MAX)	WIRE BARREL CRIMP				TENSILE STRENGTH POUNDS
	QTY	SIZE AWG		WIDTH	CRIMP HEIGHT	CRIMPER	ANVIL	
63316	1	14	.150	.120	.071	F	FLAT	50
	1	16			.063			30
	1	18			.057			20

5	REVERSE REELED	0.00381 [.000150] MIN NICKEL	T2 CR STEEL	63316-7
		0.00398 [.000157] MIN SILVER	H04 PHOS BRZ	7 63316-6
5	REVERSE REELED	TIN	BRASS	63316-5
		0.00381 [.000150] MIN NICKEL	T2 CR STEEL	63316-3
		TIN	BRASS	63316-2
		-	BRASS	63316-1
		FINISH	MATERIAL	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 6/16/87	 TE Connectivity			
		CHK MS FEHER 6/16/87				
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.25 [.010] 3 PLC ± - 4 PLC ± - ANGLES ± ± - FINISH	APVD C MEYERS 6/16/87	NAME RECEPTACLE, FLAG, FASTON, 4.75 [.187] SERIES			
		PRODUCT SPEC —				
		APPLICATION SPEC —				
MATERIAL	SEE TABLE	WEIGHT —	SIZE A2	CAGE CODE 00779	DRAWING NO C-63316	RESTRICTED TO —
CUSTOMER DRAWING			SCALE 7:1	SHEET 1 of 1	REV T1	