


REV	DOCUMENT	CHANGED BY	CHECK
A	0005401	DVM 17MAY04	AK



NOTES

- 1 - EXPLOSION PROOF - UNDERWRITERS LAB INC LISTING FOR HAZARDOUS LOCATIONS CLASS 1, GROUPS B,C AND D; CLASS 2 GROUPS E, F AND G
- 2 - EUROPEAN HAZARDOUS LOCATIONS DESIGNATION: EExd IIC T6 CATEGORY II 2 GD
- 3 - ALUMINUM ENCLOSURE FINISHED WITH BLUE AND BLACK EPOXY PAINT
- 4 - 6-32 UNC X (4,75) (.188) PAN HEAD TERMINAL SCREW (6 PER BASIC) (SEMS TERMI-LOX) (3 PER BASIC)
- 5 - CAMS MAY BE REPOSITIONED IN 7°20' INCREMENTS
- 6 - 1 BASIC; OPERATES CLOCKWISE AND COUNTER CLOCKWISE
- 7 - FOR USE IN TEMPERATURES UP TO 85°C
- 8 - SEE 7CX CHARTS 1 AND 2 (1 DRAWING) FOR LEVER ACTUATORS
- 9 - WEIGHT: 2.49 LB (1,13 Kg) APPROX

CHARACTERISTICS		ELECTRICAL DATA		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE:		DRAWN		DVM		17MAY04		Honeywell			
OPERATING TORQUE----- .922 LB FT (1,25 Nm) MAX		CONTACT ARRANGEMENT		☒ US (inch) CUSTOMARY ☐ SI (mm) METRIC		CHECK		AK		17MAY04					
RELEASE TORQUE----- .083 LB FT (0,113 Nm) MIN		D P D T		NO PLACE X ±.040 ±1		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.		SWITCH, ENCLOSED							
PRETRAVEL----- 30° MAX		L159		ONE PLACE .X ±.030 ±0,4											
DIFFERENTIAL TRAVEL----- 25° MAX		10A-125 OR 250 VAC		TWO PLACE .XX ±.015 ±0,15											
OVERTRAVEL-----75° MIN		0.3A-125 VDC; 0.15A-250 VDC		THREE PLACE .XXX ±.005 ±											
				ANGLES ±		THIRD ANGLE PROJECTION		DIMENSIONS ARE TO BE MET BEFORE PROTECTIVE COATINGS ARE APPLIED							
				RAW MATERIAL-COMMERCIAL STANDARD				3D PTC		ASME Y14.5M-1994		SIZE DWG TYPE DRAWING NAME REV			
		   								C I 14CX1E A					
										SCALE FULL WEIGHT 9 SHEET 1 OF 1					