

2,000 V - 5,000 V Rectifiers


0.05 A - 0.25 A Forward Current

70 ns Recovery Time

SMF6529

SMF6531





SMF6533



ELECTRICAL CHARACTERISTICS AND MAXIMUM RATINGS

Part Number	Working Reverse Voltage	Average Rectified Current		Reverse Current @ V _{rw}		Forward Voltage		1 Cycle Surge Current t _p =8.3ms (I _{fsm})	Repetitive Surge Current (I _{frm})	Reverse Recovery Time (3) (T _{rr})	Thermal Impd. θ_{J-C}	Junction Cap. @50VDC @1kHz (C _j)
	(V _{rw})	(I _o)		(I _r)		(V _f)						
	Volts	55°C(1) Amps	100°C(2) Amps	25°C μ A	100°C μ A	25°C Volts	25°C Amps	25°C Amps	25°C Amps	25°C ns	25°C °C / W	25°C pF
SMF6529	2000	0.250	0.125	0.1	10	3.0	0.025	10	1.50	70	20	4.0
SMF6531	3000	0.100	0.050	0.1	10	7.0	0.025	8	1.25	70	20	2.0
SMF6533	5000	0.050	0.025	0.1	10	9.0	0.025	4	0.75	70	20	1.0

(1) TC=55°C (2) TC=100°C (3) I_f=12.5mA, I_r=25.0mA, I_{rr}=6.3mA *Op. Temp.= -65°C to +175°C Stg. Temp.= -65°C to +200°C



Dimensions: In. (mm) • All temperatures are ambient unless otherwise noted. • Data subject to change without notice.



VOLTAGE MULTIPLIERS INC.
8711 W. Roosevelt Ave.
Visalia, CA 93291

TEL 559-651-1402
FAX 559-651-0740
www.voltagemultipliers.com