


KS883C02 (7A)

(20V / 7A)

SCHOTTKY BARRIER DIODE

■ Outline drawings, mm




■ Features

- Surface mount device
- Low V_F
- Super high speed switching
- High reliability by planer design

■ Applications

- High speed power switching

■ Connection diagram



■ Maximum ratings and characteristics






- Absolute maximum ratings

Item	Symbol	Conditions	Rating	Unit
Repetitive peak reverse voltage	V_{RRM}		20	V
Non-repetitive peak reverse voltage	V_{RSM}	$t_w=500ns$, duty=1/40	20	V
Average output current	I_o	Square wave, duty=1/2 $T_c=89^{\circ}C$	7.0*	A
Surge current	I_{FSM}	Sine wave 10ms	60	A
Operating junction temperature	T_j		-40 to +150	$^{\circ}C$
Storage temperature	T_{stg}		-40 to +150	$^{\circ}C$

* Average forward current of centertap full wave connection

- Electrical characteristics ($T_a=25^{\circ}C$ Unless otherwise specified)

Item	Symbol	Conditions	Max.	Unit
Forward voltage drop	V_{FM}	$I_{FM}=2.5A$	0.39	V
Reverse current	I_{RRM}	$V_R=V_{RRM}$	10.0	mA
Thermal resistance	$R_{th(j-c)}$	Junction to case	10.0	$^{\circ}C/W$

■ Characteristics**Forward Characteristic (typ.)****Reverse Characteristic (typ.)****Forward Power Dissipation****Reverse Power Dissipation****Current Derating (I_o - T_c)****Junction Capacitance Characteristic (typ.)**