





NO. A126

-3/4-24 UNS THD



CONTACT CONFIGURATION

SWITCH FUNCTION		
CONNECTED TERMINAL #		
PDS. 1	PDS. 2	PDS. 3
8-1	1-2	7-8

LEGEND

- = Detent Positions (45° or 90°)
- ⦿ = Key pull possible in these positions

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. CONTACT RATING: 4A @125VAC/28VDC, 2A @250VAC
5. CONTACT RESISTANCE: Below 10 milliohms
6. DIELECTRIC STRENGTH: 1kV RMS min. at sea level
7. ELECTRICAL LIFE: 10,000 make-and-break cycles
at full load.
8. ▲ DESIGNATE MAJOR FEATURES
9. MATERIALS:

CONTACTS: Silver Plated CU (Q Contact material)
TERMINALS: GOLD FLASH Over Silver (Q Contact material)
MOUNTING NUT: Nickel Plated zinc alloy

▲ KEYS: (2 Keys) Brass with code no. A126

CONTACT SPRING: Piano Wire			
▲ KEYS: (2 Keys) Brass with code no. A126			
A	11211	RELEASED FOR PRODUCTION	2/01/01
REV.	ECN No.	DESCRIPTION	DATE
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			
		CHKD	CJB

E-SWITCH®			
TITLE			
KD1301 (Key Code No. A126)			
SCALE	DATE	DR	REV
1:1	2/01/01	CJB	A
		DWG	
		K200218	