

Diagram illustrating the layout of a label with dimensions and components:

- Overall Dimensions:**
 - Height: 8.50
 - Width: 11.00
- Label Components:**
 - WHITE IMPRINT AREA:** Indicated by an arrow pointing to the top edge of the label.
 - CROSS HATCHED AREAS ARE CLEAR:** Indicated by an arrow pointing to the cross-hatched areas.
 - LASER IMSET LABELS:** Indicated by an arrow pointing to the top edge of the label.
 - PRINTER LEAD SIDE FEED IN THIS DIRECTION:** Indicated by an arrow pointing to the left edge of the label.
- Internal Dimensions and Spacing:**
 - .88:** Dimension from the left edge to the start of the first column of labels.
 - .80 TYP.:** Dimension between the centers of adjacent columns of labels.
 - 1.600 TYP. 6 PLCS.:** Dimension from the start of the first column to the end of the sixth column.
 - 1.000 TYP. 8 PLCS.:** Dimension from the end of the sixth column to the right edge of the label.

PART NUMBER	MATERIAL	MARKER SIZE inches (mm)	LABELS/ SHEET	SHEETS/ PKG.
S100X160YAJ	GMYZ	1.000" X 1.600"	48	53

PANDUIT CORP TINLEY PARK, ILLINOIS

OPTIMUM SELF-LAM. POLYESTER
LASER INK-JET LABELS
1.000" X 1.600"

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± (.XXX) ± .005
(.XX) ± .031 ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN IN
INCHES. THIRD ANGLE PROJECTION

	DRAIN BY RVU
--	-----------------

	MAT'Ls
--	--------

	SCALE
--	-------

NTS

DATE

	10-1-0
--	--------

SEE TABLE

DRAWING NO.

C10303

	DMS
--	-----

B

0	10-1-04	RVU		DRAWING RELEASED.
---	---------	-----	--	-------------------

3576

	R
--	---

	10
CHK'D	

CHK'D	
-------	--

--	--

REV	DATE	BY	CHK
-----	------	----	-----

DESCRIPTION

ECN

R

CUST

SUP

CHK'D	
-------	--