

DE5SC3ML

30V 5A


FEATURES

- SMT
- Tj150°C
- Low VF=0.45V
- PRRSM avalanche guaranteed
- High current capacity with Small Package

APPLICATION

- Switching power supply
- DC/DC converter
- Home Appliances, Office Equipment
- Telecommunication

OUTLINE DIMENSIONS



RATINGS


● Absolute Maximum Ratings (If not specified Tc=25°C)

Item	Symbol	Conditions	Ratings	Unit
Storage Temperature	Tstg		-55~150	°C
Operating Junction Temperature	Tj		150	°C
Maximum Reverse Voltage	VRM		30	V
Repetitive Peak Surge Reverse Voltage	VRRSM	Pulse width 0.5ms, duty 1/40	35	V
Average Rectified Forward Current	IO	50Hz sine wave, R-load, Rating for each diode IO/2, Tc=110°C	5	A
Peak Surge Forward Current	IFSM	50Hz sine wave, Non-repetitive 1 cycle peak value, Tj=25°C	90	A
Repetitive Peak Surge Reverse Power	PRRSM	Pulse width 10 μ s, Rating of per diode, Tj=25°C	330	W


● Electrical Characteristics (If not specified Tc=25°C)

Item	Symbol	Conditions	Ratings	Unit
Forward Voltage	VF	IF=2.5A, Pulse measurement, Rating of per diode	Max.0.45	V
Reverse Current	IR	VR=VRM, Pulse measurement, Rating of per diode	Max.3.5	mA
Junction Capacitance	Cj	f=1MHz, VR=10V, Rating of per diode	Typ.190	pF
Thermal Resistance	θ jc	junction to case	Max.12	°C/W


DE5SC3ML Forward Voltage




DE5SC3ML Junction Capacitance



DE5SC3ML Reverse Current




DE5SC3ML Reverse Power Dissipation



$T_j = 150^\circ\text{C}$



DE5SC3ML Forward Power Dissipation




$T_J = 150^\circ\text{C}$




DE5SC3ML


Derating Curve



$V_R = 15V$



DE5SC3ML Peak Surge Forward Capability



SBD Repetitive Surge Reverse Power Derating Curve

