





LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AG	0		G1	REVISED PER ECO-09-008864	11JUN09	DH	MB



P.C.B. LAYOUT

- 1 MATERIALS:
HOUSING - HIGH TEMPERATURE THERMOPLASTIC, UL94V-0, COLOR: BROWN.
CONTACT - PHOSPHOR BRONZE.
- 2 FINISH, CONTACT: 0.0038 MIN 100% TIN OVER 0.0011 MIN NICKEL.
3. PLCC DEVICE SHALL CONFORM TO JEDEC STANDARD MS-016.
- 4 HOUSING FLOOR TO BE SMOOTH WITHIN A 5.20 DIAMETER FOR VACUUM PLACEMENT.
- 5 TAPE PACKAGING TO CONFORM TO EIA RS-481-3. TAPE WIDTH SHALL BE 32mm, TAPE PITCH SHALL BE 24mm, AND REEL DIAMETER SHALL BE 330mm.
6. PLCC EXTRACTION TOOL: AMP PART NUMBER 821980-1 OR 822476-1.
7. PRODUCT DESIGN OBJECTIVES:
CURRENT RATING: 1 AMP, MAXIMUM
CONTACT RESISTANCE: 20 MILLIOHMS, MAXIMUM
DIELECTRIC WITHSTAND VOLTAGE: 600VAC, RMS, MINIMUM
INSULATION RESISTANCE: 5,000 MEGOHMS, MINIMUM
DURABILITY: 25 CYCLES
OPERATING TEMPERATURE RANGE: -55 TO +105C
MATING FORCE: 9.0 Kg, MAXIMUM
- 8 FINISH, CONTACT: 0.0038 MIN 93/7 TIN-LEAD OVER 0.0011 MIN NICKEL.
- 9 TUBE LENGTH 535mm. EXTERNAL CARTON 580 x 240 x 260mm TO HOLD 8,008 PIECES.
- 10 OBSOLETE PART NUMBER.

-	2	9	308	26	TUBES	822475-3
-	2	5	5	500	TAPE AND REEL	822475-2
10	8	5	5	500	TAPE AND REEL	822475-1
NOTES	FINISH	TUBES OR REELS/BOX	PCS/REEL OR TUBE	PACKAGING STYLE	AMP PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. HOLT 19OCT99	Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: mm		CHK K. KREIDLER 18OCT99				
		APVD K. KREIDLER 18OCT99	NAME SOCKET, MINI-PLCC, SURFACE MOUNT, 32 POSITION			
		PRODUCT SPEC SEE NOTES				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC NONE	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
0 PLC ± - 1 PLC ± - 2 PLC ± 0.20 3 PLC ± - 4 PLC ± - ANGLES ± -		WEIGHT 0.9 GRAMS	A2	00779	C=822475	-
MATERIAL - 1		SEE TABLE	CUSTOMER DRAWING		SCALE 3:1	SHEET 1 OF 1
					REV G1	