

## Polyester Modular Enclosures - NEMA 4X

### PJ Series - Lift-Off and Hinged Screw Cover



**Panel  
Sold  
Separately**



### Application

- Designed for use as instrument enclosures, electric, hydraulic or pneumatic control housings, electrical junction boxes or terminal wiring enclosures.
- Provides outstanding insulation and protection where equipment may be hosed down or be very wet.
- Ideal in applications with high temperatures or highly corrosive environments.

### Standards

- UL 508 Type 1, 2, 3, 4, 4X, 12 and 13
- UL 508 Type 6P (see table)
- CSA Type 1, 2, 3, 4, 4X, 12 and 13
- CSA Type 6P (see table)
- Complies with**

  - NEMA Type 1, 2, 3, 4, 4X, 12 and 13
  - IEC 60529, IP66

### Construction

- Molded fiberglass polyester enclosure with matching cover is easily punched, cut, or drilled.
- Enhanced UV inhibitors protect against outdoor weathering.
- Standard JIC sizes under 18" x 16".
- 10-32 threaded brass inserts are provided for optional inner panel or terminal kit mounting. Mounting hardware included.
- Cover is fastened with captive stainless steel screws in threaded brass inserts.
- Captive oil resistant gasket provides a positive seal.
- Threaded brass inserts are provided for mounting feet to the rear of the enclosure.
- Stainless steel mounting brackets and hardware are provided for mounting feet to the rear of the enclosure.
- Operating temperatures between 130°C and -40°C (266°F to -40°F).
- Impact index of 6.78J (5 ft/lb).
- For corrosion resistance information, please refer to table in the Technical Information section.

### Finish


- Fiberglass polyester material has a gray finish.
- Optional inner panels are available in white powder coated finished steel, unfinished aluminum, or Fiberglass.

### Accessories


- Painted steel inner panels  
...see page **138**
- PJ/ PJU swing panel...see page **138**
- Unfinished aluminum inner panels...see page **138**
- Fiberglass inner panels  
...see page **138**
- Terminal kit assemblies  
...see page **441**

## Polyester Modular Enclosures - NEMA 4X


### PJ Series - Lift-Off and Hinged Screw Cover




**Front View  
Hinged Screw Cover**



**Side View**



**End View**



**Optional Mounting Feet Locations**

#### Thermal Index

130°C to -40°C (266°F to -40°F)

#### Impact Index

6.78J (5 ft/lb)

Lift-Off Cover Part No.	Hinged Cover Part No.	Enclosure Dimensions A   B   C	Panel Dimensions D   E	Centers						Cover Dimensions U   W	Opt Steel Panel Part No. <sup>1</sup>	Ship Wt. Lbs.	
PJ664 <sup>2</sup>	PJ664H	6.10   6.10   4.13	4.88   4.88	3.76	5.01	5.01	3.52	4.25	4.25	7.32	5.83   0.49	7.69   7.69	14R0505   4
PJ864 <sup>2</sup>	PJ864H	8.00   6.12   4.13	6.75   4.88	3.68	6.89	5.01	3.47	6.25	4.25	9.19	5.85   0.50	9.59   7.71	14R0705   4
PJ1084 <sup>2</sup>	PJ1084H	10.13   8.26   4.13	8.75   6.88	3.68	8.89	7.01	3.47	8.25	6.25	11.19	7.85   0.50	11.77   9.90	14R0907   6
PJ1086 <sup>2</sup>	PJ1086H	10.13   8.26   6.13	8.75   6.88	5.68	8.89	7.01	5.47	8.25	6.25	11.19	7.85   0.50	11.77   9.90	14R0907   6
PJ12106 <sup>2</sup>	PJ12106H	12.13   10.26   6.13	10.75   8.88	5.68	10.89	9.01	5.47	10.25	8.25	13.19	9.85   0.50	13.77   11.90	14R1109   8
PJ14126 <sup>2</sup>	PJ14126H	14.13   12.26   6.13	12.75   10.88	5.68	12.89	11.01	5.47	12.25	10.25	15.19	11.85   0.50	15.73   13.85	14R1311   11
PJ16148	PJ16148H	16.27   14.40   8.13	14.75   12.88	7.68	14.89	13.01	7.47	14.25	12.25	17.19	13.71   0.50	17.87   15.99	14R1513   12
PJ18168	PJ18168H	18.40   16.40   8.13	16.88   14.88	7.68	16.97	14.97	7.47	16.25	14.25	19.28	15.72   0.50	20.00   18.00	P1868   17
PJ20168	PJ20168H	20.00   16.00   8.13	18.44   14.44	7.68	18.54	14.54	7.47	17.81	13.81	20.84	15.31   0.52	21.59   17.59	P2068   19

<sup>1</sup>For aluminum and fiberglass panels...see page 138.

<sup>2</sup>Type 6P

Technical references and CAD downloads available at [www.hammondmfg.com](http://www.hammondmfg.com)

All dimensions in inches unless specified otherwise

**Quality Products. Service Excellence.**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Hammond:

[PJ14126H](#) [PJ16148](#) [PJ12106H](#) [PJ18168H](#) [PJ12106](#) [PJ864H](#) [PJ14126](#) [PJ20168H](#) [PJ1086H](#) [PJ1086](#) [PJ20168](#)  
[PJ18168](#) [PJ16148H](#) [PJ864](#) [PJ664H](#) [PJ664](#) [PJ1084](#) [PJ1084H](#)