


M 4PB949-T2

DRAWING
 NUMBER

2

ISSUE

RELEASE NO. PR-12846
 CHECK
 PSR
 CHECK
 84
 2 MAR 84
 KAG
 CHECK
 84
 MARCH 84
 J A S I
 DRAWN
 FO-32848-A



NOTE -
 1- UNIT INCLUDES "IISM" TYPE BASIC SWITCH (4)
 2- TERMINALS ARE PLATED FOR SOLDERING
 3- SWITCHES DO NOT NECESSARILY OPERATE SIMULTANEOUSLY

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

CHARACTERISTICS	ELECTRICAL DATA	SCALE	FULL
OPERATING FORCE-----35 OZ APPROX TOTAL TRAVEL-----100 APPROX	CONTACT ARRANGEMENT S P D T (4)	DO NOT SCALE PRINT	
	250 VAC-----5 AMP 30 VOLTS DC RATING INDUCTIVE-----SEA LEVEL-----3 AMP 50,000 FT-----2.5 AMP RESISTIVE-----SEA LEVEL-----5 AMP 50,000 FT-----5 AMP MAXIMUM INRUSH-----24 AMP	TOLERANCES APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE ±	
		DIM. mm NO PLACES ONE PLACE TWO PLACES THREE PLACES ANGLES	TOL. mm/in 1/.04 0.4/.016 0.15/.008 SI METRIC
		DESIGN UNITS	US CUSTOMARY
		WEIGHT	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[4PB949-T2](#)