

TOSHIBA CMOS Digital Integrated Circuit Silicon Monolithic

TC74HC245AP, TC74HC245AF, TC74HC245AFW TC74HC640AP, TC74HC640AF

Octal Bus Transceiver

| | |
|--------------------|---------------------------|
| TC74HC245AP/AF/AFW | 3-State, Non-Inverting |
| TC74HC640AP/AF | 3-State, Inverting |

Note: xxxFW (JEDEC SOP) is not available in Japan.

The TC74HC245A, 640A are high speed CMOS OCTAL BUS TRANSCEIVERS fabricated with silicon gate C2MOS technology.

They achieve the high speed operation similar to equivalent LSTTL while maintaining the CMOS low power dissipation.

They are intended for two-way asynchronous communication between data busses. The direction of data transmission is determined by the level of the DIR input.

The enable input (\bar{G}) can be used to disable the device so that the busses are effectively isolated.

All inputs are equipped with protection circuits against static discharge or transient excess voltage.


Features (Note 1)(Note 2)

- High speed: $t_{pd} = 10 \text{ ns}$ (typ.) at $V_{CC} = 5 \text{ V}$
- Low power dissipation: $I_{CC} = 4 \mu\text{A}$ (max) at $T_a = 25^\circ\text{C}$
- High noise immunity: $V_{NIH} = V_{NIL} = 28\% V_{CC}$ (min)
- Output drive capability: 15 LSTTL loads
- Symmetrical output impedance: $|I_{OH}| = I_{OL} = 6 \text{ mA}$ (min)
- Balanced propagation delays: $t_{pLH} \approx t_{pHL}$
- Wide operating voltage range: $V_{CC} \text{ (opr)} = 2\sim 6 \text{ V}$
- Pin and function compatible with 74LS245/640

Note 1: Do not apply a signal to any bus terminal when it is in the output mode. Damage may result.


Note 2: All floating (high impedance) bus terminals must have their input levels fixed by means of pull up or pull down resistors.

TC74HC245AP, TC74HC640AP




DIP20-P-300-2.54A

TC74HC245AF, TC74HC640AF




SOP20-P-300-1.27A



SOP20-P-300-1.27

TC74HC245AFW




SOL20-P-300-1.27

Weight


| | |
|-------------------|-----------------|
| DIP20-P-300-2.54A | : 1.30 g (typ.) |
| SOP20-P-300-1.27A | : 0.22 g (typ.) |
| SOP20-P-300-1.27 | : 0.22 g (typ.) |
| SOL20-P-300-1.27 | : 0.46 g (typ.) |

Pin Assignment

TC74HC245A




TC74HC640A




IEC Logic Symbol

TC74HC245A



TC74HC640A



Truth Table

| Inputs | | Function | | Outputs | |
|-----------|-----|----------|--------|---------|---------------|
| \bar{G} | DIR | A Bus | B Bus | HC245A | HC640A |
| L | L | Output | Input | A = B | A = \bar{B} |
| L | H | Input | Output | B = A | B = \bar{A} |
| H | X | Z | | Z | Z |

X: "H" or "L"

Z: High impedance

Absolute Maximum Ratings (Note 1)

| Characteristics | Symbol | Rating | Unit |
|-----------------------------|-----------|------------------------------|------|
| Supply voltage range | V_{CC} | -0.5~7 | V |
| DC input voltage | V_{IN} | -0.5~ $V_{CC} + 0.5$ | V |
| DC output voltage | V_{OUT} | -0.5~ $V_{CC} + 0.5$ | V |
| Input diode current | I_{IK} | ± 20 | mA |
| Output diode current | I_{OK} | ± 20 | mA |
| DC output current | I_{OUT} | ± 35 | mA |
| DC V_{CC} /ground current | I_{CC} | ± 75 | mA |
| Power dissipation | P_D | 500 (DIP) (Note 2)/180 (SOP) | mW |
| Storage temperature | T_{stg} | -65~150 | °C |

Note 1: Exceeding any of the absolute maximum ratings, even briefly, lead to deterioration in IC performance or even destruction.

Note 2: 500 mW in the range of $T_a = -40$ to 65°C . From $T_a = 65$ to 85°C a derating factor of -10 mW/°C shall be applied until 300 mW.

Operating Range (Note)

| Characteristics | Symbol | Rating | Unit |
|--------------------------|------------|--|------|
| Supply voltage | V_{CC} | 2~6 | V |
| Input voltage | V_{IN} | 0~ V_{CC} | V |
| Output voltage | V_{OUT} | 0~ V_{CC} | V |
| Operating temperature | T_{opr} | -40~85 | °C |
| Input rise and fall time | t_r, t_f | 0~1000 ($V_{CC} = 2.0$ V) 0~500 ($V_{CC} = 4.5$ V) 0~400 ($V_{CC} = 6.0$ V) | ns |

Note: The operating range is required to ensure the normal operation of the device. Unused inputs and bus inputs must be tied to either V_{CC} or GND. Please connect both bus inputs and the bus outputs with V_{CC} or GND when the I/O of the bus terminal changes by the function. In this case, please note that the output is not short-circuited.

Electrical Characteristics

DC Characteristics

| Characteristics | Symbol | Test Condition | | Ta = 25°C | | | Ta = -40~85°C | | Unit | |
|----------------------------------|-----------------|---|--------------------------|---------------------|------|------|---------------|------|------|-----|
| | | | | V _{CC} (V) | Min | Typ. | Max | Min | | Max |
| High-level input voltage | V _{IH} | — | | 2.0 | 1.50 | — | — | 1.50 | — | V |
| | | | | 4.5 | 3.15 | — | — | 3.15 | — | |
| | | | | 6.0 | 4.20 | — | — | 4.20 | — | |
| Low-level input voltage | V _{IL} | — | | 2.0 | — | — | 0.50 | — | 0.50 | V |
| | | | | 4.5 | — | — | 1.35 | — | 1.35 | |
| | | | | 6.0 | — | — | 1.80 | — | 1.80 | |
| High-level output voltage | V _{OH} | V _{IN} = V _{IH} or V _{IL} | I _{OH} = -20 μA | 2.0 | 1.9 | 2.0 | — | 1.9 | — | V |
| | | | | 4.5 | 4.4 | 4.5 | — | 4.4 | — | |
| | | | | 6.0 | 5.9 | 6.0 | — | 5.9 | — | |
| | | | I _{OH} = -6 mA | 4.5 | 4.18 | 4.31 | — | 4.13 | — | |
| | | | | 6.0 | 5.68 | 5.80 | — | 5.63 | — | |
| Low-level output voltage | V _{OL} | V _{IN} = V _{IH} or V _{IL} | I _{OL} = 20 μA | 2.0 | — | 0.0 | 0.1 | — | 0.1 | V |
| | | | | 4.5 | — | 0.0 | 0.1 | — | 0.1 | |
| | | | | 6.0 | — | 0.0 | 0.1 | — | 0.1 | |
| | | | I _{OL} = 6 mA | 4.5 | — | 0.17 | 0.26 | — | 0.33 | |
| | | | | 6.0 | — | 0.18 | 0.26 | — | 0.33 | |
| 3-state output off-state current | I _{OZ} | V _{IN} = V _{IH} or V _{IL} V _{OUT} = V _{CC} or GND | | 6.0 | — | — | ±0.5 | — | ±5.0 | μA |
| Input leakage current | I _{IN} | V _{IN} = V _{CC} or GND | | 6.0 | — | — | ±0.1 | — | ±1.0 | μA |
| Quiescent supply current | I _{CC} | V _{IN} = V _{CC} or GND | | 6.0 | — | — | 4.0 | — | 40.0 | μA |

AC Characteristics (input: $t_r = t_f = 6$ ns)

| Characteristics | Symbol | Test Condition | | Ta = 25°C | | | Ta = -40~85°C | | Unit | | |
|-------------------------------|---------------------------|------------------|---------------------|-----------|------|-----|---------------|-----|------|----|----|
| | | CL (pF) | V _{CC} (V) | Min | Typ. | Max | Min | Max | | | |
| Output transition time | t_{TLH} t_{THL} | — | 50 | 2.0 | — | 52 | 60 | — | 75 | ns | |
| | | | | 4.5 | — | 7 | 12 | — | 15 | | |
| | | | | 6.0 | — | 6 | 10 | — | 13 | | |
| Propagation delay time | t_{pLH} t_{pHL} | — | 50 | 2.0 | — | 33 | 90 | — | 115 | ns | |
| | | | | 4.5 | — | 12 | 18 | — | 23 | | |
| | | | | 6.0 | — | 10 | 15 | — | 20 | | |
| | | | 150 | 2.0 | — | 48 | 120 | — | 150 | | ns |
| | | | | 4.5 | — | 16 | 24 | — | 30 | | |
| | | | | 6.0 | — | 14 | 20 | — | 26 | | |
| 3-state output enable time | t_{pZL} t_{pZH} | $R_L = 1k\Omega$ | 50 | 2.0 | — | 48 | 150 | — | 190 | ns | |
| | | | | 4.5 | — | 16 | 30 | — | 38 | | |
| | | | | 6.0 | — | 14 | 26 | — | 32 | | |
| | | | 150 | 2.0 | — | 63 | 180 | — | 225 | | ns |
| | | | | 4.5 | — | 21 | 36 | — | 45 | | |
| | | | | 6.0 | — | 18 | 31 | — | 38 | | |
| 3-state output disable time | t_{pLZ} t_{pHZ} | $R_L = 1k\Omega$ | 50 | 2.0 | — | 37 | 150 | — | 190 | ns | |
| | | | | 4.5 | — | 17 | 30 | — | 38 | | |
| | | | | 6.0 | — | 15 | 26 | — | 32 | | |
| Input capacitance | C _{IN} | DIR, G | | — | 5 | 10 | — | 10 | pF | | |
| Bus input capacitance | C _{OUT} | An, Bn | | — | 13 | — | — | — | pF | | |
| Power dissipation capacitance | C _{PD} (Note) | TC74HC245A | | — | 39 | — | — | — | pF | | |
| | | TC74HC640A | | — | 37 | — | — | — | | | |

Note: C_{PD} is defined as the value of the internal equivalent capacitance which is calculated from the operating current consumption without load.


Average operating current can be obtained by the equation:

$$I_{CC}(\text{opr}) = C_{PD} \cdot V_{CC} \cdot f_{IN} + I_{CC}/8 \text{ (per bit)}$$

Package Dimensions

DIP20-P-300-2.54A

Unit : mm




Weight: 1.30 g (typ.)

Package Dimensions

SOP20-P-300-1.27A

Unit: mm




Weight: 0.22 g (typ.)

Package Dimensions

SOP20-P-300-1.27

Unit : mm




Weight: 0.22 g (typ.)

Package Dimensions (Note)

SOL20-P-300-1.27

Unit : mm



Note: This package is not available in Japan.

Weight: 0.46 g (typ.)

RESTRICTIONS ON PRODUCT USE

20070701-EN

- The information contained herein is subject to change without notice.
- TOSHIBA is continually working to improve the quality and reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to comply with the standards of safety in making a safe design for the entire system, and to avoid situations in which a malfunction or failure of such TOSHIBA products could cause loss of human life, bodily injury or damage to property.
In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent TOSHIBA products specifications. Also, please keep in mind the precautions and conditions set forth in the "Handling Guide for Semiconductor Devices," or "TOSHIBA Semiconductor Reliability Handbook" etc.
- The TOSHIBA products listed in this document are intended for usage in general electronics applications (computer, personal equipment, office equipment, measuring equipment, industrial robotics, domestic appliances, etc.). These TOSHIBA products are neither intended nor warranted for usage in equipment that requires extraordinarily high quality and/or reliability or a malfunction or failure of which may cause loss of human life or bodily injury ("Unintended Usage"). Unintended Usage include atomic energy control instruments, airplane or spaceship instruments, transportation instruments, traffic signal instruments, combustion control instruments, medical instruments, all types of safety devices, etc.. Unintended Usage of TOSHIBA products listed in this document shall be made at the customer's own risk.
- The products described in this document shall not be used or embedded to any downstream products of which manufacture, use and/or sale are prohibited under any applicable laws and regulations.
- Please contact your sales representative for product-by-product details in this document regarding RoHS compatibility. Please use these products in this document in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances. Toshiba assumes no liability for damage or losses occurring as a result of noncompliance with applicable laws and regulations.