




PRODUCT NUMBER	DIM "J"	DIM "K"
76316-XXX	SEE NEXT SHEET	
76316-XXXC	SEE NEXT SHEET	



R TO FULL RADIUS ALLOWED TYP

NOTES:

- 1 MATERIAL HOUSING: THERMOPLASTIC POLYESTER
30 % GLASS FILLED, COLOUR BLUE, FLAME RETARDANT
PER UL 94-V0
- 2 MATERIAL BOX: BRASS ASTM B36 C26000-H02
- 3 MATERIAL SPRING: BERYLLIUM COPPER ASTM B 194
C 17200-TF 00
- 4 PLATING: SEE NEXT SHEET TIN PLATED
- 5 A LETTER "C" AT THE END OF PART NUMBER TO INDICATE
PACKAGING IN SHORT TUBES (550mm).

mal'l code SEE NOTES				tolerances unless otherwise specified		CUSTOMER COPY		BERG ELECTRONICS	
lir	ecn no	dr	date	linear		projection		title	
B	F80325	DLE	98.05.07	angles		mm		V. C. C.	
				dr		scale		DOUBLE ROW .100x.100	
				engr		5:1		product family	
				chr		A3		BERGCON	
				appd		76316		code	
sheet	revision	B	B					213	
index	sheet	1	2					1 of 2	

For all other products, please refer to the "BERG" logo in the top right corner of the drawing. The "BERG" logo is a registered trademark of BERG ELECTRONICS.

BERG
ELECTRONICS

For all other products, please refer to the "BERG" logo in the top right corner of the drawing. The "BERG" logo is a registered trademark of BERG ELECTRONICS.

PRODUCT NUMBER	NBR OF POS	DIM "J"	DIM "K"
76316-X02(C)	2x02	(2.54)	(5.08)
76316-X03(C)	2x03	(5.08)	(7.62)
76316-X04(C)	2x04	(7.62)	(10.16)
76316-X05(C)	2x05	(10.16)	(12.70)
76316-X06(C)	2x06	(12.70)	(15.24)
76316-X07(C)	2x07	(15.24)	(17.78)
76316-X08(C)	2x08	(17.78)	(20.32)
76316-X09(C)	2x09	(20.32)	(22.86)
76316-X10(C)	2x10	(22.86)	(25.40)
76316-X11(C)	2x11	(25.40)	(27.94)
76316-X12(C)	2x12	(27.94)	(30.48)
76316-X13(C)	2x13	(30.48)	(33.02)
76316-X14(C)	2x14	(33.02)	(35.56)
76316-X15(C)	2x15	(35.56)	(38.10)
76316-X16(C)	2x16	(38.10)	(40.64)
76316-X17(C)	2x17	(40.64)	(43.18)
76316-X18(C)	2x18	(43.18)	(45.72)
76316-X19(C)	2x19	(45.72)	(48.26)
76316-X20(C)	2x20	(48.26)	(50.80)
76316-X21(C)	2x21	(50.80)	(53.34)
76316-X22(C)	2x22	(53.34)	(55.88)
76316-X23(C)	2x23	(55.88)	(58.42)
76316-X24(C)	2x24	(58.42)	(60.96)
76316-X25(C)	2x25	(60.96)	(63.50)

PRODUCT NUMBER	NBR OF POS	DIM "J"	DIM "K"
76316-X26(C)	2x26	(63.50)	(66.04)
76316-X27(C)	2x27	(66.04)	(68.58)
76316-X28(C)	2x28	(68.58)	(71.12)
76316-X29(C)	2x29	(71.12)	(73.66)
76316-X30(C)	2x30	(73.66)	(76.20)
76316-X31(C)	2x31	(76.20)	(78.74)
76316-X32(C)	2x32	(78.74)	(81.28)
76316-X33(C)	2x33	(81.28)	(83.82)
76316-X34(C)	2x34	(83.82)	(86.36)
76316-X35(C)	2x35	(86.36)	(88.90)
76316-X36(C)	2x36	(88.90)	(91.44)
76316-X37(C)	2x37	(91.44)	(93.98)
76316-X38(C)	2x38	(93.98)	(96.52)
76316-X39(C)	2x39	(96.52)	(99.06)
76316-X40(C)	2x40	(99.06)	(101.60)
76316-X41(C)	2x41	(101.60)	(104.14)
76316-X42(C)	2x42	(104.14)	(106.68)
76316-X43(C)	2x43	(106.68)	(109.22)
76316-X44(C)	2x44	(109.22)	(111.76)
76316-X45(C)	2x45	(111.76)	(114.30)
76316-X46(C)	2x46	(114.30)	(116.84)
76316-X47(C)	2x47	(116.84)	(119.38)
76316-X48(C)	2x48	(119.38)	(121.92)
76316-X49(C)	2x49	(121.92)	(124.46)
76316-X50(C)	2x50	(124.46)	(127.00)

76316-9XX(C)	5µm Sn/Pb	1.25µm Sn/Pb
PLATING CODE X	PLATING THICKNESS IN CONTACT AREA	PRE-PLTEAD FLASH THICKNESS

mat'l code SEE TABLE				tolerances unless otherwise specified		CUSTOMER COPY		BERG ELECTRONICS	
lir	ecn no	dr	date	linear		projection	title V. C. C.		
B	F80325	DLE	98.05.07	angles			DOUBLE ROW .100x.100		
				dr	DLE	98.05.07	mm	product family	BERGCON
				engr	AESCHBACHER	98.05.07		code	213
				chr	AESCHBACHER	98.05.07		size dwg no	
				appd	NIZZI	98.05.07	scale	A3	76316
sheet index	revision sheet						N/A	sheet	2 of 2